

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903559

Luminaire Tested: DFN2DIP-SQ2F0-060D070US830-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903559  
REPORT IS A COMBINATION OF REPORTS P901346 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-060D070US830-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11338.7 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 109.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903559  
CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P903559  
 CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49	42
1	96	92	89	85	88	85	81	79	70	68	66	56	55	54	44	43	42	42	42	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	36	36	36	31
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	31	31	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	32	29	27	27	27	27	24
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	24	24	24	21
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21	21	21	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	19	19	19	16
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	17	17	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	16	16	16	13
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	14	14	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5139	5139	5139
5°	5139	5047	5083
10°	5079	4937	4911
15°	5000	4763	4648
20°	4899	4527	4329
25°	4795	4266	4021
30°	4658	3998	3632
35°	4524	3712	3291
40°	4387	3417	2901
45°	4229	3092	2549
50°	4065	2764	2204
55°	3892	2415	1874
60°	3692	2052	1536
65°	3462	1684	1374
70°	3181	1341	1234
75°	2829	1161	1108
80°	2323	942	938
85°	1512	586	669

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4229 cd/sqm



TEST NUMBER: P903559

CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.1	1.9
10°-20°	601.3	5.3
20°-30°	844.3	7.4
30°-40°	920.3	8.1
40°-50°	845.9	7.5
50°-60°	664.3	5.9
60°-70°	432.4	3.8
70°-80°	222.6	2.0
80°-90°	60.7	0.5
90°-100°	73.4	0.6
100°-110°	273.7	2.4
110°-120°	725.9	6.4
120°-130°	1204.0	10.6
130°-140°	1278.9	11.3
140°-150°	1188.6	10.5
150°-160°	955.6	8.4
160°-170°	615.8	5.4
170°-180°	211.9	1.9
0°-30°	1664.7	14.7
0°-40°	2585.0	22.8
0°-60°	4095.1	36.1
0°-90°	4810.9	42.4
90°-120°	1073.0	9.5
90°-150°	4744.6	41.8
90°-180°	6528.0	57.6
0°-180°	11338.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	2	19	32	40	44	11
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P903559

CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2



TEST NUMBER: P903559

CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7



TEST NUMBER: P903559  
 CATALOG NUMBER: DFN2DIP-SQ2F0-060D070US830-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.97	12.74	12.99	13.77	15.15	7.93	8.70	8.96	9.73	11.11
	3H	13.62	14.31	14.66	15.35	16.75	9.10	9.79	10.13	10.82	12.22
	4H	14.22	14.87	15.26	15.91	17.31	9.53	10.18	10.58	11.22	12.63
	6H	14.62	15.22	15.68	16.26	17.68	9.83	10.43	10.89	11.48	12.90
	8H	14.73	15.31	15.80	16.37	17.78	9.91	10.48	10.98	11.55	12.96
	12H	14.79	15.33	15.85	16.38	17.82	9.95	10.49	11.01	11.54	12.98
4H	2H	11.98	12.63	13.03	13.67	15.07	8.51	9.16	9.56	10.20	11.61
	3H	13.78	14.32	14.84	15.39	16.81	9.83	10.37	10.89	11.44	12.86
	4H	14.45	14.95	15.52	16.01	17.45	10.36	10.86	11.43	11.92	13.36
	6H	14.94	15.37	16.02	16.45	17.89	10.76	11.18	11.84	12.27	13.70
	8H	15.11	15.51	16.18	16.58	18.03	10.88	11.27	11.95	12.35	13.80
	12H	15.19	15.55	16.28	16.64	18.09	10.93	11.29	12.02	12.38	13.83
8H	4H	14.41	14.81	15.49	15.88	17.33	10.63	11.02	11.70	12.10	13.55
	6H	14.95	15.28	16.05	16.40	17.85	11.12	11.45	12.22	12.56	14.01
	8H	15.16	15.44	16.26	16.54	18.01	11.29	11.58	12.40	12.68	14.15
	12H	15.28	15.53	16.39	16.63	18.13	11.40	11.65	12.51	12.74	14.25
12H	4H	14.36	14.72	15.45	15.81	17.26	10.62	10.98	11.72	12.07	13.53
	6H	14.93	15.21	16.03	16.31	17.78	11.16	11.45	12.27	12.55	14.02
	8H	15.13	15.38	16.24	16.48	17.98	11.35	11.61	12.46	12.70	14.21