

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903611

Luminaire Tested: DFN2DIP-SQ2F0-080D080US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903611
REPORT IS A COMBINATION OF REPORTS P901362 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D080US830-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13874.3 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 143.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6853	6853	6853
5°	6852	6729	6777
10°	6772	6582	6547
15°	6667	6350	6198
20°	6532	6037	5772
25°	6393	5688	5361
30°	6211	5331	4843
35°	6032	4950	4388
40°	5850	4556	3868
45°	5639	4122	3398
50°	5420	3685	2939
55°	5190	3220	2499
60°	4923	2736	2048
65°	4616	2245	1832
70°	4242	1789	1645
75°	3772	1548	1477
80°	3097	1257	1251
85°	2016	780	890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5639 cd/sqm

TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	2.1
10°-20°	801.8	5.8
20°-30°	1125.7	8.1
30°-40°	1227.1	8.8
40°-50°	1127.8	8.1
50°-60°	885.7	6.4
60°-70°	576.5	4.2
70°-80°	296.8	2.1
80°-90°	80.2	0.6
90°-100°	83.9	0.6
100°-110°	312.8	2.3
110°-120°	829.6	6.0
120°-130°	1376.0	9.9
130°-140°	1461.6	10.5
140°-150°	1358.4	9.8
150°-160°	1092.1	7.9
160°-170°	703.7	5.1
170°-180°	242.2	1.7
0°-30°	2219.6	16.0
0°-40°	3446.7	24.8
0°-60°	5460.2	39.4
0°-90°	6413.8	46.2
90°-120°	1226.4	8.8
90°-150°	5422.4	39.1
90°-180°	7460.0	53.8
0°-180°	13874.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	2	22	37	46	50	13
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	

TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4

TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8

TEST NUMBER: P903611

CATALOG NUMBER: DFN2DIP-SQ2F0-080D080US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.36	14.16	14.35	15.16	16.48	9.32	10.12	10.31	11.12	12.45
	3H	15.01	15.73	16.02	16.74	18.09	10.49	11.20	11.49	12.21	13.56
	4H	15.61	16.28	16.62	17.30	18.65	10.92	11.60	11.94	12.61	13.97
	6H	16.01	16.63	17.04	17.65	19.02	11.22	11.85	12.25	12.87	14.23
	8H	16.13	16.72	17.16	17.75	19.12	11.31	11.90	12.34	12.93	14.30
	12H	16.18	16.74	17.22	17.77	19.16	11.34	11.90	12.38	12.93	14.32
4H	2H	13.37	14.04	14.39	15.06	16.41	9.90	10.58	10.92	11.59	12.95
	3H	15.17	15.73	16.20	16.78	18.14	11.22	11.79	12.26	12.83	14.20
	4H	15.85	16.36	16.89	17.40	18.79	11.76	12.27	12.80	13.31	14.70
	6H	16.34	16.78	17.39	17.84	19.23	12.15	12.60	13.20	13.65	15.04
	8H	16.50	16.92	17.55	17.97	19.37	12.27	12.68	13.32	13.73	15.14
	12H	16.59	16.96	17.66	18.02	19.43	12.32	12.70	13.39	13.76	15.17
8H	4H	15.81	16.22	16.86	17.27	18.67	12.02	12.43	13.07	13.49	14.89
	6H	16.35	16.69	17.42	17.78	19.18	12.51	12.85	13.59	13.95	15.35
	8H	16.55	16.85	17.63	17.93	19.35	12.69	12.99	13.77	14.07	15.49
	12H	16.68	16.94	17.76	18.01	19.47	12.79	13.06	13.88	14.13	15.59
12H	4H	15.76	16.13	16.82	17.19	18.60	12.02	12.39	13.09	13.46	14.87
	6H	16.32	16.62	17.40	17.70	19.12	12.56	12.86	13.64	13.93	15.35
	8H	16.53	16.79	17.61	17.86	19.32	12.75	13.01	13.84	14.09	15.55