

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906218

Luminaire Tested: DFN2DIP-SQ2F0-030D080US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906218
REPORT IS A COMBINATION OF REPORTS P899832 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US835-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9630.0 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2726	2726	2726
5°	2726	2677	2696
10°	2694	2619	2605
15°	2653	2526	2466
20°	2599	2402	2296
25°	2544	2263	2133
30°	2471	2121	1927
35°	2400	1969	1746
40°	2327	1813	1539
45°	2244	1640	1352
50°	2156	1466	1169
55°	2065	1281	994
60°	1958	1088	815
65°	1836	893	729
70°	1688	711	654
75°	1500	616	587
80°	1233	500	498
85°	802	311	354

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3527 cd/sqm

TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.2
10°-20°	319.0	3.3
20°-30°	447.9	4.7
30°-40°	488.2	5.1
40°-50°	448.7	4.7
50°-60°	352.4	3.7
60°-70°	229.4	2.4
70°-80°	118.1	1.2
80°-90°	37.3	0.4
90°-100°	156.6	1.6
100°-110°	497.5	5.2
110°-120°	851.3	8.8
120°-130°	1119.6	11.6
130°-140°	1256.7	13.0
140°-150°	1232.3	12.8
150°-160°	1033.7	10.7
160°-170°	685.6	7.1
170°-180°	239.6	2.5
0°-30°	883.1	9.2
0°-40°	1371.3	14.2
0°-60°	2172.4	22.6
0°-90°	2557.2	26.6
90°-120°	1505.3	15.6
90°-150°	5113.9	53.1
90°-180°	7073.0	73.4
0°-180°	9630.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	2	28	75	70	72	10
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	

TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5

TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1

TEST NUMBER: P906218

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.78	8.45	8.92	9.58	11.15	3.74	4.41	4.88	5.54	7.11
	3H	9.43	10.03	10.58	11.16	12.75	4.90	5.50	6.05	6.64	8.22
	4H	10.02	10.59	11.17	11.72	13.31	5.33	5.90	6.49	7.04	8.63
	6H	10.41	10.94	11.58	12.07	13.68	5.63	6.15	6.79	7.29	8.89
	8H	10.53	11.02	11.69	12.18	13.77	5.71	6.20	6.87	7.36	8.95
	12H	10.58	11.05	11.75	12.19	13.81	5.74	6.21	6.91	7.35	8.97
4H	2H	7.78	8.34	8.94	9.48	11.07	4.31	4.88	5.47	6.01	7.61
	3H	9.57	10.04	10.74	11.20	12.81	5.62	6.10	6.79	7.26	8.86
	4H	10.24	10.67	11.41	11.82	13.45	6.15	6.58	7.32	7.73	9.36
	6H	10.73	11.10	11.90	12.27	13.89	6.54	6.91	7.72	8.08	9.70
	8H	10.89	11.23	12.06	12.40	14.03	6.65	7.00	7.83	8.17	9.80
	12H	10.96	11.28	12.15	12.45	14.09	6.70	7.02	7.89	8.19	9.83
8H	4H	10.19	10.54	11.36	11.70	13.33	6.41	6.75	7.58	7.92	9.55
	6H	10.73	11.02	11.92	12.22	13.85	6.89	7.18	8.09	8.39	10.01
	8H	10.93	11.18	12.13	12.36	14.01	7.07	7.32	8.27	8.50	10.15
	12H	11.05	11.27	12.25	12.45	14.13	7.17	7.39	8.37	8.57	10.25
12H	4H	10.13	10.45	11.32	11.62	13.26	6.40	6.71	7.59	7.89	9.52
	6H	10.70	10.95	11.90	12.14	13.78	6.94	7.19	8.14	8.37	10.02
	8H	10.90	11.12	12.10	12.30	13.98	7.12	7.34	8.33	8.52	10.20