

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906279

Luminaire Tested: DFN2DIP-SQ2F0-060D050US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906279
REPORT IS A COMBINATION OF REPORTS P901322 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-060D050US835-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10050.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906279
CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906279

CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	45	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	26	23	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5453	5453	5453
5°	5452	5354	5393
10°	5389	5238	5210
15°	5305	5053	4932
20°	5197	4803	4593
25°	5087	4526	4266
30°	4943	4242	3854
35°	4800	3939	3492
40°	4655	3625	3078
45°	4487	3280	2704
50°	4313	2932	2339
55°	4129	2562	1988
60°	3917	2177	1629
65°	3673	1787	1458
70°	3375	1423	1308
75°	3002	1231	1175
80°	2464	1000	996
85°	1604	621	709

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4487 cd/sqm



TEST NUMBER: P906279

CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	2.3
10°-20°	638.0	6.3
20°-30°	895.7	8.9
30°-40°	976.4	9.7
40°-50°	897.4	8.9
50°-60°	704.8	7.0
60°-70°	458.8	4.6
70°-80°	236.1	2.3
80°-90°	63.3	0.6
90°-100°	55.7	0.6
100°-110°	207.4	2.1
110°-120°	550.1	5.5
120°-130°	912.4	9.1
130°-140°	969.2	9.6
140°-150°	900.8	9.0
150°-160°	724.2	7.2
160°-170°	466.6	4.6
170°-180°	160.6	1.6
0°-30°	1766.2	17.6
0°-40°	2742.6	27.3
0°-60°	4344.8	43.2
0°-90°	5103.0	50.8
90°-120°	813.2	8.1
90°-150°	3595.6	35.8
90°-180°	4947.0	49.2
0°-180°	10050.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	111
90°	1	15	24	31	33	9
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P906279

CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P906279

CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P906279
 CATALOG NUMBER: DFN2DIP-SQ2F0-060D050US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.00	13.83	13.95	14.80	16.06	8.96	9.79	9.92	10.76	12.03
	3H	14.66	15.40	15.62	16.38	17.67	10.13	10.88	11.10	11.85	13.14
	4H	15.25	15.96	16.23	16.94	18.23	10.57	11.27	11.55	12.25	13.55
	6H	15.66	16.31	16.65	17.29	18.60	10.87	11.52	11.87	12.51	13.82
	8H	15.78	16.39	16.78	17.40	18.70	10.95	11.57	11.95	12.58	13.88
	12H	15.83	16.42	16.83	17.41	18.74	10.99	11.58	11.99	12.57	13.90
4H	2H	13.01	13.72	14.00	14.70	15.99	9.54	10.25	10.53	11.23	12.53
	3H	14.82	15.41	15.82	16.42	17.72	10.87	11.46	11.87	12.47	13.78
	4H	15.50	16.03	16.50	17.04	18.37	11.41	11.94	12.41	12.95	14.28
	6H	15.99	16.45	17.01	17.48	18.81	11.81	12.27	12.82	13.29	14.62
	8H	16.16	16.59	17.17	17.61	18.95	11.92	12.36	12.94	13.37	14.72
	12H	16.24	16.63	17.28	17.67	19.01	11.98	12.37	13.02	13.40	14.75
8H	4H	15.46	15.89	16.48	16.91	18.25	11.68	12.11	12.69	13.13	14.47
	6H	16.00	16.36	17.05	17.42	18.76	12.17	12.52	13.21	13.59	14.93
	8H	16.21	16.52	17.26	17.57	18.93	12.35	12.66	13.40	13.71	15.07
	12H	16.33	16.61	17.39	17.65	19.05	12.45	12.73	13.50	13.77	15.17
12H	4H	15.41	15.80	16.45	16.83	18.18	11.68	12.07	12.71	13.10	14.45
	6H	15.98	16.29	17.03	17.34	18.70	12.21	12.53	13.26	13.57	14.93
	8H	16.18	16.46	17.24	17.50	18.90	12.41	12.68	13.46	13.72	15.13