

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922278

Luminaire Tested: DFN2DIP-PN4F0-050D040US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922278  
REPORT IS A COMBINATION OF REPORTS P899612 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-050D040US940-RLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6946.5 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 74.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922278  
CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P922278

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	60	60	60	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	43	41	39	35
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	27	24	21	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1345	1345	1345
5°	1347	1324	1332
10°	1334	1298	1289
15°	1316	1255	1223
20°	1291	1196	1141
25°	1266	1130	1061
30°	1233	1063	961
35°	1200	990	872
40°	1167	914	771
45°	1128	830	679
50°	1088	746	589
55°	1046	655	503
60°	998	561	414
65°	942	465	373
70°	875	375	338
75°	790	331	308
80°	668	278	268
85°	465	187	203

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1128 cd/sqm



TEST NUMBER: P922278

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.7	2.5
10°-20°	474.1	6.8
20°-30°	665.6	9.6
30°-40°	725.6	10.4
40°-50°	666.9	9.6
50°-60°	523.7	7.5
60°-70°	340.9	4.9
70°-80°	175.5	2.5
80°-90°	48.0	0.7
90°-100°	69.8	1.0
100°-110°	221.8	3.2
110°-120°	379.5	5.5
120°-130°	499.2	7.2
130°-140°	560.3	8.1
140°-150°	549.4	7.9
150°-160°	460.9	6.6
160°-170°	305.7	4.4
170°-180°	106.8	1.5
0°-30°	1312.4	18.9
0°-40°	2038.0	29.3
0°-60°	3228.6	46.5
0°-90°	3793.0	54.6
90°-120°	671.2	9.7
90°-150°	2280.1	32.8
90°-180°	3153.0	45.4
0°-180°	6946.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	1	12	33	31	32	7
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P922278

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2



TEST NUMBER: P922278

CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0



TEST NUMBER: P922278  
 CATALOG NUMBER: DFN2DIP-PN4F0-050D040US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.47	9.53	10.41	11.62	4.57	5.44	5.49	6.37	7.58
	3H	10.29	11.06	11.22	12.01	13.24	5.76	6.54	6.70	7.48	8.71
	4H	10.90	11.63	11.85	12.58	13.82	6.21	6.95	7.16	7.90	9.14
	6H	11.32	12.00	12.29	12.96	14.21	6.54	7.21	7.50	8.17	9.42
	8H	11.45	12.10	12.42	13.07	14.32	6.63	7.27	7.60	8.24	9.49
	12H	11.52	12.13	12.49	13.10	14.37	6.67	7.29	7.65	8.25	9.53
4H	2H	8.63	9.36	9.58	10.31	11.55	5.17	5.90	6.13	6.86	8.10
	3H	10.46	11.07	11.43	12.05	13.31	6.52	7.13	7.49	8.12	9.37
	4H	11.16	11.71	12.13	12.69	13.97	7.07	7.63	8.05	8.61	9.88
	6H	11.68	12.16	12.66	13.15	14.43	7.50	7.98	8.48	8.97	10.25
	8H	11.86	12.30	12.84	13.29	14.59	7.63	8.07	8.61	9.07	10.36
	12H	11.95	12.36	12.96	13.36	14.66	7.69	8.10	8.70	9.11	10.40
8H	4H	11.13	11.58	12.12	12.57	13.86	7.36	7.81	8.35	8.80	10.09
	6H	11.70	12.07	12.71	13.10	14.39	7.88	8.25	8.89	9.28	10.57
	8H	11.92	12.24	12.94	13.26	14.57	8.07	8.40	9.09	9.42	10.73
	12H	12.06	12.35	13.08	13.36	14.71	8.19	8.48	9.22	9.49	10.85
12H	4H	11.08	11.48	12.09	12.49	13.79	7.37	7.77	8.37	8.78	10.07
	6H	11.67	12.00	12.70	13.02	14.33	7.93	8.26	8.95	9.28	10.58
	8H	11.90	12.19	12.92	13.20	14.55	8.14	8.43	9.17	9.44	10.80