

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906325

Luminaire Tested: DFN2DIP-SQ2F0-080D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906325
REPORT IS A COMBINATION OF REPORTS P901325 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D050US835-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12870.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56	56	56	52
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48	48	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	35	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	30	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	27	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	24	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	21	21	19
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19	19	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6845	6845	6845
5°	6844	6735	6785
10°	6777	6629	6684
15°	6665	6505	6531
20°	6519	6339	6374
25°	6373	6143	6195
30°	6192	5959	5970
35°	6021	5745	5732
40°	5812	5528	5505
45°	5602	5310	5272
50°	5373	5081	5004
55°	5131	4816	4754
60°	4858	4504	4468
65°	4558	4178	4132
70°	4177	3781	3767
75°	3654	3305	3417
80°	3019	2698	2775
85°	2039	1704	1743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5602 cd/sqm

TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	2.3
10°-20°	824.3	6.4
20°-30°	1211.5	9.4
30°-40°	1407.0	10.9
40°-50°	1405.3	10.9
50°-60°	1225.4	9.5
60°-70°	905.8	7.0
70°-80°	512.5	4.0
80°-90°	138.2	1.1
90°-100°	55.7	0.4
100°-110°	207.4	1.6
110°-120°	550.1	4.3
120°-130°	912.4	7.1
130°-140°	969.2	7.5
140°-150°	900.8	7.0
150°-160°	724.2	5.6
160°-170°	466.6	3.6
170°-180°	160.6	1.2
0°-30°	2328.8	18.1
0°-40°	3735.8	29.0
0°-60°	6366.4	49.5
0°-90°	7923.0	61.6
90°-120°	813.2	6.3
90°-150°	3595.6	27.9
90°-180°	4947.0	38.4
0°-180°	12870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	1	15	24	31	33	12
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P906325

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.84	15.82	15.69	16.69	17.79	14.40	15.37	15.25	16.25	17.34
	3H	16.49	17.37	17.36	18.25	19.37	16.00	16.88	16.87	17.76	18.88
	4H	17.07	17.90	17.95	18.79	19.92	16.58	17.41	17.46	18.30	19.43
	6H	17.46	18.23	18.35	19.12	20.27	16.96	17.73	17.86	18.62	19.77
	8H	17.56	18.29	18.46	19.20	20.35	17.06	17.79	17.96	18.70	19.85
	12H	17.61	18.30	18.51	19.21	20.38	17.10	17.79	18.01	18.70	19.87
4H	2H	15.31	16.14	16.19	17.02	18.16	14.95	15.78	15.84	16.67	17.80
	3H	17.16	17.85	18.06	18.77	19.92	16.75	17.44	17.65	18.36	19.51
	4H	17.86	18.49	18.77	19.41	20.58	17.44	18.07	18.35	18.99	20.16
	6H	18.37	18.91	19.29	19.85	21.03	17.93	18.48	18.86	19.42	20.59
	8H	18.51	19.02	19.43	19.95	21.14	18.07	18.58	19.00	19.52	20.70
	12H	18.58	19.04	19.52	19.99	21.19	18.13	18.59	19.07	19.54	20.74
8H	4H	18.06	18.57	18.98	19.50	20.69	17.68	18.19	18.60	19.12	20.31
	6H	18.67	19.09	19.62	20.07	21.26	18.29	18.71	19.24	19.68	20.87
	8H	18.88	19.25	19.84	20.22	21.42	18.49	18.86	19.45	19.82	21.03
	12H	19.00	19.33	19.97	20.29	21.54	18.59	18.92	19.56	19.88	21.13
12H	4H	18.05	18.51	18.99	19.46	20.65	17.68	18.14	18.62	19.09	20.28
	6H	18.70	19.07	19.66	20.04	21.24	18.32	18.70	19.28	19.66	20.87
	8H	18.93	19.26	19.89	20.22	21.47	18.55	18.87	19.51	19.83	21.09