

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922346

Luminaire Tested: DFN2DIP-PN4F0-060D120US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922346
REPORT IS A COMBINATION OF REPORTS P899758 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-060D120US940-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14017.7 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 158.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1614	1614	1614
5°	1617	1589	1599
10°	1601	1558	1547
15°	1579	1506	1467
20°	1549	1436	1369
25°	1520	1356	1274
30°	1480	1275	1153
35°	1440	1187	1047
40°	1400	1097	925
45°	1354	996	815
50°	1306	895	707
55°	1256	786	604
60°	1198	673	497
65°	1131	557	448
70°	1050	450	406
75°	949	397	370
80°	801	333	322
85°	558	224	244

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2649 cd/sqm

TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.2	1.5
10°-20°	568.9	4.1
20°-30°	798.7	5.7
30°-40°	870.7	6.2
40°-50°	800.3	5.7
50°-60°	628.5	4.5
60°-70°	409.1	2.9
70°-80°	210.6	1.5
80°-90°	63.4	0.5
90°-100°	209.4	1.5
100°-110°	665.4	4.7
110°-120°	1138.7	8.1
120°-130°	1497.5	10.7
130°-140°	1680.9	12.0
140°-150°	1648.3	11.8
150°-160°	1382.7	9.9
160°-170°	917.0	6.5
170°-180°	320.5	2.3
0°-30°	1574.9	11.2
0°-40°	2445.6	17.4
0°-60°	3874.3	27.6
0°-90°	4557.3	32.5
90°-120°	2013.4	14.4
90°-150°	6840.1	48.8
90°-180°	9460.0	67.5
0°-180°	14017.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2211	2211	2211	2211	2211	
5°	2211	2201	2175	2193	2187	210
15°	2103	2081	2013	1975	1955	593
25°	1909	1845	1713	1631	1601	878
35°	1645	1543	1367	1241	1197	1030
45°	1345	1211	1001	858	810	1039
55°	1022	866	650	530	492	914
65°	690	528	348	280	274	685
75°	368	228	160	146	144	389
85°	86	44	38	38	38	99
90°	3	37	100	94	97	14
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2211.3	2211.3	2211.3	2211.3	2211.3
2.5°	2221.3	2211.3	2189.1	2209.3	2205.3
5°	2211.3	2201.3	2175.1	2193.3	2187.3
7.5°	2193.3	2181.3	2153.3	2161.1	2151.2
10°	2169.2	2155.2	2115.3	2109.2	2097.2
12.5°	2139.3	2121.2	2067.1	2055.2	2033.1
15°	2103.2	2081.1	2013.1	1975.1	1955.2
17.5°	2061.2	2029.1	1945.0	1901.0	1869.0
20°	2013.1	1973.0	1873.0	1823.1	1779.0
22.5°	1961.1	1915.0	1798.9	1731.0	1701.0
25°	1909.2	1845.0	1713.0	1631.0	1600.9
27.5°	1847.2	1779.0	1632.9	1538.8	1492.8
30°	1781.1	1704.9	1544.8	1442.9	1388.7
32.5°	1717.0	1624.9	1461.0	1340.8	1290.7
35°	1645.0	1542.9	1366.9	1240.7	1196.6
37.5°	1574.9	1464.7	1278.8	1140.6	1090.7
40°	1500.8	1380.9	1186.6	1044.5	992.6
42.5°	1424.9	1296.8	1094.7	946.5	896.6
45°	1344.8	1210.6	1000.7	858.4	810.4
47.5°	1268.8	1126.8	910.6	768.4	724.4
50°	1184.7	1042.7	822.5	684.3	642.5
52.5°	1102.5	952.4	738.4	606.4	568.4
55°	1022.5	866.5	650.3	530.4	492.3
57.5°	940.6	780.4	572.4	460.3	428.2
60°	856.5	696.4	490.3	388.3	356.2
62.5°	774.5	614.5	420.2	324.2	308.3
65°	690.5	528.2	348.2	280.3	274.1
67.5°	610.4	448.2	280.3	246.1	240.1
70°	526.3	370.2	232.0	212.1	204.0
72.5°	446.3	298.1	194.0	178.2	174.1
75°	368.2	228.0	160.1	146.1	144.2
77.5°	290.3	162.0	126.1	118.1	114.0
80°	218.0	116.1	95.9	88.1	88.1
82.5°	152.0	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5

TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P922346

CATALOG NUMBER: DFN2DIP-PN4F0-060D120US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.92	7.62	8.02	8.71	10.22	2.88	3.59	3.98	4.68	6.18
	3H	8.59	9.22	9.69	10.32	11.84	4.06	4.69	5.17	5.79	7.31
	4H	9.19	9.79	10.31	10.89	12.42	4.51	5.10	5.62	6.21	7.73
	6H	9.61	10.16	10.74	11.26	12.80	4.82	5.37	5.95	6.48	8.01
	8H	9.73	10.26	10.86	11.38	12.91	4.91	5.43	6.04	6.55	8.08
	12H	9.79	10.29	10.93	11.40	12.96	4.95	5.45	6.08	6.56	8.11
4H	2H	6.92	7.52	8.04	8.62	10.15	3.46	4.06	4.59	5.16	6.69
	3H	8.74	9.24	9.87	10.37	11.90	4.80	5.30	5.93	6.43	7.97
	4H	9.43	9.89	10.56	11.00	12.56	5.35	5.80	6.48	6.92	8.48
	6H	9.94	10.33	11.08	11.47	13.02	5.76	6.15	6.90	7.29	8.84
	8H	10.11	10.48	11.25	11.61	13.18	5.89	6.25	7.03	7.38	8.95
	12H	10.21	10.54	11.36	11.68	13.25	5.95	6.28	7.10	7.42	8.99
8H	4H	9.39	9.75	10.53	10.89	12.45	5.62	5.98	6.76	7.12	8.68
	6H	9.95	10.25	11.11	11.43	12.99	6.13	6.44	7.29	7.61	9.17
	8H	10.17	10.43	11.34	11.59	13.17	6.33	6.59	7.49	7.74	9.33
	12H	10.31	10.54	11.48	11.69	13.31	6.44	6.67	7.61	7.82	9.44
12H	4H	9.33	9.66	10.49	10.81	12.38	5.62	5.95	6.77	7.09	8.66
	6H	9.93	10.19	11.09	11.35	12.93	6.18	6.45	7.35	7.60	9.18
	8H	10.14	10.38	11.31	11.53	13.14	6.39	6.62	7.56	7.77	9.39

END OF REPORT