

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922410

Luminaire Tested: DFN2DIP-PN4F0-080D100US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922410
REPORT IS A COMBINATION OF REPORTS P899726 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D100US940-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13955.3 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 152.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2152	2152	2152
5°	2156	2118	2132
10°	2134	2077	2063
15°	2105	2009	1956
20°	2066	1914	1825
25°	2026	1808	1698
30°	1973	1700	1537
35°	1920	1583	1396
40°	1867	1462	1233
45°	1805	1328	1087
50°	1741	1193	943
55°	1674	1048	805
60°	1597	897	663
65°	1508	743	597
70°	1400	600	541
75°	1265	529	493
80°	1068	445	429
85°	745	298	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2209 cd/sqm

TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.3	2.0
10°-20°	758.6	5.4
20°-30°	1065.0	7.6
30°-40°	1160.9	8.3
40°-50°	1067.0	7.6
50°-60°	838.0	6.0
60°-70°	545.4	3.9
70°-80°	280.8	2.0
80°-90°	79.7	0.6
90°-100°	174.5	1.3
100°-110°	554.5	4.0
110°-120°	948.9	6.8
120°-130°	1247.9	8.9
130°-140°	1400.8	10.0
140°-150°	1373.6	9.8
150°-160°	1152.3	8.3
160°-170°	764.1	5.5
170°-180°	267.1	1.9
0°-30°	2099.9	15.0
0°-40°	3260.8	23.4
0°-60°	5165.8	37.0
0°-90°	6071.7	43.5
90°-120°	1677.9	12.0
90°-150°	5700.1	40.8
90°-180°	7884.0	56.5
0°-180°	13955.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	3	31	83	78	81	14
95°	124	148	152	152	148	138
105°	512	519	524	528	528	540
115°	952	966	962	959	952	942
125°	1385	1406	1400	1392	1389	1238
135°	1791	1818	1823	1820	1814	1385
145°	2175	2192	2206	2208	2199	1359
155°	2487	2494	2501	2513	2506	1145
165°	2705	2703	2703	2720	2708	763
175°	2815	2808	2803	2820	2806	267
180°	2820	2820	2820	2820	2820	

TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	2.6	30.6	83.3	78.2	80.8
92.5°	52.7	71.4	74.0	76.5	76.5
95°	124.1	147.9	152.2	152.2	147.9
97.5°	206.6	228.7	238.1	238.1	238.1
100°	301.8	321.4	328.1	328.1	325.7
102.5°	402.2	416.6	426.0	428.5	426.0
105°	511.8	518.6	523.7	528.0	528.0
107.5°	620.6	630.9	630.9	632.6	620.6
110°	726.1	739.7	739.7	739.7	732.9

TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	840.0	854.4	851.9	845.1	840.0
115°	952.3	965.8	961.6	959.0	952.3
117.5°	1063.6	1082.4	1070.4	1063.6	1056.8
120°	1175.8	1194.5	1175.8	1175.8	1168.2
122.5°	1277.8	1301.6	1289.8	1283.0	1277.8
125°	1385.0	1406.2	1399.5	1391.8	1389.3
127.5°	1489.6	1515.9	1506.5	1496.4	1489.6
130°	1587.3	1617.9	1613.7	1608.6	1599.3
132.5°	1697.0	1720.8	1722.5	1710.7	1703.8
135°	1791.4	1817.8	1822.8	1820.3	1813.5
137.5°	1896.8	1918.1	1922.3	1920.7	1910.4
140°	1989.5	2010.7	2022.7	2022.7	2013.3
142.5°	2084.7	2106.0	2112.7	2115.3	2106.0
145°	2174.8	2191.8	2205.5	2208.0	2198.6
147.5°	2255.6	2276.9	2287.1	2291.3	2282.0
150°	2339.0	2353.4	2362.8	2370.3	2362.8
152.5°	2412.9	2427.3	2439.3	2448.6	2439.3
155°	2486.9	2493.7	2501.3	2513.2	2505.5
157.5°	2550.6	2555.7	2560.0	2577.0	2565.1
160°	2607.6	2612.7	2615.2	2629.7	2619.5
162.5°	2660.3	2660.3	2662.8	2679.0	2667.1
165°	2705.4	2702.8	2702.8	2719.8	2707.9
167.5°	2746.2	2738.5	2738.5	2755.6	2743.6
170°	2776.8	2770.0	2767.4	2784.5	2770.0
172.5°	2798.0	2791.2	2788.6	2805.7	2791.2
175°	2815.0	2808.3	2803.2	2820.1	2805.7
177.5°	2824.4	2817.6	2812.5	2826.9	2812.5
180°	2820.1	2820.1	2820.1	2820.1	2820.1

TEST NUMBER: P922410

CATALOG NUMBER: DFN2DIP-PN4F0-080D100US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.18	9.96	10.19	10.98	12.34	5.14	5.92	6.16	6.94	8.31
	3H	10.85	11.55	11.88	12.58	13.97	6.33	7.03	7.36	8.06	9.44
	4H	11.46	12.12	12.50	13.16	14.55	6.78	7.44	7.82	8.47	9.86
	6H	11.88	12.49	12.93	13.53	14.93	7.10	7.70	8.15	8.74	10.14
	8H	12.01	12.59	13.06	13.64	15.04	7.19	7.76	8.24	8.82	10.22
	12H	12.07	12.62	13.13	13.67	15.09	7.23	7.78	8.29	8.82	10.25
4H	2H	9.19	9.85	10.24	10.88	12.27	5.73	6.39	6.78	7.43	8.82
	3H	11.02	11.57	12.07	12.63	14.03	7.08	7.63	8.13	8.69	10.09
	4H	11.71	12.21	12.77	13.26	14.69	7.63	8.13	8.69	9.18	10.61
	6H	12.22	12.66	13.29	13.73	15.15	8.04	8.47	9.11	9.55	10.97
	8H	12.40	12.80	13.47	13.87	15.31	8.17	8.57	9.24	9.64	11.08
	12H	12.50	12.86	13.58	13.94	15.38	8.24	8.60	9.32	9.68	11.12
8H	4H	11.67	12.08	12.74	13.14	14.58	7.90	8.31	8.97	9.38	10.81
	6H	12.24	12.57	13.33	13.68	15.12	8.42	8.75	9.51	9.86	11.30
	8H	12.46	12.75	13.56	13.84	15.30	8.61	8.91	9.71	10.00	11.45
	12H	12.60	12.85	13.70	13.94	15.44	8.73	8.99	9.83	10.08	11.57
12H	4H	11.62	11.99	12.71	13.07	14.51	7.91	8.27	8.99	9.35	10.80
	6H	12.22	12.51	13.32	13.60	15.05	8.47	8.76	9.57	9.86	11.31
	8H	12.44	12.69	13.54	13.78	15.28	8.68	8.94	9.78	10.03	11.52