

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908941

Luminaire Tested: DFN2DIP-SQ2F0-030D070US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908941
REPORT IS A COMBINATION OF REPORTS P901339 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D070US840-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9997.7 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2592	2592	2592
5°	2592	2550	2569
10°	2566	2510	2531
15°	2524	2464	2473
20°	2469	2400	2414
25°	2413	2326	2346
30°	2345	2257	2261
35°	2280	2176	2171
40°	2201	2094	2085
45°	2122	2011	1997
50°	2035	1924	1895
55°	1944	1824	1801
60°	1840	1706	1693
65°	1727	1582	1565
70°	1582	1432	1426
75°	1384	1252	1294
80°	1143	1021	1051
85°	774	644	660

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2267 cd/sqm

TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.1
10°-20°	312.2	3.1
20°-30°	458.8	4.6
30°-40°	532.8	5.3
40°-50°	532.2	5.3
50°-60°	464.1	4.6
60°-70°	343.1	3.4
70°-80°	194.1	1.9
80°-90°	55.4	0.6
90°-100°	78.7	0.8
100°-110°	293.3	2.9
110°-120°	777.8	7.8
120°-130°	1290.0	12.9
130°-140°	1370.3	13.7
140°-150°	1273.5	12.7
150°-160°	1023.9	10.2
160°-170°	659.7	6.6
170°-180°	227.1	2.3
0°-30°	881.9	8.8
0°-40°	1414.7	14.2
0°-60°	2411.0	24.1
0°-90°	3003.5	30.0
90°-120°	1149.7	11.5
90°-150°	5083.5	50.8
90°-180°	6994.0	70.0
0°-180°	9997.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	2	21	34	43	47	9
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P908941

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.26	8.96	9.37	10.07	11.60	7.81	8.52	8.93	9.63	11.16
	3H	9.89	10.52	11.01	11.64	13.18	9.40	10.03	10.52	11.15	12.69
	4H	10.46	11.06	11.58	12.17	13.72	9.96	10.56	11.09	11.68	13.23
	6H	10.83	11.38	11.97	12.50	14.07	10.33	10.89	11.47	12.00	13.57
	8H	10.92	11.45	12.07	12.58	14.14	10.42	10.95	11.56	12.08	13.64
	12H	10.96	11.46	12.11	12.59	14.17	10.45	10.95	11.60	12.08	13.66
4H	2H	8.69	9.29	9.83	10.41	11.96	8.33	8.93	9.47	10.05	11.60
	3H	10.52	11.02	11.66	12.16	13.73	10.11	10.61	11.25	11.75	13.32
	4H	11.21	11.67	12.36	12.80	14.39	10.79	11.25	11.93	12.38	13.96
	6H	11.70	12.09	12.85	13.25	14.82	11.27	11.66	12.42	12.82	14.39
	8H	11.83	12.20	12.99	13.35	14.94	11.40	11.77	12.55	12.91	14.50
	12H	11.89	12.23	13.06	13.38	14.98	11.44	11.78	12.61	12.93	14.53
8H	4H	11.38	11.75	12.53	12.90	14.49	11.00	11.37	12.16	12.52	14.11
	6H	11.98	12.29	13.16	13.48	15.06	11.60	11.90	12.77	13.09	14.68
	8H	12.19	12.46	13.37	13.62	15.23	11.80	12.06	12.97	13.23	14.84
	12H	12.30	12.53	13.48	13.70	15.34	11.89	12.12	13.07	13.29	14.93
12H	4H	11.36	11.69	12.53	12.85	14.45	10.99	11.32	12.16	12.48	14.08
	6H	12.01	12.27	13.18	13.44	15.05	11.63	11.90	12.81	13.07	14.67
	8H	12.23	12.46	13.41	13.62	15.27	11.84	12.08	13.03	13.24	14.88

END OF REPORT