

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922475

Luminaire Tested: DFN2DIP-PN4F0-100D080US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922475
REPORT IS A COMBINATION OF REPORTS P901214 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D080US940-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14641.9 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 158.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52	52	52
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50	45	45	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38	38	38
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33	33	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29	29	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25	25	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22	22	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20	20	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18	18	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16	16	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2690	2690	2690
5°	2694	2648	2665
10°	2668	2596	2579
15°	2631	2511	2445
20°	2582	2393	2281
25°	2533	2261	2123
30°	2466	2125	1921
35°	2400	1979	1745
40°	2334	1828	1542
45°	2256	1661	1358
50°	2176	1491	1179
55°	2093	1310	1006
60°	1996	1121	829
65°	1885	929	746
70°	1750	749	676
75°	1581	662	616
80°	1335	556	536
85°	930	373	406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2256 cd/sqm

TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.4
10°-20°	948.2	6.5
20°-30°	1331.2	9.1
30°-40°	1451.1	9.9
40°-50°	1333.8	9.1
50°-60°	1047.4	7.2
60°-70°	681.8	4.7
70°-80°	351.0	2.4
80°-90°	93.8	0.6
90°-100°	79.4	0.5
100°-110°	295.9	2.0
110°-120°	784.9	5.4
120°-130°	1301.8	8.9
130°-140°	1382.8	9.4
140°-150°	1285.1	8.8
150°-160°	1033.2	7.1
160°-170°	665.8	4.5
170°-180°	229.2	1.6
0°-30°	2624.8	17.9
0°-40°	4076.0	27.8
0°-60°	6457.2	44.1
0°-90°	7583.8	51.8
90°-120°	1160.2	7.9
90°-150°	5129.9	35.0
90°-180°	7058.0	48.2
0°-180°	14641.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	2	21	35	44	47	14
95°	113	56	68	77	75	134
105°	530	582	106	125	132	566
115°	1002	1031	1075	268	143	986
125°	1416	1439	1472	1484	1489	1263
135°	1753	1780	1796	1814	1810	1354
145°	2033	2031	2061	2073	2064	1272
155°	2238	2223	2244	2254	2240	1032
165°	2359	2348	2354	2366	2354	666
175°	2413	2400	2404	2416	2399	230
180°	2408	2408	2408	2408	2408	

TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	1.7	20.9	34.8	43.6	47.0
92.5°	43.6	36.6	41.8	45.3	47.0
95°	113.2	55.6	67.9	76.8	74.9
97.5°	203.8	61.0	88.7	94.2	95.8
100°	308.4	69.7	99.3	113.2	116.6
102.5°	423.3	419.9	102.8	121.8	127.2
105°	529.6	581.9	106.3	125.4	132.4
107.5°	653.3	696.7	109.9	128.9	135.9
110°	771.9	808.2	305.0	130.7	137.6



TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	883.3	914.5	885.0	134.0	139.5
115°	1001.7	1031.3	1074.9	268.3	142.9
117.5°	1104.5	1139.2	1169.0	919.7	463.4
120°	1219.5	1245.5	1277.0	1297.9	1062.7
122.5°	1316.9	1344.9	1379.8	1390.2	1392.0
125°	1416.2	1439.0	1472.0	1484.3	1489.4
127.5°	1506.8	1531.2	1557.6	1574.8	1576.5
130°	1592.2	1620.1	1639.2	1658.5	1656.8
132.5°	1679.4	1702.1	1721.2	1736.9	1735.2
135°	1752.6	1780.5	1796.0	1813.6	1810.1
137.5°	1829.2	1850.0	1867.6	1885.0	1879.8
140°	1904.0	1918.1	1937.2	1952.8	1944.1
142.5°	1966.9	1979.1	2001.6	2015.5	2006.8
145°	2033.1	2031.2	2060.8	2073.0	2064.3
147.5°	2090.4	2085.3	2114.8	2123.5	2116.7
150°	2146.3	2134.0	2162.0	2172.3	2163.6
152.5°	2193.3	2179.3	2205.4	2216.0	2203.8
155°	2238.5	2223.0	2243.9	2254.2	2240.4
157.5°	2275.1	2261.3	2277.0	2289.2	2275.1
160°	2306.6	2296.1	2306.6	2316.9	2304.7
162.5°	2334.3	2324.0	2332.6	2344.8	2329.1
165°	2358.8	2348.4	2353.6	2365.7	2353.6
167.5°	2377.9	2367.4	2372.8	2385.0	2369.3
170°	2393.7	2383.1	2386.7	2398.9	2383.1
172.5°	2404.1	2393.7	2397.2	2409.4	2393.7
175°	2412.7	2400.5	2404.1	2416.2	2398.9
177.5°	2416.2	2404.1	2405.8	2418.1	2402.4
180°	2407.5	2407.5	2407.5	2407.5	2407.5

TEST NUMBER: P922475

CATALOG NUMBER: DFN2DIP-PN4F0-100D080US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.76	11.60	11.71	12.56	13.81	6.72	7.57	7.67	8.53	9.78
	3H	12.44	13.20	13.40	14.17	15.44	7.91	8.67	8.87	9.64	10.91
	4H	13.05	13.77	14.03	14.74	16.02	8.37	9.08	9.34	10.05	11.33
	6H	13.48	14.13	14.46	15.11	16.40	8.69	9.35	9.67	10.32	11.62
	8H	13.60	14.23	14.60	15.22	16.51	8.78	9.40	9.77	10.40	11.69
	12H	13.67	14.26	14.66	15.25	16.56	8.82	9.42	9.82	10.41	11.72
4H	2H	10.78	11.49	11.76	12.47	13.75	7.32	8.04	8.30	9.01	10.29
	3H	12.61	13.21	13.60	14.21	15.50	8.67	9.27	9.66	10.27	11.56
	4H	13.31	13.85	14.30	14.85	16.16	9.22	9.77	10.22	10.76	12.08
	6H	13.83	14.29	14.84	15.31	16.63	9.65	10.11	10.65	11.13	12.45
	8H	14.00	14.44	15.01	15.45	16.78	9.78	10.21	10.79	11.22	12.55
	12H	14.10	14.49	15.13	15.52	16.86	9.84	10.23	10.87	11.26	12.60
8H	4H	13.28	13.71	14.29	14.72	16.05	9.51	9.94	10.52	10.95	12.28
	6H	13.85	14.21	14.88	15.26	16.59	10.03	10.39	11.06	11.44	12.77
	8H	14.07	14.38	15.11	15.42	16.77	10.22	10.54	11.26	11.58	12.92
	12H	14.21	14.48	15.25	15.52	16.91	10.34	10.62	11.39	11.65	13.04
12H	4H	13.23	13.62	14.26	14.65	15.98	9.51	9.91	10.54	10.93	12.27
	6H	13.82	14.14	14.86	15.18	16.53	10.08	10.39	11.12	11.43	12.78
	8H	14.05	14.32	15.09	15.36	16.75	10.29	10.57	11.33	11.60	12.99

END OF REPORT