

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911662

Luminaire Tested: DFN2DIP-SQ2F0-030D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911662
REPORT IS A COMBINATION OF REPORTS P899796 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D050US850-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7735.3 lumens
Efficiency: N/A
Efficacy: 127.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 60.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911662
CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P911662
 CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37			37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38	32			32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32	27			27
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	38	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	16	17	14	13	11			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3023	3023	3023
5°	3023	2969	2990
10°	2988	2904	2889
15°	2942	2802	2735
20°	2882	2663	2547
25°	2821	2510	2365
30°	2741	2352	2137
35°	2662	2184	1936
40°	2581	2010	1707
45°	2488	1819	1499
50°	2391	1626	1297
55°	2290	1420	1103
60°	2172	1207	904
65°	2036	991	809
70°	1872	789	726
75°	1664	683	651
80°	1367	555	552
85°	890	344	393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2488 cd/sqm



TEST NUMBER: P911662

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	1.7
10°-20°	353.8	4.6
20°-30°	496.7	6.4
30°-40°	541.4	7.0
40°-50°	497.6	6.4
50°-60°	390.8	5.1
60°-70°	254.4	3.3
70°-80°	130.9	1.7
80°-90°	38.4	0.5
90°-100°	108.5	1.4
100°-110°	344.8	4.5
110°-120°	590.1	7.6
120°-130°	776.0	10.0
130°-140°	871.0	11.3
140°-150°	854.2	11.0
150°-160°	716.5	9.3
160°-170°	475.2	6.1
170°-180°	166.1	2.1
0°-30°	979.3	12.7
0°-40°	1520.7	19.7
0°-60°	2409.2	31.1
0°-90°	2832.9	36.6
90°-120°	1043.4	13.5
90°-150°	3544.6	45.8
90°-180°	4902.0	63.4
0°-180°	7735.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	2	19	52	49	50	8
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P911662

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P911662

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P911662
 CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.48	10.21	10.55	11.28	12.73	5.44	6.17	6.51	7.24	8.69
	3H	11.13	11.78	12.21	12.86	14.33	6.60	7.26	7.68	8.33	9.80
	4H	11.72	12.34	12.81	13.42	14.90	7.04	7.66	8.13	8.73	10.21
	6H	12.12	12.69	13.22	13.77	15.26	7.34	7.91	8.43	8.99	10.48
	8H	12.24	12.78	13.34	13.88	15.36	7.41	7.96	8.52	9.05	10.54
	12H	12.29	12.80	13.39	13.89	15.40	7.45	7.96	8.55	9.05	10.56
4H	2H	9.48	10.10	10.58	11.18	12.66	6.01	6.63	7.11	7.71	9.19
	3H	11.28	11.79	12.38	12.90	14.39	7.33	7.85	8.44	8.95	10.44
	4H	11.95	12.42	13.06	13.52	15.03	7.86	8.33	8.97	9.43	10.94
	6H	12.44	12.85	13.56	13.97	15.47	8.26	8.66	9.37	9.78	11.28
	8H	12.60	12.98	13.72	14.09	15.61	8.37	8.75	9.49	9.86	11.38
	12H	12.68	13.03	13.82	14.15	15.67	8.42	8.76	9.55	9.89	11.41
8H	4H	11.91	12.29	13.02	13.40	14.92	8.12	8.50	9.24	9.61	11.13
	6H	12.45	12.76	13.58	13.91	15.43	8.61	8.93	9.75	10.08	11.59
	8H	12.65	12.92	13.79	14.06	15.59	8.79	9.06	9.93	10.20	11.73
	12H	12.77	13.01	13.92	14.14	15.71	8.89	9.13	10.04	10.26	11.83
12H	4H	11.85	12.20	12.99	13.32	14.84	8.12	8.46	9.25	9.58	11.11
	6H	12.42	12.69	13.56	13.83	15.36	8.66	8.93	9.80	10.06	11.60
	8H	12.62	12.86	13.77	13.99	15.56	8.85	9.09	9.99	10.22	11.79