

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911673

Luminaire Tested: DFN2DIP-SQ2F0-030D080US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911673
REPORT IS A COMBINATION OF REPORTS P901351 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US850-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12077.1 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2846	2846	2846
5°	2846	2801	2822
10°	2818	2757	2780
15°	2772	2705	2716
20°	2711	2636	2651
25°	2650	2555	2576
30°	2575	2478	2483
35°	2504	2389	2384
40°	2417	2299	2290
45°	2330	2209	2192
50°	2235	2113	2081
55°	2134	2003	1977
60°	2020	1873	1859
65°	1896	1737	1718
70°	1737	1573	1566
75°	1519	1375	1421
80°	1255	1122	1155
85°	848	709	725

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2841 cd/sqm

TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	1.0
10°-20°	342.8	2.8
20°-30°	503.8	4.2
30°-40°	585.2	4.8
40°-50°	584.4	4.8
50°-60°	509.6	4.2
60°-70°	376.7	3.1
70°-80°	213.1	1.8
80°-90°	61.5	0.5
90°-100°	98.7	0.8
100°-110°	368.1	3.0
110°-120°	976.2	8.1
120°-130°	1619.0	13.4
130°-140°	1719.8	14.2
140°-150°	1598.3	13.2
150°-160°	1285.0	10.6
160°-170°	828.0	6.9
170°-180°	285.0	2.4
0°-30°	968.5	8.0
0°-40°	1553.6	12.9
0°-60°	2647.7	21.9
0°-90°	3299.0	27.3
90°-120°	1442.9	11.9
90°-150°	6380.0	52.8
90°-180°	8778.0	72.7
0°-180°	12077.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	57
90°	2	26	43	54	58	11
95°	141	69	84	96	93	167
105°	659	724	132	156	165	704
115°	1246	1283	1337	334	178	1226
125°	1761	1790	1831	1846	1852	1571
135°	2180	2214	2234	2256	2251	1684
145°	2528	2526	2563	2578	2567	1581
155°	2784	2765	2791	2804	2786	1283
165°	2934	2921	2927	2942	2927	829
175°	3001	2985	2990	3005	2983	286
180°	2994	2994	2994	2994	2994	

TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	2.1	26.0	43.3	54.2	58.4
92.5°	54.2	45.6	52.0	56.3	58.4
95°	140.7	69.2	84.4	95.5	93.2
97.5°	253.4	75.9	110.3	117.1	119.1
100°	383.6	86.7	123.5	140.7	145.1
102.5°	526.4	522.2	127.9	151.5	158.3
105°	658.6	723.7	132.2	155.9	164.7
107.5°	812.5	866.5	136.6	160.3	169.0
110°	960.0	1005.2	379.3	162.6	171.1

TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1098.6	1137.4	1100.7	166.7	173.4
115°	1245.7	1282.6	1336.8	333.7	177.8
117.5°	1373.6	1416.9	1453.9	1143.8	576.3
120°	1516.7	1549.1	1588.2	1614.1	1321.6
122.5°	1637.8	1672.6	1716.1	1728.9	1731.3
125°	1761.3	1789.6	1830.7	1845.9	1852.4
127.5°	1874.0	1904.4	1937.1	1958.6	1960.7
130°	1980.2	2014.9	2038.7	2062.6	2060.5
132.5°	2088.6	2116.9	2140.6	2160.1	2158.0
135°	2179.6	2214.3	2233.6	2255.6	2251.2
137.5°	2274.9	2300.8	2322.7	2344.3	2337.9
140°	2367.9	2385.5	2409.2	2428.7	2417.8
142.5°	2446.2	2461.3	2489.4	2506.7	2495.8
145°	2528.5	2526.2	2563.0	2578.2	2567.3
147.5°	2599.8	2593.4	2630.1	2641.0	2632.4
150°	2669.3	2654.1	2688.8	2701.6	2690.9
152.5°	2727.7	2710.4	2742.8	2756.0	2740.8
155°	2784.0	2764.7	2790.7	2803.6	2786.4
157.5°	2829.5	2812.3	2831.8	2847.0	2829.5
160°	2868.7	2855.6	2868.7	2881.5	2866.3
162.5°	2903.1	2890.3	2901.0	2916.2	2896.7
165°	2933.5	2920.7	2927.1	2942.2	2927.1
167.5°	2957.4	2944.3	2950.9	2966.1	2946.6
170°	2977.0	2963.8	2968.2	2983.4	2963.8
172.5°	2989.9	2977.0	2981.3	2996.5	2977.0
175°	3000.6	2985.4	2989.9	3004.9	2983.4
177.5°	3004.9	2989.9	2992.1	3007.3	2987.8
180°	2994.2	2994.2	2994.2	2994.2	2994.2

TEST NUMBER: P911673

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.20	8.89	9.33	10.01	11.57	7.75	8.44	8.88	9.56	11.13
	3H	9.83	10.44	10.96	11.57	13.15	9.33	9.95	10.47	11.08	12.66
	4H	10.39	10.98	11.54	12.11	13.69	9.90	10.48	11.05	11.61	13.20
	6H	10.77	11.31	11.92	12.44	14.03	10.27	10.81	11.42	11.94	13.53
	8H	10.86	11.37	12.02	12.52	14.11	10.36	10.87	11.52	12.02	13.61
	12H	10.89	11.38	12.06	12.52	14.13	10.39	10.87	11.55	12.02	13.62
4H	2H	8.63	9.21	9.78	10.34	11.93	8.27	8.86	9.43	9.99	11.57
	3H	10.45	10.94	11.61	12.10	13.69	10.04	10.53	11.20	11.69	13.29
	4H	11.14	11.59	12.31	12.74	14.35	10.72	11.17	11.88	12.32	13.93
	6H	11.63	12.02	12.80	13.18	14.79	11.20	11.58	12.37	12.75	14.36
	8H	11.77	12.13	12.93	13.29	14.91	11.33	11.69	12.50	12.85	14.47
	12H	11.82	12.15	13.01	13.32	14.95	11.37	11.70	12.56	12.87	14.50
8H	4H	11.32	11.68	12.48	12.83	14.46	10.94	11.30	12.10	12.46	14.08
	6H	11.92	12.21	13.10	13.41	15.03	11.53	11.83	12.72	13.03	14.65
	8H	12.12	12.38	13.31	13.56	15.20	11.73	11.99	12.92	13.17	14.80
	12H	12.23	12.46	13.43	13.64	15.31	11.82	12.05	13.02	13.23	14.90
12H	4H	11.29	11.62	12.47	12.79	14.41	10.92	11.25	12.10	12.42	14.04
	6H	11.94	12.20	13.13	13.38	15.02	11.57	11.82	12.76	13.00	14.64
	8H	12.16	12.38	13.35	13.56	15.23	11.78	12.00	12.97	13.18	14.85