

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922556

Luminaire Tested: DFN2DIP-PN4F0-120D110US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922556
REPORT IS A COMBINATION OF REPORTS P899751 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-120D110US940-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19274.3 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 217.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	91	87		92	88	85	81		76	73	71		64	62	61		54	52	51
2	90	83	76	71		83	77	71	67		66	62	59		56	53	51		47	45	43
3	82	73	65	59		76	68	61	56		58	53	49		50	46	43		42	39	37
4	75	64	56	50		70	60	53	47		52	46	42		44	40	37		37	34	32
5	69	57	49	43		64	54	46	41		46	41	36		40	35	32		34	30	28
6	64	51	43	37		59	48	41	35		42	36	32		36	32	28		31	27	24
7	59	46	38	33		55	44	36	31		38	32	28		33	28	25		28	24	22
8	55	42	34	29		51	40	33	28		35	29	25		30	25	22		26	22	19
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	20	18
10	48	35	28	23		44	33	27	22		29	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3039	3039	3039
5°	3044	2997	3018
10°	3019	2957	2977
15°	2975	2909	2914
20°	2915	2842	2849
25°	2855	2761	2774
30°	2781	2686	2679
35°	2710	2598	2578
40°	2623	2509	2481
45°	2535	2419	2383
50°	2440	2326	2269
55°	2341	2217	2165
60°	2228	2088	2045
65°	2106	1955	1904
70°	1949	1792	1752
75°	1732	1598	1612
80°	1472	1350	1345
85°	1065	921	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2535 cd/sqm

TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.9	2.0
10°-20°	1102.6	5.7
20°-30°	1620.4	8.4
30°-40°	1882.0	9.8
40°-50°	1879.7	9.8
50°-60°	1639.0	8.5
60°-70°	1211.6	6.3
70°-80°	685.5	3.6
80°-90°	189.7	1.0
90°-100°	192.0	1.0
100°-110°	609.9	3.2
110°-120°	1043.8	5.4
120°-130°	1372.7	7.1
130°-140°	1540.8	8.0
140°-150°	1511.0	7.8
150°-160°	1267.5	6.6
160°-170°	840.6	4.4
170°-180°	293.8	1.5
0°-30°	3114.9	16.2
0°-40°	4996.9	25.9
0°-60°	8515.5	44.2
0°-90°	10602.3	55.0
90°-120°	1845.7	9.6
90°-150°	6270.1	32.5
90°-180°	8672.0	45.0
0°-180°	19274.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4164	4164	4164	4164	4164	
5°	4164	4148	4104	4136	4128	395
15°	3964	3940	3888	3904	3884	1116
25°	3587	3555	3487	3495	3487	1651
35°	3095	3055	2991	2967	2947	1933
45°	2518	2490	2430	2386	2370	1944
55°	1906	1882	1834	1786	1766	1704
65°	1285	1261	1221	1185	1165	1271
75°	672	665	644	621	629	718
85°	164	160	156	144	140	183
90°	3	34	92	86	89	19
95°	136	163	167	167	163	152
105°	563	570	576	581	581	594
115°	1048	1062	1058	1055	1048	1036
125°	1524	1547	1539	1531	1528	1361
135°	1970	2000	2005	2002	1995	1523
145°	2392	2411	2426	2429	2418	1495
155°	2736	2743	2752	2765	2756	1259
165°	2976	2973	2973	2992	2979	840
175°	3097	3089	3083	3102	3086	294
180°	3102	3102	3102	3102	3102	

TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4163.7	4163.7	4163.7	4163.7	4163.7
2.5°	4187.8	4167.9	4123.7	4163.7	4156.0
5°	4163.7	4147.9	4103.7	4135.6	4127.9
7.5°	4135.6	4111.8	4067.6	4099.9	4091.9
10°	4091.9	4063.8	4015.8	4047.7	4035.8
12.5°	4031.5	4007.7	3959.7	3979.7	3971.6
15°	3963.6	3939.8	3887.5	3903.6	3883.7
17.5°	3879.5	3855.7	3803.4	3823.4	3803.4
20°	3787.3	3763.5	3707.5	3719.3	3703.6
22.5°	3695.5	3659.4	3607.1	3607.1	3599.1
25°	3587.2	3555.3	3487.4	3495.1	3487.4
27.5°	3467.0	3439.0	3387.2	3375.2	3355.3
30°	3347.2	3314.9	3255.0	3243.2	3227.0
32.5°	3218.9	3195.2	3131.0	3106.8	3090.7
35°	3094.9	3055.0	2990.8	2966.6	2946.7
37.5°	2954.7	2918.7	2854.5	2826.5	2806.5
40°	2810.8	2778.5	2714.3	2678.6	2662.5
42.5°	2670.6	2638.3	2574.5	2534.2	2510.4
45°	2518.5	2490.5	2430.1	2386.4	2370.3
47.5°	2370.3	2342.2	2278.1	2233.9	2210.1
50°	2213.9	2194.0	2137.9	2081.8	2061.8
52.5°	2061.8	2033.8	1982.0	1937.8	1909.8
55°	1905.9	1881.8	1833.7	1785.7	1765.8
57.5°	1749.6	1729.7	1677.4	1629.4	1613.3
60°	1593.3	1577.6	1521.5	1477.4	1465.4
62.5°	1441.3	1413.2	1373.3	1333.4	1317.2
65°	1285.4	1261.1	1221.2	1185.1	1165.2
67.5°	1125.2	1104.8	1069.2	1041.2	1025.0
70°	977.0	960.8	924.7	896.7	881.0
72.5°	824.9	808.8	788.8	760.8	748.9
75°	672.4	664.8	644.3	620.6	628.7
77.5°	536.5	520.3	512.3	500.3	488.5
80°	400.6	396.3	388.3	376.4	368.3
82.5°	272.2	272.2	268.5	252.4	252.4
85°	164.0	160.2	156.3	144.0	140.2
87.5°	72.2	64.1	56.1	44.1	39.9
90°	2.8	33.7	91.7	86.1	88.8
92.5°	58.0	78.6	81.3	84.2	84.2
95°	136.5	162.7	167.4	167.4	162.7
97.5°	227.3	251.6	261.9	261.9	261.9
100°	332.0	353.5	361.0	361.0	358.2
102.5°	442.4	458.2	468.6	471.4	468.6
105°	563.0	570.5	576.1	580.8	580.8
107.5°	682.7	693.9	693.9	695.8	682.7
110°	798.7	813.7	813.7	813.7	806.2

TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	924.0	939.9	937.1	929.6	924.0
115°	1047.5	1062.4	1057.7	1055.0	1047.5
117.5°	1170.0	1190.5	1177.4	1170.0	1162.5
120°	1293.4	1314.0	1293.4	1293.4	1285.0
122.5°	1405.7	1431.8	1418.7	1411.2	1405.7
125°	1523.5	1546.8	1539.4	1531.0	1528.1
127.5°	1638.5	1667.5	1657.2	1646.0	1638.5
130°	1746.1	1779.8	1775.0	1769.4	1759.2
132.5°	1866.7	1892.9	1894.8	1881.7	1874.2
135°	1970.5	1999.5	2005.1	2002.3	1994.8
137.5°	2086.5	2109.9	2114.5	2112.6	2101.5
140°	2188.4	2211.8	2224.9	2224.9	2214.7
142.5°	2293.2	2316.6	2324.1	2326.8	2316.6
145°	2392.3	2411.0	2426.0	2428.8	2418.5
147.5°	2481.2	2504.5	2515.8	2520.4	2510.2
150°	2572.9	2588.7	2599.0	2607.5	2599.0
152.5°	2654.2	2670.0	2683.2	2693.5	2683.2
155°	2735.6	2743.0	2751.5	2764.6	2756.1
157.5°	2805.7	2811.3	2815.9	2834.7	2821.5
160°	2868.4	2874.0	2876.7	2892.7	2881.5
162.5°	2926.3	2926.3	2929.2	2946.9	2933.8
165°	2975.9	2973.1	2973.1	2991.8	2978.7
167.5°	3020.8	3012.4	3012.4	3031.1	3018.0
170°	3054.5	3047.0	3044.2	3062.8	3047.0
172.5°	3077.8	3070.3	3067.6	3086.3	3070.3
175°	3096.6	3089.1	3083.4	3102.2	3086.3
177.5°	3106.8	3099.3	3093.7	3109.7	3093.7
180°	3102.2	3102.2	3102.2	3102.2	3102.2

TEST NUMBER: P922556

CATALOG NUMBER: DFN2DIP-PN4F0-120D110US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.50	12.50	13.43	14.63	11.15	12.06	12.06	12.99	14.19
	3H	13.26	14.07	14.18	15.01	16.23	12.77	13.59	13.70	14.53	15.75
	4H	13.85	14.62	14.79	15.57	16.80	13.36	14.13	14.30	15.08	16.31
	6H	14.25	14.96	15.20	15.92	17.16	13.76	14.47	14.71	15.42	16.67
	8H	14.36	15.04	15.32	16.01	17.25	13.87	14.54	14.83	15.51	16.76
	12H	14.41	15.06	15.37	16.02	17.29	13.91	14.56	14.88	15.52	16.79
4H	2H	12.06	12.83	13.00	13.77	15.01	11.71	12.48	12.65	13.42	14.65
	3H	13.93	14.57	14.89	15.55	16.80	13.53	14.17	14.48	15.15	16.39
	4H	14.65	15.24	15.61	16.21	17.48	14.23	14.82	15.20	15.79	17.06
	6H	15.17	15.68	16.15	16.67	17.94	14.75	15.25	15.72	16.25	17.52
	8H	15.32	15.80	16.30	16.78	18.07	14.89	15.37	15.87	16.35	17.64
	12H	15.40	15.83	16.40	16.83	18.12	14.96	15.39	15.96	16.39	17.68
8H	4H	14.85	15.32	15.83	16.31	17.59	14.48	14.95	15.46	15.94	17.22
	6H	15.49	15.88	16.49	16.91	18.19	15.11	15.50	16.11	16.53	17.81
	8H	15.71	16.06	16.72	17.07	18.37	15.33	15.67	16.34	16.69	17.99
	12H	15.85	16.15	16.86	17.16	18.51	15.44	15.75	16.46	16.76	18.10
12H	4H	14.84	15.27	15.84	16.27	17.56	14.48	14.90	15.47	15.91	17.20
	6H	15.52	15.86	16.53	16.88	18.18	15.15	15.50	16.17	16.52	17.81
	8H	15.76	16.07	16.78	17.08	18.42	15.39	15.70	16.41	16.71	18.05