

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925044

Luminaire Tested: DFN2DIP-PN4F0-060D050US950-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925044  
REPORT IS A COMBINATION OF REPORTS P899631 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-060D050US950-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9888.2 lumens  
Efficiency: N/A  
Efficacy: 107.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 92.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925044  
CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P925044

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	56	54	53	48	48	48	48
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45	40	40	40	40
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	41	38	34	34	34	34
4	76	65	57	51	70	61	53	48	53	47	43	46	41	38	39	36	33	29	29	29	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26	26	26	26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22	22	22	22
7	59	47	39	33	55	44	37	32	39	33	28	34	29	25	29	25	22	20	20	20	20
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18	18	18	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16	16	16	16
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15	15	15	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1626	1626	1626
5°	1628	1603	1614
10°	1615	1582	1593
15°	1591	1556	1559
20°	1559	1520	1524
25°	1527	1477	1484
30°	1487	1437	1433
35°	1450	1390	1379
40°	1403	1342	1327
45°	1356	1294	1275
50°	1305	1244	1214
55°	1252	1186	1158
60°	1192	1117	1094
65°	1126	1046	1018
70°	1043	959	937
75°	927	855	863
80°	787	722	719
85°	569	493	481

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1356 cd/sqm



TEST NUMBER: P925044

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.6	2.1
10°-20°	589.8	6.0
20°-30°	866.8	8.8
30°-40°	1006.7	10.2
40°-50°	1005.5	10.2
50°-60°	876.7	8.9
60°-70°	648.1	6.6
70°-80°	366.7	3.7
80°-90°	101.1	1.0
90°-100°	93.4	0.9
100°-110°	296.6	3.0
110°-120°	507.6	5.1
120°-130°	667.5	6.8
130°-140°	749.3	7.6
140°-150°	734.8	7.4
150°-160°	616.4	6.2
160°-170°	408.8	4.1
170°-180°	142.9	1.4
0°-30°	1666.2	16.9
0°-40°	2673.0	27.0
0°-60°	4555.2	46.1
0°-90°	5671.1	57.4
90°-120°	897.5	9.1
90°-150°	3049.2	30.8
90°-180°	4217.0	42.6
0°-180°	9888.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2227	2227	2227	2227	2227	
5°	2227	2219	2195	2212	2208	211
15°	2120	2108	2080	2088	2078	597
25°	1919	1902	1866	1870	1866	883
35°	1656	1634	1600	1587	1576	1034
45°	1347	1332	1300	1276	1268	1040
55°	1020	1007	981	955	945	912
65°	688	675	653	634	623	680
75°	360	356	345	332	336	384
85°	88	86	84	77	75	98
90°	1	16	45	42	43	10
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	



TEST NUMBER: P925044

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2229.5	2205.8	2227.2	2223.1
5°	2227.2	2218.8	2195.2	2212.2	2208.1
7.5°	2212.2	2199.5	2175.9	2193.2	2188.9
10°	2188.9	2173.9	2148.1	2165.2	2158.8
12.5°	2156.6	2143.8	2118.2	2128.9	2124.6
15°	2120.2	2107.5	2079.5	2088.2	2077.5
17.5°	2075.2	2062.5	2034.6	2045.2	2034.6
20°	2025.9	2013.2	1983.2	1989.6	1981.2
22.5°	1976.9	1957.5	1929.6	1929.6	1925.3
25°	1918.9	1901.9	1865.5	1869.6	1865.5
27.5°	1854.6	1839.6	1811.8	1805.5	1794.9
30°	1790.6	1773.2	1741.2	1734.8	1726.2
32.5°	1721.9	1709.2	1674.8	1661.9	1653.3
35°	1655.6	1634.2	1599.9	1586.9	1576.2
37.5°	1580.6	1561.2	1527.0	1511.9	1501.2
40°	1503.5	1486.2	1452.0	1432.9	1424.2
42.5°	1428.5	1411.3	1377.2	1355.6	1342.9
45°	1347.2	1332.2	1299.9	1276.5	1267.9
47.5°	1267.9	1252.9	1218.6	1195.0	1182.2
50°	1184.3	1173.6	1143.7	1113.6	1102.9
52.5°	1102.9	1087.9	1060.2	1036.6	1021.6
55°	1019.5	1006.6	980.9	955.2	944.6
57.5°	936.0	925.3	897.3	871.7	863.0
60°	852.3	843.9	814.0	790.3	783.9
62.5°	770.9	755.9	734.6	713.2	704.6
65°	687.5	674.7	653.3	633.9	623.2
67.5°	601.9	591.0	571.9	556.9	548.3
70°	522.6	514.0	494.6	479.7	471.3
72.5°	441.2	432.6	422.0	407.0	400.6
75°	359.7	355.7	344.7	332.0	336.3
77.5°	287.0	278.4	274.0	267.7	261.3
80°	214.3	212.0	207.7	201.3	197.0
82.5°	145.7	145.7	143.6	135.0	135.0
85°	87.7	85.7	83.6	77.0	75.0
87.5°	38.6	34.3	30.0	23.7	21.4
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0



TEST NUMBER: P925044

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6



TEST NUMBER: P925044  
 CATALOG NUMBER: DFN2DIP-PN4F0-060D050US950-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.62	10.55	10.51	11.46	12.62	9.18	10.11	10.07	11.02	12.18
	3H	11.29	12.12	12.19	13.04	14.23	10.80	11.64	11.71	12.56	13.75
	4H	11.88	12.67	12.80	13.60	14.79	11.39	12.18	12.31	13.11	14.31
	6H	12.29	13.01	13.22	13.95	15.16	11.79	12.52	12.72	13.46	14.67
	8H	12.39	13.09	13.33	14.04	15.25	11.90	12.60	12.84	13.55	14.75
	12H	12.45	13.11	13.39	14.05	15.28	11.95	12.61	12.89	13.55	14.78
4H	2H	10.09	10.88	11.01	11.81	13.00	9.74	10.53	10.66	11.45	12.65
	3H	11.96	12.62	12.90	13.58	14.79	11.56	12.22	12.50	13.18	14.39
	4H	12.68	13.29	13.63	14.24	15.47	12.27	12.87	13.21	13.82	15.06
	6H	13.21	13.73	14.16	14.70	15.94	12.78	13.30	13.74	14.28	15.51
	8H	13.36	13.84	14.32	14.81	16.06	12.93	13.42	13.89	14.38	15.64
	12H	13.44	13.88	14.42	14.86	16.12	13.00	13.43	13.98	14.42	15.68
8H	4H	12.89	13.37	13.85	14.34	15.59	12.52	13.00	13.48	13.97	15.22
	6H	13.52	13.93	14.51	14.94	16.19	13.15	13.55	14.13	14.56	15.81
	8H	13.75	14.10	14.74	15.10	16.37	13.36	13.72	14.36	14.72	15.98
	12H	13.88	14.20	14.88	15.19	16.50	13.48	13.79	14.48	14.79	16.10
12H	4H	12.88	13.31	13.85	14.30	15.56	12.51	12.95	13.49	13.94	15.19
	6H	13.55	13.91	14.55	14.91	16.18	13.19	13.55	14.18	14.54	15.81
	8H	13.80	14.12	14.80	15.11	16.42	13.43	13.74	14.43	14.74	16.05