

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911778

Luminaire Tested: DFN2DIP-SQ2F0-080D040US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911778
REPORT IS A COMBINATION OF REPORTS P899794 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D040US850-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11467.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 108.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8063	8063	8063
5°	8062	7917	7974
10°	7968	7745	7704
15°	7844	7472	7292
20°	7685	7103	6791
25°	7522	6692	6308
30°	7308	6273	5698
35°	7098	5824	5163
40°	6883	5361	4552
45°	6635	4850	3998
50°	6377	4336	3458
55°	6106	3788	2940
60°	5792	3219	2410
65°	5431	2642	2156
70°	4991	2104	1935
75°	4438	1821	1738
80°	3644	1479	1473
85°	2372	918	1048

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6635 cd/sqm

TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	3.0
10°-20°	943.4	8.2
20°-30°	1324.5	11.6
30°-40°	1443.8	12.6
40°-50°	1327.0	11.6
50°-60°	1042.1	9.1
60°-70°	678.3	5.9
70°-80°	349.2	3.0
80°-90°	93.1	0.8
90°-100°	86.8	0.8
100°-110°	275.8	2.4
110°-120°	472.0	4.1
120°-130°	620.8	5.4
130°-140°	696.8	6.1
140°-150°	683.3	6.0
150°-160°	573.2	5.0
160°-170°	380.1	3.3
170°-180°	132.9	1.2
0°-30°	2611.6	22.8
0°-40°	4055.4	35.4
0°-60°	6424.5	56.0
0°-90°	7545.2	65.8
90°-120°	834.7	7.3
90°-150°	2835.6	24.7
90°-180°	3922.0	34.2
0°-180°	11467.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	1	15	42	39	40	11
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P911778

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.64	16.62	16.46	17.46	18.48	11.60	12.58	12.42	13.42	14.45
	3H	17.31	18.19	18.14	19.03	20.09	12.79	13.66	13.62	14.50	15.56
	4H	17.92	18.74	18.76	19.59	20.66	13.23	14.06	14.08	14.91	15.97
	6H	18.33	19.09	19.19	19.95	21.03	13.54	14.30	14.40	15.16	16.24
	8H	18.45	19.17	19.32	20.05	21.13	13.63	14.35	14.50	15.23	16.31
	12H	18.51	19.20	19.38	20.07	21.17	13.67	14.36	14.54	15.23	16.33
4H	2H	15.68	16.50	16.53	17.35	18.42	12.21	13.03	13.06	13.88	14.95
	3H	17.50	18.18	18.36	19.06	20.15	13.55	14.24	14.41	15.12	16.20
	4H	18.18	18.80	19.05	19.68	20.79	14.09	14.71	14.96	15.59	16.70
	6H	18.68	19.22	19.57	20.12	21.24	14.50	15.03	15.39	15.94	17.05
	8H	18.85	19.35	19.74	20.25	21.38	14.62	15.12	15.51	16.02	17.14
	12H	18.94	19.39	19.85	20.31	21.44	14.68	15.13	15.59	16.05	17.18
8H	4H	18.15	18.65	19.04	19.55	20.68	14.37	14.87	15.26	15.77	16.89
	6H	18.70	19.12	19.62	20.06	21.18	14.87	15.28	15.79	16.22	17.35
	8H	18.91	19.27	19.84	20.21	21.35	15.04	15.41	15.97	16.34	17.49
	12H	19.04	19.36	19.97	20.29	21.48	15.15	15.48	16.09	16.40	17.60
12H	4H	18.11	18.56	19.02	19.48	20.61	14.38	14.83	15.29	15.75	16.88
	6H	18.68	19.04	19.61	19.98	21.12	14.91	15.28	15.84	16.21	17.36
	8H	18.89	19.21	19.82	20.14	21.33	15.11	15.44	16.04	16.36	17.56