

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914383

Luminaire Tested: DFN2DIP-SQ2F0-030D030US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914383
REPORT IS A COMBINATION OF REPORTS P901292 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D030US927-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4372.8 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2160	2160	2160
5°	2159	2121	2136
10°	2134	2075	2064
15°	2101	2001	1953
20°	2059	1902	1819
25°	2015	1793	1690
30°	1958	1680	1527
35°	1901	1560	1383
40°	1844	1436	1219
45°	1777	1299	1071
50°	1708	1162	926
55°	1636	1015	788
60°	1551	862	646
65°	1455	707	578
70°	1337	564	518
75°	1189	488	465
80°	977	396	394
85°	635	246	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1777 cd/sqm

TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	2.1
10°-20°	252.7	5.8
20°-30°	354.8	8.1
30°-40°	386.8	8.8
40°-50°	355.5	8.1
50°-60°	279.2	6.4
60°-70°	181.7	4.2
70°-80°	93.5	2.1
80°-90°	25.3	0.6
90°-100°	26.5	0.6
100°-110°	98.6	2.3
110°-120°	261.5	6.0
120°-130°	433.7	9.9
130°-140°	460.7	10.5
140°-150°	428.1	9.8
150°-160°	344.2	7.9
160°-170°	221.8	5.1
170°-180°	76.3	1.7
0°-30°	699.6	16.0
0°-40°	1086.3	24.8
0°-60°	1720.9	39.4
0°-90°	2021.5	46.2
90°-120°	386.5	8.8
90°-150°	1709.0	39.1
90°-180°	2351.0	53.8
0°-180°	4372.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	972	93
15°	934	924	894	877	868	263
25°	848	820	761	724	711	390
35°	731	685	607	551	532	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	44
90°	1	7	12	15	16	4
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.2	982.2	982.2	982.2	982.2
2.5°	986.7	982.2	972.4	981.4	979.6
5°	982.2	977.8	966.2	974.2	971.5
7.5°	974.2	968.9	956.5	960.0	955.5
10°	963.5	957.4	939.6	936.8	931.6
12.5°	950.2	942.2	918.2	912.9	903.1
15°	934.2	924.4	894.2	877.3	868.5
17.5°	915.5	901.3	864.0	844.5	830.2
20°	894.2	876.4	831.9	809.8	790.2
22.5°	871.2	850.6	799.1	768.9	755.6
25°	848.0	819.5	760.9	724.4	711.1
27.5°	820.5	790.2	725.3	683.6	663.1
30°	791.2	757.3	686.2	641.0	616.9
32.5°	762.6	721.8	649.0	595.6	573.3
35°	730.7	685.3	607.1	551.1	531.6
37.5°	699.6	650.6	568.0	506.6	484.5
40°	666.7	613.4	527.1	464.0	440.9
42.5°	632.9	576.1	486.2	420.4	398.2
45°	597.4	537.7	444.5	381.3	360.0
47.5°	563.6	500.5	404.5	341.3	321.8
50°	526.2	463.1	365.4	304.0	285.3
52.5°	489.7	423.1	328.0	269.3	252.5
55°	454.2	384.8	288.8	235.6	218.7
57.5°	417.8	346.7	254.3	204.5	190.2
60°	380.4	309.3	217.8	172.5	158.3
62.5°	344.0	272.9	186.6	144.0	137.0
65°	306.7	234.6	154.6	124.5	121.8
67.5°	271.2	199.1	124.5	109.3	106.6
70°	233.8	164.5	103.1	94.2	90.6
72.5°	198.2	132.4	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.1	7.1	6.3	6.3
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P914383

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.34	10.14	10.34	11.15	12.47	5.31	6.11	6.30	7.11	8.44
	3H	11.00	11.72	12.01	12.73	14.08	6.47	7.19	7.48	8.20	9.55
	4H	11.59	12.27	12.61	13.29	14.64	6.91	7.59	7.93	8.60	9.96
	6H	12.00	12.62	13.03	13.64	15.01	7.21	7.83	8.24	8.85	10.22
	8H	12.12	12.71	13.15	13.74	15.11	7.29	7.89	8.33	8.92	10.28
	12H	12.17	12.73	13.21	13.76	15.15	7.33	7.89	8.37	8.92	10.31
4H	2H	9.35	10.03	10.38	11.05	12.40	5.89	6.56	6.91	7.58	8.93
	3H	11.16	11.72	12.19	12.76	14.13	7.21	7.77	8.25	8.82	10.19
	4H	11.83	12.35	12.87	13.38	14.78	7.74	8.26	8.78	9.29	10.68
	6H	12.33	12.77	13.38	13.83	15.22	8.14	8.58	9.19	9.64	11.03
	8H	12.49	12.90	13.54	13.96	15.36	8.26	8.67	9.31	9.72	11.12
	12H	12.57	12.95	13.64	14.01	15.42	8.31	8.68	9.38	9.75	11.16
8H	4H	11.80	12.21	12.85	13.26	14.66	8.01	8.42	9.06	9.47	10.87
	6H	12.34	12.68	13.41	13.77	15.17	8.50	8.84	9.58	9.93	11.33
	8H	12.54	12.84	13.62	13.92	15.34	8.68	8.98	9.76	10.05	11.47
	12H	12.66	12.93	13.75	14.00	15.46	8.78	9.05	9.87	10.12	11.58
12H	4H	11.74	12.12	12.81	13.18	14.59	8.01	8.38	9.08	9.45	10.85
	6H	12.31	12.61	13.39	13.69	15.11	8.55	8.84	9.63	9.92	11.34
	8H	12.52	12.78	13.60	13.85	15.31	8.74	9.00	9.82	10.07	11.53