

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914391

Luminaire Tested: DFN2DIP-SQ2F0-030D050US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914391
REPORT IS A COMBINATION OF REPORTS P901316 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D050US927-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5941.4 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 60.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2160	2160	2160
5°	2159	2121	2136
10°	2134	2075	2064
15°	2101	2001	1953
20°	2059	1902	1819
25°	2015	1793	1690
30°	1958	1680	1527
35°	1901	1560	1383
40°	1844	1436	1219
45°	1777	1299	1071
50°	1708	1162	926
55°	1636	1015	788
60°	1551	862	646
65°	1455	707	578
70°	1337	564	518
75°	1189	488	465
80°	977	396	394
85°	635	246	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1777 cd/sqm

TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	1.5
10°-20°	252.7	4.3
20°-30°	354.8	6.0
30°-40°	386.8	6.5
40°-50°	355.5	6.0
50°-60°	279.2	4.7
60°-70°	181.7	3.1
70°-80°	93.5	1.6
80°-90°	26.2	0.4
90°-100°	44.1	0.7
100°-110°	164.3	2.8
110°-120°	435.8	7.3
120°-130°	722.8	12.2
130°-140°	767.8	12.9
140°-150°	713.6	12.0
150°-160°	573.7	9.7
160°-170°	369.7	6.2
170°-180°	127.2	2.1
0°-30°	699.6	11.8
0°-40°	1086.3	18.3
0°-60°	1720.9	29.0
0°-90°	2022.4	34.0
90°-120°	644.2	10.8
90°-150°	2848.4	47.9
90°-180°	3919.0	66.0
0°-180°	5941.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	972	93
15°	934	924	894	877	868	263
25°	848	820	761	724	711	390
35°	731	685	607	551	532	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	44
90°	1	12	19	24	26	6
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	

TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.2	982.2	982.2	982.2	982.2
2.5°	986.7	982.2	972.4	981.4	979.6
5°	982.2	977.8	966.2	974.2	971.5
7.5°	974.2	968.9	956.5	960.0	955.5
10°	963.5	957.4	939.6	936.8	931.6
12.5°	950.2	942.2	918.2	912.9	903.1
15°	934.2	924.4	894.2	877.3	868.5
17.5°	915.5	901.3	864.0	844.5	830.2
20°	894.2	876.4	831.9	809.8	790.2
22.5°	871.2	850.6	799.1	768.9	755.6
25°	848.0	819.5	760.9	724.4	711.1
27.5°	820.5	790.2	725.3	683.6	663.1
30°	791.2	757.3	686.2	641.0	616.9
32.5°	762.6	721.8	649.0	595.6	573.3
35°	730.7	685.3	607.1	551.1	531.6
37.5°	699.6	650.6	568.0	506.6	484.5
40°	666.7	613.4	527.1	464.0	440.9
42.5°	632.9	576.1	486.2	420.4	398.2
45°	597.4	537.7	444.5	381.3	360.0
47.5°	563.6	500.5	404.5	341.3	321.8
50°	526.2	463.1	365.4	304.0	285.3
52.5°	489.7	423.1	328.0	269.3	252.5
55°	454.2	384.8	288.8	235.6	218.7
57.5°	417.8	346.7	254.3	204.5	190.2
60°	380.4	309.3	217.8	172.5	158.3
62.5°	344.0	272.9	186.6	144.0	137.0
65°	306.7	234.6	154.6	124.5	121.8
67.5°	271.2	199.1	124.5	109.3	106.6
70°	233.8	164.5	103.1	94.2	90.6
72.5°	198.2	132.4	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.1	7.1	6.3	6.3
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4

TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7

TEST NUMBER: P914391

CATALOG NUMBER: DFN2DIP-SQ2F0-030D050US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.00	8.72	9.09	9.80	11.29	3.96	4.68	5.05	5.76	7.25
	3H	9.65	10.29	10.75	11.38	12.89	5.12	5.76	6.22	6.86	8.36
	4H	10.24	10.85	11.35	11.94	13.45	5.56	6.16	6.66	7.26	8.76
	6H	10.64	11.20	11.76	12.30	13.82	5.85	6.41	6.97	7.51	9.03
	8H	10.76	11.29	11.88	12.40	13.91	5.93	6.46	7.05	7.58	9.09
	12H	10.81	11.31	11.93	12.41	13.95	5.97	6.47	7.09	7.57	9.11
4H	2H	8.00	8.61	9.12	9.70	11.21	4.53	5.14	5.65	6.23	7.74
	3H	9.80	10.30	10.92	11.42	12.94	5.85	6.36	6.97	7.48	9.00
	4H	10.47	10.93	11.59	12.04	13.58	6.38	6.84	7.50	7.95	9.49
	6H	10.96	11.36	12.09	12.49	14.02	6.77	7.17	7.90	8.30	9.83
	8H	11.12	11.49	12.25	12.62	14.17	6.89	7.26	8.02	8.38	9.93
	12H	11.20	11.54	12.35	12.67	14.23	6.94	7.27	8.09	8.41	9.96
8H	4H	10.42	10.79	11.56	11.92	13.47	6.64	7.01	7.77	8.13	9.68
	6H	10.97	11.27	12.12	12.44	13.98	7.13	7.43	8.28	8.60	10.15
	8H	11.17	11.43	12.33	12.58	14.15	7.31	7.57	8.46	8.72	10.28
	12H	11.29	11.52	12.45	12.66	14.27	7.41	7.64	8.57	8.78	10.38
12H	4H	10.37	10.71	11.52	11.84	13.40	6.64	6.97	7.78	8.11	9.66
	6H	10.94	11.20	12.10	12.35	13.92	7.17	7.44	8.33	8.58	10.15
	8H	11.14	11.37	12.30	12.52	14.12	7.36	7.60	8.52	8.74	10.34