

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914397

Luminaire Tested: DFN2DIP-SQ2F0-030D070US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914397
REPORT IS A COMBINATION OF REPORTS P901339 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D070US927-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7842.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2033	2033	2033
5°	2033	2001	2016
10°	2013	1969	1986
15°	1980	1932	1940
20°	1936	1883	1894
25°	1893	1825	1840
30°	1840	1770	1773
35°	1789	1707	1703
40°	1726	1642	1636
45°	1664	1577	1566
50°	1596	1509	1487
55°	1524	1431	1412
60°	1443	1338	1328
65°	1354	1241	1228
70°	1241	1123	1119
75°	1085	982	1016
80°	897	801	824
85°	606	506	517

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1776 cd/sqm

TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.1
10°-20°	244.9	3.1
20°-30°	359.9	4.6
30°-40°	418.0	5.3
40°-50°	417.5	5.3
50°-60°	364.0	4.6
60°-70°	269.1	3.4
70°-80°	152.3	1.9
80°-90°	43.5	0.6
90°-100°	61.7	0.8
100°-110°	230.0	2.9
110°-120°	610.1	7.8
120°-130°	1011.9	12.9
130°-140°	1074.9	13.7
140°-150°	999.0	12.7
150°-160°	803.2	10.2
160°-170°	517.5	6.6
170°-180°	178.1	2.3
0°-30°	691.8	8.8
0°-40°	1109.8	14.2
0°-60°	1891.3	24.1
0°-90°	2356.1	30.0
90°-120°	901.9	11.5
90°-150°	3987.7	50.8
90°-180°	5487.0	70.0
0°-180°	7842.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	1	16	27	34	36	7
95°	88	43	53	60	58	104
105°	412	452	83	97	103	440
115°	779	802	836	209	111	767
125°	1101	1119	1144	1154	1158	982
135°	1362	1384	1396	1410	1407	1052
145°	1580	1579	1602	1612	1605	988
155°	1740	1728	1744	1752	1742	802
165°	1834	1826	1830	1839	1830	518
175°	1876	1866	1869	1878	1865	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	1.3	16.2	27.0	33.9	36.5
92.5°	33.9	28.4	32.5	35.3	36.5
95°	87.9	43.3	52.8	59.7	58.2
97.5°	158.4	47.5	69.0	73.2	74.5
100°	239.8	54.2	77.2	87.9	90.7
102.5°	329.0	326.5	79.9	94.7	98.9
105°	411.7	452.3	82.6	97.4	102.9
107.5°	507.8	541.6	85.4	100.2	105.7
110°	600.0	628.3	237.0	101.6	106.9

TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.7	710.9	687.9	104.2	108.4
115°	778.6	801.6	835.5	208.6	111.1
117.5°	858.6	885.6	908.7	714.9	360.2
120°	947.9	968.2	992.7	1008.9	826.1
122.5°	1023.7	1045.4	1072.6	1080.6	1082.0
125°	1100.9	1118.6	1144.3	1153.8	1157.8
127.5°	1171.3	1190.3	1210.7	1224.2	1225.5
130°	1237.7	1259.4	1274.2	1289.2	1287.9
132.5°	1305.4	1323.1	1337.9	1350.1	1348.8
135°	1362.3	1384.0	1396.1	1409.8	1407.1
137.5°	1421.8	1438.1	1451.8	1465.3	1461.3
140°	1480.0	1491.0	1505.8	1518.0	1511.2
142.5°	1528.9	1538.4	1555.9	1566.7	1560.0
145°	1580.4	1579.0	1601.9	1611.5	1604.7
147.5°	1624.9	1621.0	1643.9	1650.7	1645.4
150°	1668.3	1658.9	1680.6	1688.6	1681.9
152.5°	1704.9	1694.1	1714.4	1722.5	1713.1
155°	1740.1	1728.0	1744.2	1752.3	1741.5
157.5°	1768.5	1757.8	1770.0	1779.5	1768.5
160°	1793.0	1784.8	1793.0	1801.0	1791.5
162.5°	1814.6	1806.5	1813.2	1822.7	1810.5
165°	1833.5	1825.5	1829.5	1839.0	1829.5
167.5°	1848.5	1840.2	1844.4	1853.9	1841.7
170°	1860.7	1852.5	1855.2	1864.7	1852.5
172.5°	1868.8	1860.7	1863.4	1872.9	1860.7
175°	1875.5	1866.0	1868.8	1878.2	1864.7
177.5°	1878.2	1868.8	1870.2	1879.7	1867.4
180°	1871.4	1871.4	1871.4	1871.4	1871.4

TEST NUMBER: P914397

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.41	8.12	8.53	9.23	10.76	6.97	7.68	8.08	8.78	10.31
	3H	9.04	9.68	10.16	10.79	12.34	8.55	9.19	9.67	10.30	11.85
	4H	9.61	10.21	10.74	11.33	12.88	9.12	9.72	10.25	10.84	12.39
	6H	9.99	10.54	11.13	11.66	13.22	9.49	10.04	10.63	11.16	12.72
	8H	10.08	10.61	11.22	11.74	13.30	9.58	10.11	10.72	11.24	12.80
	12H	10.12	10.62	11.26	11.74	13.32	9.61	10.11	10.75	11.24	12.82
4H	2H	7.85	8.45	8.98	9.56	11.11	7.49	8.09	8.63	9.21	10.76
	3H	9.67	10.18	10.82	11.32	12.88	9.27	9.77	10.41	10.91	12.47
	4H	10.37	10.83	11.51	11.96	13.54	9.94	10.40	11.09	11.54	13.12
	6H	10.85	11.25	12.01	12.40	13.98	10.42	10.82	11.57	11.97	13.55
	8H	10.99	11.36	12.14	12.50	14.10	10.55	10.92	11.71	12.07	13.66
	12H	11.05	11.38	12.21	12.54	14.13	10.60	10.93	11.77	12.09	13.69
8H	4H	10.54	10.91	11.69	12.05	13.65	10.16	10.53	11.31	11.68	13.27
	6H	11.14	11.44	12.31	12.63	14.22	10.76	11.06	11.93	12.25	13.84
	8H	11.35	11.61	12.52	12.78	14.39	10.95	11.22	12.13	12.38	13.99
	12H	11.46	11.69	12.64	12.85	14.50	11.05	11.28	12.23	12.44	14.09
12H	4H	10.51	10.85	11.68	12.01	13.60	10.15	10.48	11.31	11.64	13.23
	6H	11.16	11.43	12.34	12.60	14.20	10.79	11.06	11.97	12.22	13.83
	8H	11.38	11.62	12.56	12.78	14.42	11.00	11.24	12.18	12.40	14.04

END OF REPORT