

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914401

Luminaire Tested: DFN2DIP-SQ2F0-030D080US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914401
REPORT IS A COMBINATION OF REPORTS P901351 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US927-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8626.8 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914401
CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P914401

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23				23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21	16				16
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18	14				14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16	12				12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11				11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9				9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8				8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10	8				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2033	2033	2033
5°	2033	2001	2016
10°	2013	1969	1986
15°	1980	1932	1940
20°	1936	1883	1894
25°	1893	1825	1840
30°	1840	1770	1773
35°	1789	1707	1703
40°	1726	1642	1636
45°	1664	1577	1566
50°	1596	1509	1487
55°	1524	1431	1412
60°	1443	1338	1328
65°	1354	1241	1228
70°	1241	1123	1119
75°	1085	982	1016
80°	897	801	824
85°	606	506	517

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2029 cd/sqm



TEST NUMBER: P914401

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.0
10°-20°	244.9	2.8
20°-30°	359.9	4.2
30°-40°	418.0	4.8
40°-50°	417.5	4.8
50°-60°	364.0	4.2
60°-70°	269.1	3.1
70°-80°	152.3	1.8
80°-90°	43.9	0.5
90°-100°	70.5	0.8
100°-110°	262.9	3.0
110°-120°	697.3	8.1
120°-130°	1156.5	13.4
130°-140°	1228.4	14.2
140°-150°	1141.7	13.2
150°-160°	917.9	10.6
160°-170°	591.5	6.9
170°-180°	203.6	2.4
0°-30°	691.8	8.0
0°-40°	1109.8	12.9
0°-60°	1891.3	21.9
0°-90°	2356.5	27.3
90°-120°	1030.7	11.9
90°-150°	4557.3	52.8
90°-180°	6270.0	72.7
0°-180°	8626.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	2	18	31	39	42	8
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	



TEST NUMBER: P914401

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2



TEST NUMBER: P914401

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8



TEST NUMBER: P914401
 CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.03	7.72	8.16	8.84	10.40	6.58	7.27	7.71	8.39	9.96
	3H	8.66	9.27	9.79	10.40	11.98	8.17	8.78	9.30	9.91	11.49
	4H	9.22	9.81	10.37	10.94	12.52	8.73	9.32	9.88	10.45	12.03
	6H	9.60	10.14	10.75	11.27	12.86	9.10	9.64	10.25	10.77	12.37
	8H	9.69	10.20	10.85	11.35	12.94	9.19	9.70	10.35	10.85	12.44
	12H	9.73	10.21	10.89	11.35	12.96	9.22	9.70	10.38	10.85	12.46
4H	2H	7.46	8.04	8.61	9.17	10.76	7.10	7.69	8.26	8.82	10.40
	3H	9.28	9.77	10.44	10.93	12.52	8.88	9.37	10.04	10.52	12.12
	4H	9.98	10.43	11.14	11.57	13.18	9.55	10.00	10.71	11.15	12.76
	6H	10.46	10.85	11.63	12.02	13.62	10.03	10.42	11.20	11.58	13.19
	8H	10.60	10.96	11.77	12.12	13.74	10.16	10.52	11.33	11.68	13.30
	12H	10.65	10.98	11.84	12.15	13.78	10.21	10.53	11.39	11.70	13.33
8H	4H	10.15	10.51	11.31	11.67	13.29	9.77	10.13	10.94	11.29	12.91
	6H	10.75	11.04	11.93	12.24	13.86	10.36	10.66	11.55	11.86	13.48
	8H	10.95	11.21	12.14	12.39	14.03	10.56	10.82	11.75	12.00	13.64
	12H	11.06	11.29	12.26	12.47	14.14	10.65	10.88	11.85	12.06	13.73
12H	4H	10.12	10.45	11.30	11.62	13.24	9.75	10.08	10.94	11.25	12.87
	6H	10.77	11.03	11.96	12.21	13.85	10.40	10.66	11.59	11.84	13.47
	8H	10.99	11.22	12.18	12.39	14.06	10.61	10.83	11.80	12.01	13.68