

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925116

Luminaire Tested: DFN2DIP-PN4F0-080D050US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925116
REPORT IS A COMBINATION OF REPORTS P899635 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D050US950-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11777.1 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69
1	101	97	93	89	95	91	87	84	80	77	75		70	68	66		61
2	92	84	78	73	86	79	74	69	70	66	62		62	58	56		54
3	84	74	67	61	79	70	63	58	62	57	52		55	50	47		48
4	77	66	58	51	72	62	55	49	55	49	45		49	44	40		43
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		38
6	65	53	44	38	61	50	42	37	45	38	34		40	35	31		35
7	60	48	40	34	56	45	38	32	40	34	30		36	31	27		32
8	56	43	35	30	53	41	34	29	37	31	27		33	28	24		29
9	52	40	32	27	49	38	31	26	34	28	24		30	26	22		27
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2168	2168	2168
5°	2171	2138	2152
10°	2154	2109	2124
15°	2122	2075	2078
20°	2079	2027	2032
25°	2037	1970	1979
30°	1983	1916	1911
35°	1933	1853	1838
40°	1870	1789	1770
45°	1808	1726	1700
50°	1741	1659	1619
55°	1669	1581	1544
60°	1589	1489	1458
65°	1502	1394	1358
70°	1390	1278	1249
75°	1236	1140	1150
80°	1050	963	959
85°	759	657	642

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1808 cd/sqm

TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.4
10°-20°	786.4	6.7
20°-30°	1155.7	9.8
30°-40°	1342.3	11.4
40°-50°	1340.6	11.4
50°-60°	1169.0	9.9
60°-70°	864.1	7.3
70°-80°	488.9	4.2
80°-90°	133.3	1.1
90°-100°	93.4	0.8
100°-110°	296.6	2.5
110°-120°	507.6	4.3
120°-130°	667.5	5.7
130°-140°	749.3	6.4
140°-150°	734.8	6.2
150°-160°	616.4	5.2
160°-170°	408.8	3.5
170°-180°	142.9	1.2
0°-30°	2221.6	18.9
0°-40°	3563.9	30.3
0°-60°	6073.6	51.6
0°-90°	7560.0	64.2
90°-120°	897.5	7.6
90°-150°	3049.2	25.9
90°-180°	4217.0	35.8
0°-180°	11777.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	1	16	45	42	43	11
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	

TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0

TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6

TEST NUMBER: P925116

CATALOG NUMBER: DFN2DIP-PN4F0-080D050US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.18	12.19	12.01	13.03	14.09	10.74	11.75	11.57	12.59	13.65
	3H	12.86	13.76	13.69	14.62	15.70	12.37	13.27	13.21	14.13	15.21
	4H	13.45	14.30	14.31	15.17	16.26	12.96	13.82	13.82	14.68	15.77
	6H	13.86	14.65	14.73	15.52	16.62	13.37	14.16	14.24	15.03	16.13
	8H	13.97	14.72	14.85	15.61	16.71	13.48	14.23	14.35	15.12	16.22
	12H	14.03	14.74	14.91	15.62	16.75	13.53	14.24	14.41	15.12	16.25
4H	2H	11.66	12.51	12.52	13.38	14.47	11.31	12.16	12.17	13.03	14.12
	3H	13.54	14.25	14.41	15.15	16.26	13.14	13.85	14.01	14.75	15.86
	4H	14.26	14.91	15.15	15.81	16.94	13.85	14.50	14.73	15.39	16.52
	6H	14.79	15.35	15.69	16.27	17.40	14.37	14.93	15.26	15.84	16.98
	8H	14.95	15.47	15.85	16.38	17.53	14.52	15.04	15.42	15.95	17.10
	12H	15.03	15.50	15.95	16.43	17.58	14.59	15.06	15.51	15.99	17.14
8H	4H	14.47	15.00	15.37	15.91	17.06	14.10	14.63	15.00	15.54	16.69
	6H	15.11	15.55	16.04	16.50	17.65	14.74	15.17	15.67	16.13	17.27
	8H	15.34	15.72	16.28	16.67	17.83	14.95	15.34	15.89	16.28	17.45
	12H	15.48	15.82	16.42	16.75	17.97	15.08	15.42	16.02	16.35	17.57
12H	4H	14.47	14.94	15.39	15.87	17.02	14.10	14.58	15.02	15.51	16.66
	6H	15.15	15.53	16.08	16.48	17.64	14.78	15.17	15.72	16.11	17.28
	8H	15.40	15.74	16.34	16.67	17.89	15.02	15.36	15.96	16.30	17.52