

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914404

Luminaire Tested: DFN2DIP-SQ2F0-040D030US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914404
REPORT IS A COMBINATION OF REPORTS P899773 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D030US927-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5240.3 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 56.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2711	2711	2711
5°	2711	2667	2688
10°	2684	2626	2647
15°	2640	2577	2587
20°	2582	2511	2525
25°	2524	2433	2454
30°	2453	2360	2365
35°	2385	2276	2271
40°	2302	2190	2181
45°	2219	2103	2088
50°	2128	2012	1982
55°	2033	1908	1883
60°	1924	1784	1770
65°	1805	1655	1637
70°	1654	1498	1492
75°	1448	1309	1354
80°	1195	1068	1100
85°	808	675	690

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2219 cd/sqm

TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	2.2
10°-20°	326.5	6.2
20°-30°	479.8	9.2
30°-40°	557.3	10.6
40°-50°	556.6	10.6
50°-60°	485.3	9.3
60°-70°	358.8	6.8
70°-80°	203.0	3.9
80°-90°	55.7	1.1
90°-100°	46.5	0.9
100°-110°	147.8	2.8
110°-120°	252.9	4.8
120°-130°	332.6	6.3
130°-140°	373.3	7.1
140°-150°	366.1	7.0
150°-160°	307.1	5.9
160°-170°	203.7	3.9
170°-180°	71.2	1.4
0°-30°	922.4	17.6
0°-40°	1479.7	28.2
0°-60°	2521.7	48.1
0°-90°	3139.2	59.9
90°-120°	447.2	8.5
90°-150°	1519.2	29.0
90°-180°	2101.0	40.1
0°-180°	5240.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	8	22	21	22	5
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	

TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4



TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6

TEST NUMBER: P914404

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.49	12.45	12.35	13.33	14.46	11.04	12.00	11.91	12.89	14.01
	3H	13.14	14.00	14.02	14.89	16.04	12.65	13.51	13.53	14.40	15.55
	4H	13.72	14.53	14.61	15.43	16.59	13.22	14.03	14.12	14.94	16.10
	6H	14.11	14.85	15.01	15.77	16.94	13.61	14.36	14.51	15.27	16.44
	8H	14.21	14.92	15.12	15.85	17.02	13.70	14.42	14.62	15.35	16.52
	12H	14.25	14.93	15.17	15.85	17.05	13.74	14.42	14.66	15.34	16.54
4H	2H	11.95	12.76	12.85	13.67	14.82	11.59	12.41	12.49	13.31	14.47
	3H	13.80	14.48	14.71	15.42	16.59	13.39	14.07	14.30	15.01	16.18
	4H	14.50	15.12	15.43	16.05	17.25	14.08	14.70	15.00	15.63	16.83
	6H	15.01	15.54	15.94	16.50	17.69	14.57	15.11	15.51	16.06	17.26
	8H	15.15	15.65	16.09	16.60	17.81	14.71	15.21	15.65	16.16	17.37
	12H	15.22	15.67	16.18	16.63	17.85	14.77	15.22	15.73	16.19	17.40
8H	4H	14.70	15.20	15.64	16.15	17.36	14.32	14.82	15.26	15.77	16.98
	6H	15.31	15.72	16.27	16.71	17.92	14.92	15.34	15.89	16.33	17.54
	8H	15.52	15.88	16.49	16.86	18.09	15.12	15.49	16.10	16.47	17.70
	12H	15.64	15.96	16.62	16.93	18.21	15.23	15.55	16.21	16.52	17.80
12H	4H	14.68	15.14	15.64	16.10	17.32	14.31	14.77	15.27	15.73	16.95
	6H	15.33	15.70	16.31	16.68	17.91	14.96	15.33	15.93	16.31	17.54
	8H	15.57	15.89	16.54	16.86	18.14	15.18	15.51	16.16	16.48	17.76