

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925237

Luminaire Tested: DFN2DIP-PN4F0-110D080US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925237
REPORT IS A COMBINATION OF REPORTS P901215 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D080US950-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17944.8 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 172.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	54	50	51	47	44	44	41	38
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	50	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2981	2981	2981
5°	2985	2939	2959
10°	2961	2900	2920
15°	2918	2853	2858
20°	2859	2787	2794
25°	2800	2708	2721
30°	2727	2635	2627
35°	2657	2548	2528
40°	2572	2460	2434
45°	2487	2373	2337
50°	2393	2281	2226
55°	2296	2174	2123
60°	2185	2048	2005
65°	2065	1917	1867
70°	1911	1758	1718
75°	1699	1567	1581
80°	1444	1324	1319
85°	1044	903	882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2487 cd/sqm

TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.3	2.1
10°-20°	1081.3	6.0
20°-30°	1589.1	8.9
30°-40°	1845.7	10.3
40°-50°	1843.4	10.3
50°-60°	1607.4	9.0
60°-70°	1188.2	6.6
70°-80°	672.3	3.7
80°-90°	182.0	1.0
90°-100°	84.9	0.5
100°-110°	316.6	1.8
110°-120°	839.7	4.7
120°-130°	1392.7	7.8
130°-140°	1479.4	8.2
140°-150°	1374.9	7.7
150°-160°	1105.4	6.2
160°-170°	712.3	4.0
170°-180°	245.2	1.4
0°-30°	3054.8	17.0
0°-40°	4900.4	27.3
0°-60°	8351.2	46.5
0°-90°	10393.6	57.9
90°-120°	1241.3	6.9
90°-150°	5488.3	30.6
90°-180°	7551.0	42.1
0°-180°	17944.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4083	4083	4083	4083	4083	
5°	4083	4068	4024	4056	4048	388
15°	3887	3864	3812	3828	3809	1095
25°	3518	3487	3420	3428	3420	1619
35°	3035	2996	2933	2909	2890	1895
45°	2470	2442	2383	2340	2324	1906
55°	1869	1845	1798	1751	1732	1671
65°	1260	1237	1198	1162	1143	1246
75°	659	652	632	609	617	704
85°	161	157	153	141	138	179
90°	2	22	37	47	50	17
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	

TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4083.3	4083.3	4083.3	4083.3	4083.3
2.5°	4107.0	4087.4	4044.1	4083.3	4075.8
5°	4083.3	4067.9	4024.5	4055.7	4048.3
7.5°	4055.7	4032.5	3989.2	4020.8	4012.9
10°	4012.9	3985.3	3938.3	3969.5	3957.9
12.5°	3953.8	3930.4	3883.4	3902.9	3895.0
15°	3887.1	3863.7	3812.5	3828.3	3808.7
17.5°	3804.6	3781.3	3730.0	3749.6	3730.0
20°	3714.2	3690.8	3635.9	3647.5	3632.2
22.5°	3624.2	3588.8	3537.5	3537.5	3529.6
25°	3518.0	3486.8	3420.1	3427.6	3420.1
27.5°	3400.1	3372.6	3321.7	3310.1	3290.5
30°	3282.6	3250.9	3192.2	3180.5	3164.7
32.5°	3156.8	3133.5	3070.5	3046.8	3031.0
35°	3035.2	2996.0	2933.1	2909.3	2889.8
37.5°	2897.7	2862.3	2799.4	2771.8	2752.3
40°	2756.5	2724.8	2661.9	2626.9	2611.1
42.5°	2619.0	2587.3	2524.9	2485.3	2462.0
45°	2469.9	2442.3	2383.2	2340.4	2324.5
47.5°	2324.5	2297.0	2234.1	2190.8	2167.4
50°	2171.2	2151.7	2096.6	2041.7	2022.1
52.5°	2022.1	1994.5	1943.8	1900.4	1872.9
55°	1869.2	1845.4	1798.4	1751.3	1731.7
57.5°	1715.9	1696.3	1645.1	1597.9	1582.1
60°	1562.6	1547.2	1492.2	1448.8	1437.2
62.5°	1413.4	1386.0	1346.8	1307.6	1291.8
65°	1260.5	1236.8	1197.7	1162.3	1142.7
67.5°	1103.5	1083.6	1048.5	1021.1	1005.2
70°	958.1	942.3	906.9	879.4	863.9
72.5°	809.0	793.2	773.6	746.1	734.4
75°	659.4	652.0	631.9	608.7	616.6
77.5°	526.1	510.3	502.4	490.7	479.1
80°	392.9	388.7	380.7	369.1	361.2
82.5°	267.0	267.0	263.3	247.5	247.5
85°	160.8	157.0	153.3	141.2	137.5
87.5°	70.8	62.9	55.0	43.3	39.1
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2

TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7

TEST NUMBER: P925237

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.77	12.71	12.66	13.62	14.77	11.33	12.27	12.22	13.18	14.33
	3H	13.44	14.28	14.34	15.20	16.38	12.96	13.80	13.86	14.72	15.89
	4H	14.04	14.83	14.95	15.75	16.94	13.55	14.34	14.46	15.27	16.45
	6H	14.44	15.18	15.37	16.10	17.30	13.95	14.68	14.88	15.61	16.81
	8H	14.55	15.25	15.48	16.19	17.39	14.06	14.76	14.99	15.70	16.90
	12H	14.60	15.27	15.54	16.21	17.43	14.10	14.77	15.04	15.71	16.93
4H	2H	12.24	13.04	13.16	13.96	15.15	11.89	12.69	12.81	13.61	14.80
	3H	14.12	14.78	15.05	15.74	16.94	13.72	14.38	14.65	15.33	16.54
	4H	14.84	15.45	15.78	16.39	17.62	14.42	15.03	15.36	15.98	17.20
	6H	15.36	15.89	16.32	16.86	18.08	14.94	15.46	15.89	16.43	17.66
	8H	15.52	16.00	16.47	16.97	18.21	15.09	15.58	16.04	16.54	17.78
	12H	15.59	16.03	16.57	17.02	18.26	15.15	15.59	16.13	16.58	17.82
8H	4H	15.04	15.53	16.00	16.50	17.74	14.67	15.16	15.63	16.13	17.37
	6H	15.68	16.09	16.66	17.09	18.33	15.30	15.71	16.29	16.72	17.96
	8H	15.90	16.26	16.90	17.26	18.52	15.52	15.88	16.51	16.87	18.13
	12H	16.04	16.36	17.04	17.35	18.65	15.64	15.95	16.63	16.94	18.25
12H	4H	15.03	15.47	16.01	16.46	17.70	14.67	15.11	15.65	16.09	17.34
	6H	15.71	16.07	16.70	17.07	18.32	15.35	15.70	16.34	16.70	17.96
	8H	15.96	16.27	16.95	17.26	18.57	15.59	15.90	16.58	16.89	18.20