

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914500

Luminaire Tested: DFN2DIP-SQ2F0-080D030US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914500
REPORT IS A COMBINATION OF REPORTS P899781 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D030US927-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8377.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 101.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5422	5422	5422
5°	5422	5335	5375
10°	5368	5251	5295
15°	5280	5153	5174
20°	5164	5021	5050
25°	5048	4866	4908
30°	4905	4721	4729
35°	4769	4551	4541
40°	4604	4380	4361
45°	4438	4207	4177
50°	4256	4025	3964
55°	4065	3815	3766
60°	3848	3568	3540
65°	3611	3310	3273
70°	3309	2995	2984
75°	2895	2618	2706
80°	2392	2138	2198
85°	1615	1350	1381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4438 cd/sqm

TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	2.8
10°-20°	653.0	7.8
20°-30°	959.7	11.5
30°-40°	1114.6	13.3
40°-50°	1113.2	13.3
50°-60°	970.7	11.6
60°-70°	717.6	8.6
70°-80°	406.0	4.8
80°-90°	109.3	1.3
90°-100°	46.5	0.6
100°-110°	147.8	1.8
110°-120°	252.9	3.0
120°-130°	332.6	4.0
130°-140°	373.3	4.5
140°-150°	366.1	4.4
150°-160°	307.1	3.7
160°-170°	203.7	2.4
170°-180°	71.2	0.8
0°-30°	1844.8	22.0
0°-40°	2959.4	35.3
0°-60°	5043.4	60.2
0°-90°	6276.2	74.9
90°-120°	447.2	5.3
90°-150°	1519.2	18.1
90°-180°	2101.0	25.1
0°-180°	8377.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2466	2466	2466	2466	2466	
5°	2466	2457	2430	2449	2445	234
15°	2348	2333	2302	2312	2300	661
25°	2125	2106	2066	2070	2066	978
35°	1833	1809	1771	1757	1745	1145
45°	1492	1475	1439	1413	1404	1151
55°	1129	1114	1086	1058	1046	1009
65°	761	747	723	702	690	753
75°	398	394	382	368	372	425
85°	97	95	93	85	83	108
90°	1	8	22	21	22	8
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	

TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.9	2465.9	2465.9	2465.9	2465.9
2.5°	2480.2	2468.4	2442.3	2465.9	2461.4
5°	2465.9	2456.6	2430.5	2449.3	2444.8
7.5°	2449.3	2435.2	2409.1	2428.2	2423.4
10°	2423.4	2406.8	2378.4	2397.2	2390.2
12.5°	2387.7	2373.6	2345.2	2357.0	2352.2
15°	2347.5	2333.4	2302.4	2312.0	2300.2
17.5°	2297.6	2283.5	2252.6	2264.4	2252.6
20°	2243.1	2229.0	2195.8	2202.8	2193.5
22.5°	2188.7	2167.3	2136.4	2136.4	2131.6
25°	2124.6	2105.7	2065.5	2070.0	2065.5
27.5°	2053.3	2036.8	2006.0	1999.0	1987.2
30°	1982.4	1963.3	1927.9	1920.8	1911.2
32.5°	1906.5	1892.4	1854.3	1840.0	1830.5
35°	1832.9	1809.3	1771.3	1757.0	1745.2
37.5°	1749.9	1728.5	1690.6	1674.0	1662.2
40°	1664.7	1645.5	1607.6	1586.4	1576.8
42.5°	1581.7	1562.5	1524.8	1500.9	1486.8
45°	1491.6	1475.0	1439.2	1413.3	1403.8
47.5°	1403.8	1387.2	1349.2	1323.0	1308.9
50°	1311.2	1299.4	1266.1	1233.0	1221.1
52.5°	1221.1	1204.5	1173.9	1147.7	1131.1
55°	1128.8	1114.4	1086.1	1057.6	1045.8
57.5°	1036.3	1024.4	993.5	965.0	955.4
60°	943.6	934.4	901.1	875.0	867.9
62.5°	853.6	837.0	813.3	789.7	780.1
65°	761.3	746.9	723.3	701.9	690.1
67.5°	666.4	654.3	633.2	616.6	607.0
70°	578.6	569.0	547.7	531.1	521.7
72.5°	488.5	479.0	467.1	450.6	443.5
75°	398.2	393.7	381.7	367.6	372.3
77.5°	317.7	308.2	303.4	296.4	289.3
80°	237.3	234.7	230.0	222.9	218.1
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4



TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6

TEST NUMBER: P914500

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.07	16.21	15.78	16.94	17.80	14.63	15.77	15.33	16.49	17.36
	3H	16.73	17.76	17.45	18.50	19.39	16.24	17.27	16.96	18.01	18.90
	4H	17.32	18.29	18.06	19.03	19.94	16.82	17.79	17.57	18.54	19.45
	6H	17.72	18.61	18.47	19.37	20.29	17.22	18.11	17.97	18.87	19.79
	8H	17.82	18.67	18.59	19.45	20.38	17.32	18.17	18.09	18.95	19.88
	12H	17.87	18.69	18.64	19.46	20.41	17.36	18.18	18.13	18.95	19.90
4H	2H	15.55	16.52	16.30	17.27	18.18	15.20	16.16	15.94	16.91	17.82
	3H	17.42	18.23	18.18	19.01	19.94	17.01	17.82	17.77	18.61	19.53
	4H	18.13	18.87	18.90	19.65	20.61	17.71	18.44	18.48	19.23	20.18
	6H	18.64	19.28	19.43	20.09	21.05	18.21	18.85	19.00	19.66	20.62
	8H	18.79	19.39	19.58	20.19	21.17	18.35	18.95	19.15	19.75	20.73
	12H	18.87	19.40	19.68	20.23	21.21	18.42	18.95	19.23	19.78	20.76
8H	4H	18.34	18.93	19.13	19.74	20.71	17.96	18.56	18.75	19.36	20.34
	6H	18.96	19.45	19.78	20.30	21.27	18.57	19.07	19.40	19.91	20.89
	8H	19.17	19.61	20.00	20.45	21.44	18.77	19.21	19.61	20.06	21.05
	12H	19.30	19.69	20.14	20.52	21.57	18.89	19.28	19.73	20.11	21.16
12H	4H	18.33	18.87	19.15	19.70	20.68	17.96	18.50	18.78	19.33	20.31
	6H	18.98	19.42	19.82	20.27	21.26	18.61	19.05	19.45	19.90	20.89
	8H	19.22	19.61	20.06	20.45	21.50	18.84	19.23	19.68	20.07	21.11

END OF REPORT