

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925252

Luminaire Tested: DFN2DIP-PN4F0-110D120US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925252
REPORT IS A COMBINATION OF REPORTS P899767 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D120US950-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20520.5 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 217.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925252
CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P925252

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	48	48	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	40	40	40	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	34	34	34	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	30	30	30	26
5	68	57	49	43	63	53	45	40	45	40	35	38	34	30	32	28	26	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	20	20	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2981	2981	2981
5°	2985	2939	2959
10°	2961	2900	2920
15°	2918	2853	2858
20°	2859	2787	2794
25°	2800	2708	2721
30°	2727	2635	2627
35°	2657	2548	2528
40°	2572	2460	2434
45°	2487	2373	2337
50°	2393	2281	2226
55°	2296	2174	2123
60°	2185	2048	2005
65°	2065	1917	1867
70°	1911	1758	1718
75°	1699	1567	1581
80°	1444	1324	1319
85°	1044	903	882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2835 cd/sqm



TEST NUMBER: P925252

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.3	1.9
10°-20°	1081.3	5.3
20°-30°	1589.1	7.7
30°-40°	1845.7	9.0
40°-50°	1843.4	9.0
50°-60°	1607.4	7.8
60°-70°	1188.2	5.8
70°-80°	672.3	3.3
80°-90°	187.7	0.9
90°-100°	224.0	1.1
100°-110°	711.8	3.5
110°-120°	1218.2	5.9
120°-130°	1602.1	7.8
130°-140°	1798.3	8.8
140°-150°	1763.5	8.6
150°-160°	1479.3	7.2
160°-170°	981.0	4.8
170°-180°	342.9	1.7
0°-30°	3054.8	14.9
0°-40°	4900.4	23.9
0°-60°	8351.2	40.7
0°-90°	10399.4	50.7
90°-120°	2154.1	10.5
90°-150°	7318.0	35.7
90°-180°	10121.0	49.3
0°-180°	20520.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4083	4083	4083	4083	4083	
5°	4083	4068	4024	4056	4048	388
15°	3887	3864	3812	3828	3809	1095
25°	3518	3487	3420	3428	3420	1619
35°	3035	2996	2933	2909	2890	1895
45°	2470	2442	2383	2340	2324	1906
55°	1869	1845	1798	1751	1732	1671
65°	1260	1237	1198	1162	1143	1246
75°	659	652	632	609	617	704
85°	161	157	153	141	138	179
90°	3	39	107	100	104	20
95°	159	190	195	195	190	177
105°	657	666	672	678	678	693
115°	1222	1240	1234	1231	1222	1209
125°	1778	1805	1797	1787	1784	1589
135°	2300	2334	2340	2337	2328	1778
145°	2792	2814	2831	2835	2823	1745
155°	3193	3201	3211	3226	3217	1470
165°	3473	3470	3470	3492	3476	980
175°	3614	3605	3599	3620	3602	343
180°	3620	3620	3620	3620	3620	



TEST NUMBER: P925252

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4083.3	4083.3	4083.3	4083.3	4083.3
2.5°	4107.0	4087.4	4044.1	4083.3	4075.8
5°	4083.3	4067.9	4024.5	4055.7	4048.3
7.5°	4055.7	4032.5	3989.2	4020.8	4012.9
10°	4012.9	3985.3	3938.3	3969.5	3957.9
12.5°	3953.8	3930.4	3883.4	3902.9	3895.0
15°	3887.1	3863.7	3812.5	3828.3	3808.7
17.5°	3804.6	3781.3	3730.0	3749.6	3730.0
20°	3714.2	3690.8	3635.9	3647.5	3632.2
22.5°	3624.2	3588.8	3537.5	3537.5	3529.6
25°	3518.0	3486.8	3420.1	3427.6	3420.1
27.5°	3400.1	3372.6	3321.7	3310.1	3290.5
30°	3282.6	3250.9	3192.2	3180.5	3164.7
32.5°	3156.8	3133.5	3070.5	3046.8	3031.0
35°	3035.2	2996.0	2933.1	2909.3	2889.8
37.5°	2897.7	2862.3	2799.4	2771.8	2752.3
40°	2756.5	2724.8	2661.9	2626.9	2611.1
42.5°	2619.0	2587.3	2524.9	2485.3	2462.0
45°	2469.9	2442.3	2383.2	2340.4	2324.5
47.5°	2324.5	2297.0	2234.1	2190.8	2167.4
50°	2171.2	2151.7	2096.6	2041.7	2022.1
52.5°	2022.1	1994.5	1943.8	1900.4	1872.9
55°	1869.2	1845.4	1798.4	1751.3	1731.7
57.5°	1715.9	1696.3	1645.1	1597.9	1582.1
60°	1562.6	1547.2	1492.2	1448.8	1437.2
62.5°	1413.4	1386.0	1346.8	1307.6	1291.8
65°	1260.5	1236.8	1197.7	1162.3	1142.7
67.5°	1103.5	1083.6	1048.5	1021.1	1005.2
70°	958.1	942.3	906.9	879.4	863.9
72.5°	809.0	793.2	773.6	746.1	734.4
75°	659.4	652.0	631.9	608.7	616.6
77.5°	526.1	510.3	502.4	490.7	479.1
80°	392.9	388.7	380.7	369.1	361.2
82.5°	267.0	267.0	263.3	247.5	247.5
85°	160.8	157.0	153.3	141.2	137.5
87.5°	70.8	62.9	55.0	43.3	39.1
90°	3.2	39.3	106.9	100.5	103.7
92.5°	67.6	91.7	94.9	98.3	98.3
95°	159.3	189.9	195.4	195.4	189.9
97.5°	265.2	293.6	305.7	305.7	305.7
100°	387.5	412.6	421.3	421.3	418.0
102.5°	516.3	534.8	546.8	550.2	546.8
105°	657.1	665.8	672.4	677.8	677.8
107.5°	796.8	809.9	809.9	812.0	796.8
110°	932.2	949.6	949.6	949.6	940.9



TEST NUMBER: P925252

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1078.4	1097.0	1093.7	1085.0	1078.4
115°	1222.5	1240.0	1234.5	1231.2	1222.5
117.5°	1365.5	1389.5	1374.2	1365.5	1356.8
120°	1509.6	1533.6	1509.6	1509.6	1499.8
122.5°	1640.6	1671.1	1655.9	1647.1	1640.6
125°	1778.1	1805.3	1796.7	1786.8	1783.5
127.5°	1912.4	1946.2	1934.1	1921.1	1912.4
130°	2037.8	2077.1	2071.7	2065.1	2053.1
132.5°	2178.6	2209.3	2211.4	2196.1	2187.4
135°	2299.8	2333.7	2340.3	2336.9	2328.2
137.5°	2435.2	2462.5	2467.9	2465.7	2452.6
140°	2554.1	2581.4	2596.7	2596.7	2584.7
142.5°	2676.4	2703.7	2712.4	2715.7	2703.7
145°	2792.1	2813.9	2831.4	2834.7	2822.7
147.5°	2895.8	2923.1	2936.2	2941.7	2929.6
150°	3002.8	3021.3	3033.3	3043.2	3033.3
152.5°	3097.7	3116.2	3131.6	3143.6	3131.6
155°	3192.7	3201.4	3211.3	3226.5	3216.7
157.5°	3274.6	3281.1	3286.5	3308.4	3293.1
160°	3347.7	3354.3	3357.5	3376.1	3362.9
162.5°	3415.3	3415.3	3418.7	3439.4	3424.1
165°	3473.2	3470.0	3470.0	3491.7	3476.5
167.5°	3525.6	3515.8	3515.8	3537.6	3522.4
170°	3564.9	3556.1	3552.9	3574.7	3556.1
172.5°	3592.2	3583.4	3580.2	3602.0	3583.4
175°	3614.0	3605.3	3598.8	3620.5	3602.0
177.5°	3626.1	3617.3	3610.7	3629.3	3610.7
180°	3620.5	3620.5	3620.5	3620.5	3620.5



TEST NUMBER: P925252
 CATALOG NUMBER: DFN2DIP-PN4F0-110D120US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.13	12.00	12.09	12.97	14.23	10.69	11.56	11.65	12.53	13.79
	3H	12.80	13.58	13.76	14.55	15.84	12.31	13.09	13.28	14.07	15.35
	4H	13.39	14.12	14.36	15.10	16.40	12.90	13.64	13.88	14.62	15.91
	6H	13.79	14.47	14.78	15.45	16.76	13.30	13.98	14.29	14.96	16.27
	8H	13.90	14.54	14.89	15.55	16.85	13.40	14.05	14.40	15.05	16.35
	12H	13.95	14.56	14.95	15.56	16.88	13.45	14.06	14.45	15.06	16.38
4H	2H	11.60	12.33	12.58	13.31	14.61	11.25	11.98	12.23	12.96	14.25
	3H	13.47	14.08	14.46	15.09	16.40	13.06	13.68	14.06	14.69	15.99
	4H	14.18	14.75	15.18	15.75	17.08	13.77	14.33	14.77	15.33	16.66
	6H	14.70	15.19	15.71	16.21	17.54	14.28	14.76	15.29	15.79	17.11
	8H	14.85	15.31	15.87	16.32	17.67	14.42	14.88	15.44	15.90	17.24
	12H	14.93	15.34	15.96	16.37	17.72	14.49	14.90	15.52	15.93	17.28
8H	4H	14.38	14.83	15.39	15.85	17.19	14.01	14.46	15.02	15.48	16.82
	6H	15.02	15.39	16.05	16.45	17.79	14.64	15.01	15.68	16.07	17.41
	8H	15.24	15.57	16.28	16.61	17.97	14.85	15.18	15.90	16.23	17.59
	12H	15.37	15.66	16.42	16.70	18.11	14.97	15.26	16.02	16.30	17.70
12H	4H	14.37	14.78	15.40	15.81	17.16	14.00	14.41	15.04	15.45	16.80
	6H	15.05	15.38	16.09	16.42	17.78	14.68	15.01	15.73	16.06	17.42
	8H	15.29	15.58	16.34	16.62	18.02	14.92	15.21	15.97	16.25	17.65