

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917113

Luminaire Tested: DFN2DIP-SQ2F0-030D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917113
REPORT IS A COMBINATION OF REPORTS P901303 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D040US930-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5650.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2093	2093	2093
5°	2092	2059	2074
10°	2072	2027	2043
15°	2038	1989	1997
20°	1993	1938	1949
25°	1948	1878	1894
30°	1893	1822	1825
35°	1841	1756	1752
40°	1777	1690	1683
45°	1713	1624	1612
50°	1643	1553	1530
55°	1569	1472	1454
60°	1485	1377	1366
65°	1394	1278	1264
70°	1277	1156	1152
75°	1117	1010	1045
80°	923	824	849
85°	624	520	532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1713 cd/sqm

TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.6
10°-20°	252.0	4.5
20°-30°	370.4	6.6
30°-40°	430.2	7.6
40°-50°	429.7	7.6
50°-60°	374.6	6.6
60°-70°	277.0	4.9
70°-80°	156.7	2.8
80°-90°	43.3	0.8
90°-100°	36.3	0.6
100°-110°	135.3	2.4
110°-120°	358.8	6.4
120°-130°	595.1	10.5
130°-140°	632.1	11.2
140°-150°	587.5	10.4
150°-160°	472.3	8.4
160°-170°	304.4	5.4
170°-180°	104.8	1.9
0°-30°	712.0	12.6
0°-40°	1142.2	20.2
0°-60°	1946.5	34.5
0°-90°	2423.4	42.9
90°-120°	530.4	9.4
90°-150°	2345.2	41.5
90°-180°	3227.0	57.1
0°-180°	5650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	1	10	16	20	21	5
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9

TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P917113

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.03	9.83	10.04	10.85	12.22	8.58	9.38	9.60	10.41	11.78
	3H	10.66	11.38	11.69	12.42	13.80	10.17	10.89	11.20	11.93	13.32
	4H	11.24	11.92	12.27	12.95	14.35	10.74	11.42	11.78	12.46	13.86
	6H	11.62	12.24	12.67	13.28	14.69	11.12	11.74	12.17	12.79	14.19
	8H	11.71	12.31	12.77	13.37	14.77	11.21	11.81	12.27	12.87	14.27
	12H	11.75	12.32	12.81	13.37	14.80	11.24	11.81	12.30	12.86	14.29
4H	2H	9.47	10.15	10.52	11.19	12.58	9.11	9.80	10.16	10.83	12.23
	3H	11.31	11.88	12.36	12.94	14.35	10.90	11.47	11.95	12.53	13.94
	4H	12.00	12.52	13.06	13.58	15.01	11.58	12.10	12.64	13.16	14.59
	6H	12.50	12.94	13.57	14.02	15.45	12.07	12.51	13.13	13.59	15.02
	8H	12.64	13.05	13.71	14.13	15.57	12.20	12.62	13.27	13.69	15.13
	12H	12.70	13.08	13.78	14.16	15.61	12.25	12.63	13.34	13.71	15.16
8H	4H	12.18	12.60	13.25	13.67	15.12	11.81	12.22	12.88	13.30	14.74
	6H	12.79	13.13	13.88	14.25	15.69	12.40	12.75	13.50	13.86	15.30
	8H	13.00	13.30	14.10	14.40	15.85	12.60	12.91	13.70	14.00	15.46
	12H	13.11	13.38	14.21	14.47	15.97	12.70	12.97	13.80	14.06	15.56
12H	4H	12.16	12.54	13.25	13.63	15.08	11.80	12.17	12.88	13.26	14.71
	6H	12.81	13.12	13.91	14.21	15.67	12.44	12.74	13.54	13.84	15.30
	8H	13.04	13.30	14.14	14.40	15.89	12.66	12.92	13.76	14.01	15.51

END OF REPORT