

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917129

Luminaire Tested: DFN2DIP-SQ2F0-030D080US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917129
REPORT IS A COMBINATION OF REPORTS P901351 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US930-FLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8878.6 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917129
CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P917129

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23				23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21	16				16
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18	14				14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16	12				12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11				11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9				9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8				8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10	8				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2093	2093	2093
5°	2092	2059	2074
10°	2072	2027	2043
15°	2038	1989	1997
20°	1993	1938	1949
25°	1948	1878	1894
30°	1893	1822	1825
35°	1841	1756	1752
40°	1777	1690	1683
45°	1713	1624	1612
50°	1643	1553	1530
55°	1569	1472	1454
60°	1485	1377	1366
65°	1394	1278	1264
70°	1277	1156	1152
75°	1117	1010	1045
80°	923	824	849
85°	624	520	532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2092 cd/sqm



TEST NUMBER: P917129

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.0
10°-20°	252.0	2.8
20°-30°	370.4	4.2
30°-40°	430.2	4.8
40°-50°	429.7	4.8
50°-60°	374.6	4.2
60°-70°	277.0	3.1
70°-80°	156.7	1.8
80°-90°	45.2	0.5
90°-100°	72.6	0.8
100°-110°	270.6	3.0
110°-120°	717.6	8.1
120°-130°	1190.2	13.4
130°-140°	1264.3	14.2
140°-150°	1175.0	13.2
150°-160°	944.7	10.6
160°-170°	608.7	6.9
170°-180°	209.5	2.4
0°-30°	712.0	8.0
0°-40°	1142.2	12.9
0°-60°	1946.5	21.9
0°-90°	2425.3	27.3
90°-120°	1060.8	11.9
90°-150°	4690.4	52.8
90°-180°	6453.0	72.7
0°-180°	8878.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	2	19	32	40	43	8
95°	104	51	62	70	68	123
105°	484	532	97	115	121	517
115°	916	943	983	245	131	902
125°	1295	1316	1346	1357	1362	1155
135°	1602	1628	1642	1658	1655	1238
145°	1859	1857	1884	1895	1887	1163
155°	2047	2032	2052	2061	2048	943
165°	2157	2147	2152	2163	2152	609
175°	2206	2195	2198	2209	2193	210
180°	2201	2201	2201	2201	2201	



TEST NUMBER: P917129

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.5	50.9	62.0	70.2	68.5
97.5°	186.3	55.8	81.1	86.1	87.6
100°	282.0	63.8	90.8	103.5	106.6
102.5°	387.0	383.9	94.0	111.4	116.3
105°	484.2	532.1	97.2	114.6	121.1
107.5°	597.3	637.0	100.4	117.8	124.3
110°	705.7	739.0	278.8	119.5	125.8



TEST NUMBER: P917129

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.6	836.2	809.2	122.5	127.5
115°	915.8	942.9	982.8	245.3	130.7
117.5°	1009.8	1041.6	1068.9	840.9	423.7
120°	1115.0	1138.8	1167.6	1186.7	971.6
122.5°	1204.0	1229.6	1261.6	1271.0	1272.8
125°	1294.9	1315.6	1345.9	1357.1	1361.8
127.5°	1377.7	1400.0	1424.1	1439.9	1441.4
130°	1455.8	1481.3	1498.8	1516.4	1514.8
132.5°	1535.5	1556.2	1573.7	1588.0	1586.5
135°	1602.4	1627.9	1642.1	1658.2	1655.0
137.5°	1672.4	1691.5	1707.6	1723.5	1718.7
140°	1740.8	1753.7	1771.2	1785.5	1777.5
142.5°	1798.4	1809.5	1830.1	1842.8	1834.8
145°	1858.9	1857.2	1884.2	1895.4	1887.4
147.5°	1911.3	1906.6	1933.6	1941.6	1935.3
150°	1962.3	1951.2	1976.7	1986.1	1978.2
152.5°	2005.3	1992.6	2016.4	2026.1	2014.9
155°	2046.7	2032.5	2051.6	2061.1	2048.4
157.5°	2080.2	2067.5	2081.9	2093.0	2080.2
160°	2108.9	2099.3	2108.9	2118.4	2107.2
162.5°	2134.3	2124.8	2132.7	2143.9	2129.6
165°	2156.6	2147.2	2151.9	2163.0	2151.9
167.5°	2174.2	2164.5	2169.4	2180.6	2166.2
170°	2188.6	2178.9	2182.1	2193.3	2178.9
172.5°	2198.0	2188.6	2191.8	2202.9	2188.6
175°	2206.0	2194.8	2198.0	2209.1	2193.3
177.5°	2209.1	2198.0	2199.7	2210.8	2196.5
180°	2201.2	2201.2	2201.2	2201.2	2201.2



TEST NUMBER: P917129
 CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.13	7.82	8.26	8.94	10.50	6.68	7.37	7.81	8.49	10.06
	3H	8.76	9.37	9.89	10.50	12.08	8.27	8.88	9.40	10.01	11.59
	4H	9.32	9.91	10.47	11.04	12.62	8.83	9.41	9.98	10.55	12.13
	6H	9.70	10.24	10.85	11.37	12.96	9.20	9.74	10.35	10.87	12.47
	8H	9.79	10.30	10.95	11.45	13.04	9.29	9.80	10.45	10.95	12.54
	12H	9.83	10.31	10.99	11.45	13.06	9.32	9.80	10.48	10.95	12.56
4H	2H	7.56	8.14	8.71	9.27	10.86	7.20	7.79	8.36	8.92	10.50
	3H	9.38	9.87	10.54	11.03	12.62	8.98	9.47	10.14	10.62	12.22
	4H	10.08	10.53	11.24	11.67	13.28	9.65	10.10	10.81	11.25	12.86
	6H	10.56	10.95	11.73	12.12	13.72	10.13	10.52	11.30	11.68	13.29
	8H	10.70	11.06	11.87	12.22	13.84	10.26	10.62	11.43	11.78	13.40
	12H	10.75	11.08	11.94	12.25	13.88	10.31	10.63	11.49	11.80	13.43
8H	4H	10.25	10.61	11.41	11.77	13.39	9.87	10.23	11.04	11.39	13.01
	6H	10.85	11.14	12.03	12.35	13.96	10.46	10.76	11.65	11.96	13.58
	8H	11.05	11.31	12.24	12.49	14.13	10.66	10.92	11.85	12.10	13.74
	12H	11.16	11.39	12.36	12.57	14.24	10.75	10.98	11.95	12.16	13.83
12H	4H	10.22	10.55	11.40	11.72	13.34	9.85	10.18	11.04	11.35	12.97
	6H	10.87	11.13	12.06	12.31	13.95	10.50	10.76	11.69	11.93	13.57
	8H	11.09	11.32	12.28	12.49	14.16	10.71	10.93	11.90	12.11	13.78