

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903490

Luminaire Tested: DFN2DIP-SQ2F0-030D080US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903490
REPORT IS A COMBINATION OF REPORTS P899832 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US830-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9076.7 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2570	2570	2570
5°	2569	2523	2541
10°	2539	2468	2455
15°	2500	2381	2324
20°	2449	2264	2164
25°	2398	2133	2010
30°	2329	1999	1816
35°	2262	1856	1646
40°	2194	1709	1451
45°	2115	1546	1274
50°	2032	1382	1102
55°	1946	1207	937
60°	1846	1026	768
65°	1731	842	687
70°	1590	670	617
75°	1414	580	554
80°	1162	471	470
85°	755	293	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3323 cd/sqm

TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.2
10°-20°	300.7	3.3
20°-30°	422.1	4.7
30°-40°	460.2	5.1
40°-50°	422.9	4.7
50°-60°	332.2	3.7
60°-70°	216.2	2.4
70°-80°	111.3	1.2
80°-90°	35.2	0.4
90°-100°	147.6	1.6
100°-110°	468.9	5.2
110°-120°	802.4	8.8
120°-130°	1055.3	11.6
130°-140°	1184.5	13.0
140°-150°	1161.5	12.8
150°-160°	974.4	10.7
160°-170°	646.2	7.1
170°-180°	225.9	2.5
0°-30°	832.3	9.2
0°-40°	1292.5	14.2
0°-60°	2047.6	22.6
0°-90°	2410.3	26.6
90°-120°	1418.8	15.6
90°-150°	4820.1	53.1
90°-180°	6666.0	73.4
0°-180°	9076.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	2	26	70	66	68	9
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7

TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7

TEST NUMBER: P903490

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.58	8.25	8.72	9.37	10.95	3.54	4.21	4.68	5.34	6.91
	3H	9.22	9.82	10.37	10.96	12.55	4.70	5.30	5.84	6.43	8.02
	4H	9.81	10.38	10.97	11.52	13.11	5.13	5.70	6.28	6.83	8.42
	6H	10.21	10.73	11.37	11.87	13.47	5.42	5.95	6.59	7.08	8.69
	8H	10.32	10.82	11.49	11.97	13.57	5.50	6.00	6.67	7.15	8.75
	12H	10.37	10.84	11.54	11.99	13.61	5.53	6.00	6.70	7.15	8.77
4H	2H	7.57	8.14	8.74	9.28	10.87	4.10	4.67	5.27	5.81	7.40
	3H	9.36	9.84	10.53	11.00	12.60	5.42	5.89	6.59	7.05	8.66
	4H	10.03	10.47	11.20	11.62	13.24	5.94	6.38	7.11	7.53	9.15
	6H	10.52	10.89	11.70	12.07	13.68	6.33	6.71	7.51	7.88	9.49
	8H	10.68	11.03	11.86	12.19	13.82	6.45	6.80	7.62	7.96	9.59
	12H	10.76	11.07	11.95	12.25	13.88	6.50	6.81	7.69	7.99	9.62
8H	4H	9.98	10.33	11.16	11.50	13.13	6.20	6.55	7.37	7.71	9.34
	6H	10.52	10.81	11.72	12.02	13.64	6.69	6.97	7.88	8.18	9.81
	8H	10.73	10.98	11.93	12.16	13.81	6.86	7.11	8.06	8.30	9.95
	12H	10.84	11.06	12.05	12.24	13.92	6.96	7.18	8.16	8.36	10.04
12H	4H	9.93	10.24	11.12	11.42	13.05	6.19	6.51	7.38	7.68	9.32
	6H	10.50	10.75	11.70	11.93	13.58	6.73	6.98	7.93	8.16	9.81
	8H	10.70	10.92	11.90	12.10	13.78	6.92	7.14	8.12	8.32	10.00

END OF REPORT