

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917175

Luminaire Tested: DFN2DIP-SQ2F0-050D070US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917175
REPORT IS A COMBINATION OF REPORTS P901344 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D070US930-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9115.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39	33		
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28		
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24		
4	73	63	55	50	66	57	51	46	47	42	39	38	34	32	29	27	25	21		
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19		
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20	16		
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	18	15		
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13		
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12		
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3705	3705	3705
5°	3704	3638	3664
10°	3661	3559	3540
15°	3604	3433	3351
20°	3531	3264	3120
25°	3456	3075	2898
30°	3358	2882	2618
35°	3261	2676	2372
40°	3162	2463	2092
45°	3049	2228	1837
50°	2930	1992	1589
55°	2806	1741	1351
60°	2662	1479	1107
65°	2495	1214	991
70°	2293	967	889
75°	2039	837	798
80°	1675	679	676
85°	1090	421	481

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3049 cd/sqm

TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.7
10°-20°	433.5	4.8
20°-30°	608.6	6.7
30°-40°	663.4	7.3
40°-50°	609.7	6.7
50°-60°	478.8	5.3
60°-70°	311.7	3.4
70°-80°	160.4	1.8
80°-90°	44.3	0.5
90°-100°	63.5	0.7
100°-110°	236.8	2.6
110°-120°	627.9	6.9
120°-130°	1041.5	11.4
130°-140°	1106.3	12.1
140°-150°	1028.1	11.3
150°-160°	826.6	9.1
160°-170°	532.6	5.8
170°-180°	183.3	2.0
0°-30°	1200.0	13.2
0°-40°	1863.4	20.4
0°-60°	2951.9	32.4
0°-90°	3468.4	38.1
90°-120°	928.2	10.2
90°-150°	4104.1	45.0
90°-180°	5647.0	62.0
0°-180°	9115.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	1	17	28	35	38	8
95°	90	44	54	61	60	107
105°	424	466	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1178	1188	1192	1010
135°	1402	1424	1437	1451	1448	1083
145°	1626	1625	1649	1658	1652	1017
155°	1791	1778	1795	1803	1792	825
165°	1887	1879	1883	1893	1883	533
175°	1930	1920	1923	1933	1919	184
180°	1926	1926	1926	1926	1926	

TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	163.0	48.8	71.0	75.3	76.6
100°	246.8	55.8	79.4	90.5	93.4
102.5°	338.6	336.0	82.3	97.5	101.7
105°	423.7	465.5	85.0	100.3	105.9
107.5°	522.6	557.4	87.9	103.1	108.8
110°	617.5	646.6	243.9	104.6	110.1

TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.7	731.6	708.0	107.2	111.5
115°	801.4	825.0	859.9	214.7	114.4
117.5°	883.6	911.4	935.2	735.8	370.7
120°	975.6	996.5	1021.7	1038.4	850.2
122.5°	1053.5	1075.9	1103.9	1112.1	1113.6
125°	1133.0	1151.2	1177.7	1187.5	1191.6
127.5°	1205.5	1225.0	1246.0	1260.0	1261.3
130°	1273.8	1296.2	1311.4	1326.8	1325.5
132.5°	1343.5	1361.7	1377.0	1389.5	1388.2
135°	1402.1	1424.4	1436.9	1450.9	1448.1
137.5°	1463.3	1480.1	1494.1	1508.1	1503.9
140°	1523.2	1534.5	1549.7	1562.3	1555.3
142.5°	1573.5	1583.3	1601.3	1612.4	1605.5
145°	1626.5	1625.1	1648.7	1658.5	1651.5
147.5°	1672.3	1668.3	1691.9	1698.8	1693.4
150°	1717.0	1707.3	1729.7	1737.9	1731.0
152.5°	1754.6	1743.5	1764.4	1772.8	1763.1
155°	1790.9	1778.4	1795.1	1803.4	1792.4
157.5°	1820.2	1809.1	1821.6	1831.4	1820.2
160°	1845.3	1836.9	1845.3	1853.6	1843.8
162.5°	1867.5	1859.2	1866.1	1875.9	1863.4
165°	1887.0	1878.8	1882.8	1892.6	1882.8
167.5°	1902.4	1893.9	1898.3	1908.0	1895.5
170°	1915.0	1906.6	1909.3	1919.1	1906.6
172.5°	1923.3	1915.0	1917.8	1927.5	1915.0
175°	1930.2	1920.4	1923.3	1933.0	1919.1
177.5°	1933.0	1923.3	1924.8	1934.5	1921.9
180°	1926.1	1926.1	1926.1	1926.1	1926.1

TEST NUMBER: P917175

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.35	11.10	11.41	12.15	13.59	6.31	7.06	7.37	8.11	9.55
	3H	12.00	12.67	13.07	13.73	15.19	7.48	8.14	8.55	9.21	10.66
	4H	12.60	13.22	13.68	14.29	15.75	7.91	8.54	8.99	9.61	11.07
	6H	13.00	13.57	14.09	14.65	16.12	8.21	8.79	9.30	9.86	11.33
	8H	13.11	13.66	14.21	14.75	16.22	8.29	8.84	9.38	9.93	11.39
	12H	13.16	13.69	14.26	14.77	16.26	8.32	8.84	9.42	9.93	11.41
4H	2H	10.36	10.98	11.44	12.05	13.51	6.89	7.52	7.97	8.59	10.04
	3H	12.15	12.68	13.25	13.77	15.25	8.21	8.73	9.30	9.83	11.30
	4H	12.83	13.31	13.93	14.39	15.89	8.74	9.22	9.84	10.30	11.80
	6H	13.32	13.73	14.43	14.84	16.33	9.13	9.54	10.24	10.65	12.14
	8H	13.48	13.87	14.59	14.97	16.47	9.25	9.63	10.35	10.73	12.24
	12H	13.56	13.91	14.68	15.02	16.53	9.30	9.65	10.42	10.76	12.27
8H	4H	12.78	13.17	13.89	14.27	15.77	9.00	9.38	10.11	10.48	11.99
	6H	13.33	13.64	14.45	14.79	16.28	9.49	9.81	10.62	10.95	12.45
	8H	13.53	13.81	14.66	14.93	16.45	9.67	9.94	10.80	11.07	12.59
	12H	13.65	13.89	14.79	15.01	16.57	9.77	10.01	10.90	11.13	12.69
12H	4H	12.73	13.08	13.85	14.19	15.70	9.00	9.34	10.12	10.46	11.97
	6H	13.30	13.58	14.43	14.70	16.22	9.53	9.81	10.67	10.94	12.45
	8H	13.50	13.74	14.64	14.87	16.42	9.72	9.97	10.86	11.09	12.64

END OF REPORT