

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917185

Luminaire Tested: DFN2DIP-SQ2F0-060D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917185
REPORT IS A COMBINATION OF REPORTS P901309 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-060D040US930-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8071.4 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4185	4185	4185
5°	4185	4118	4149
10°	4144	4053	4087
15°	4075	3978	3993
20°	3986	3876	3898
25°	3897	3756	3788
30°	3786	3644	3650
35°	3682	3513	3505
40°	3553	3381	3366
45°	3426	3247	3224
50°	3285	3107	3060
55°	3138	2945	2907
60°	2971	2754	2732
65°	2787	2555	2526
70°	2554	2312	2304
75°	2235	2021	2089
80°	1846	1650	1697
85°	1246	1041	1066

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3426 cd/sqm

TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.2
10°-20°	504.1	6.2
20°-30°	740.8	9.2
30°-40°	860.4	10.7
40°-50°	859.3	10.6
50°-60°	749.3	9.3
60°-70°	553.9	6.9
70°-80°	313.4	3.9
80°-90°	84.6	1.0
90°-100°	36.3	0.4
100°-110°	135.3	1.7
110°-120°	358.8	4.4
120°-130°	595.1	7.4
130°-140°	632.1	7.8
140°-150°	587.5	7.3
150°-160°	472.3	5.9
160°-170°	304.4	3.8
170°-180°	104.8	1.3
0°-30°	1424.0	17.6
0°-40°	2284.3	28.3
0°-60°	3892.9	48.2
0°-90°	4844.8	60.0
90°-120°	530.4	6.6
90°-150°	2345.2	29.1
90°-180°	3227.0	40.0
0°-180°	8071.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	1	10	16	20	21	7
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9

TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P917185

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.01	13.97	13.87	14.85	15.98	12.56	13.52	13.43	14.41	15.53
	3H	14.66	15.52	15.53	16.41	17.56	14.17	15.03	15.04	15.92	17.07
	4H	15.24	16.05	16.13	16.95	18.11	14.74	15.56	15.64	16.46	17.61
	6H	15.63	16.38	16.53	17.29	18.45	15.13	15.88	16.03	16.79	17.95
	8H	15.73	16.44	16.64	17.37	18.54	15.22	15.94	16.14	16.87	18.03
	12H	15.77	16.45	16.69	17.37	18.57	15.26	15.94	16.18	16.86	18.06
4H	2H	13.47	14.28	14.37	15.19	16.34	13.11	13.93	14.01	14.83	15.99
	3H	15.32	16.00	16.23	16.94	18.11	14.91	15.59	15.82	16.53	17.70
	4H	16.02	16.64	16.95	17.57	18.77	15.60	16.22	16.52	17.15	18.35
	6H	16.53	17.06	17.46	18.02	19.21	16.09	16.63	17.03	17.58	18.78
	8H	16.67	17.17	17.61	18.12	19.33	16.23	16.73	17.17	17.68	18.89
	12H	16.74	17.19	17.69	18.15	19.37	16.29	16.74	17.25	17.71	18.92
8H	4H	16.22	16.72	17.15	17.66	18.88	15.84	16.34	16.78	17.29	18.50
	6H	16.83	17.24	17.79	18.23	19.44	16.44	16.86	17.41	17.85	19.06
	8H	17.04	17.40	18.01	18.38	19.61	16.64	17.01	17.62	17.99	19.22
	12H	17.16	17.48	18.14	18.45	19.73	16.75	17.07	17.73	18.04	19.32
12H	4H	16.21	16.66	17.16	17.62	18.84	15.84	16.29	16.79	17.25	18.47
	6H	16.85	17.22	17.83	18.20	19.43	16.48	16.85	17.45	17.83	19.05
	8H	17.09	17.41	18.06	18.38	19.66	16.70	17.03	17.68	18.00	19.28