

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903533

Luminaire Tested: DFN2DIP-SQ2F0-050D070US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903533
REPORT IS A COMBINATION OF REPORTS P901343 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D070US830-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11197.4 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	87	84	80	78	69	67	65	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4032	4032	4032
5°	4032	3967	3997
10°	3992	3905	3937
15°	3926	3832	3847
20°	3840	3734	3755
25°	3754	3619	3649
30°	3648	3510	3517
35°	3547	3384	3377
40°	3423	3257	3243
45°	3300	3128	3106
50°	3165	2993	2947
55°	3023	2837	2801
60°	2862	2653	2633
65°	2685	2461	2434
70°	2461	2227	2219
75°	2153	1947	2013
80°	1778	1589	1635
85°	1201	1003	1026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3300 cd/sqm

TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.6	1.5
10°-20°	485.6	4.3
20°-30°	713.7	6.4
30°-40°	828.9	7.4
40°-50°	827.8	7.4
50°-60°	721.8	6.4
60°-70°	533.6	4.8
70°-80°	301.9	2.7
80°-90°	83.6	0.7
90°-100°	73.4	0.7
100°-110°	273.7	2.4
110°-120°	725.9	6.5
120°-130°	1204.0	10.8
130°-140°	1278.9	11.4
140°-150°	1188.6	10.6
150°-160°	955.6	8.5
160°-170°	615.8	5.5
170°-180°	211.9	1.9
0°-30°	1371.9	12.3
0°-40°	2200.7	19.7
0°-60°	3750.4	33.5
0°-90°	4669.5	41.7
90°-120°	1073.0	9.6
90°-150°	4744.6	42.4
90°-180°	6528.0	58.3
0°-180°	11197.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	2	19	32	40	44	10
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	

TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2

TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7

TEST NUMBER: P903533

CATALOG NUMBER: DFN2DIP-SQ2F0-050D070US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.18	11.97	12.21	13.01	14.39	10.74	11.53	11.76	12.56	13.95
	3H	12.82	13.53	13.85	14.57	15.97	12.33	13.04	13.36	14.08	15.48
	4H	13.39	14.06	14.44	15.11	16.52	12.90	13.57	13.94	14.61	16.02
	6H	13.77	14.39	14.83	15.44	16.86	13.27	13.89	14.33	14.94	16.36
	8H	13.87	14.46	14.93	15.52	16.94	13.36	13.95	14.43	15.02	16.44
	12H	13.90	14.46	14.97	15.52	16.97	13.40	13.96	14.46	15.01	16.46
4H	2H	11.62	12.30	12.68	13.34	14.75	11.27	11.94	12.32	12.99	14.40
	3H	13.46	14.02	14.52	15.09	16.52	13.05	13.61	14.11	14.69	16.11
	4H	14.16	14.67	15.22	15.73	17.18	13.73	14.25	14.80	15.31	16.76
	6H	14.65	15.09	15.73	16.18	17.62	14.22	14.66	15.29	15.75	17.19
	8H	14.79	15.20	15.87	16.28	17.74	14.35	14.76	15.43	15.84	17.30
	12H	14.85	15.22	15.94	16.31	17.78	14.40	14.77	15.50	15.87	17.33
8H	4H	14.34	14.75	15.41	15.83	17.28	13.96	14.37	15.04	15.45	16.91
	6H	14.94	15.28	16.04	16.40	17.86	14.56	14.90	15.66	16.02	17.47
	8H	15.15	15.45	16.25	16.55	18.02	14.75	15.05	15.86	16.16	17.63
	12H	15.26	15.53	16.37	16.62	18.14	14.85	15.12	15.96	16.21	17.73
12H	4H	14.32	14.69	15.41	15.78	17.24	13.95	14.32	15.04	15.41	16.87
	6H	14.96	15.26	16.07	16.37	17.84	14.59	14.89	15.70	15.99	17.47
	8H	15.19	15.45	16.30	16.55	18.06	14.81	15.07	15.92	16.17	17.68