

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903537

Luminaire Tested: DFN2DIP-SQ2F0-050D080US830-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903537  
REPORT IS A COMBINATION OF REPORTS P901355 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-050D080US830-FLLONL  
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12130.5 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 109.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903537  
CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P903537

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38				38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4032	4032	4032
5°	4032	3967	3997
10°	3992	3905	3937
15°	3926	3832	3847
20°	3840	3734	3755
25°	3754	3619	3649
30°	3648	3510	3517
35°	3547	3384	3377
40°	3423	3257	3243
45°	3300	3128	3106
50°	3165	2993	2947
55°	3023	2837	2801
60°	2862	2653	2633
65°	2685	2461	2434
70°	2461	2227	2219
75°	2153	1947	2013
80°	1778	1589	1635
85°	1201	1003	1026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3300 cd/sqm



TEST NUMBER: P903537

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.6	1.4
10°-20°	485.6	4.0
20°-30°	713.7	5.9
30°-40°	828.9	6.8
40°-50°	827.8	6.8
50°-60°	721.8	6.0
60°-70°	533.6	4.4
70°-80°	301.9	2.5
80°-90°	84.2	0.7
90°-100°	83.9	0.7
100°-110°	312.8	2.6
110°-120°	829.6	6.8
120°-130°	1376.0	11.3
130°-140°	1461.6	12.0
140°-150°	1358.4	11.2
150°-160°	1092.1	9.0
160°-170°	703.7	5.8
170°-180°	242.2	2.0
0°-30°	1371.9	11.3
0°-40°	2200.7	18.1
0°-60°	3750.4	30.9
0°-90°	4670.1	38.5
90°-120°	1226.4	10.1
90°-150°	5422.4	44.7
90°-180°	7460.0	61.5
0°-180°	12130.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	2	22	37	46	50	11
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P903537

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P903537

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8



TEST NUMBER: P903537  
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.83	11.60	11.88	12.66	14.08	10.39	11.16	11.44	12.21	13.64
	3H	12.47	13.16	13.53	14.22	15.66	11.98	12.67	13.04	13.73	15.17
	4H	13.04	13.69	14.11	14.76	16.21	12.54	13.20	13.62	14.26	15.71
	6H	13.42	14.02	14.50	15.09	16.55	12.92	13.52	14.00	14.59	16.05
	8H	13.51	14.08	14.60	15.17	16.63	13.01	13.58	14.10	14.67	16.13
	12H	13.55	14.09	14.64	15.17	16.65	13.04	13.58	14.13	14.66	16.15
4H	2H	11.27	11.92	12.35	12.99	14.44	10.92	11.57	12.00	12.63	14.09
	3H	13.11	13.65	14.19	14.74	16.21	12.70	13.24	13.78	14.34	15.80
	4H	13.80	14.30	14.89	15.38	16.87	13.38	13.88	14.47	14.96	16.45
	6H	14.29	14.72	15.39	15.83	17.31	13.86	14.29	14.96	15.40	16.87
	8H	14.43	14.83	15.53	15.93	17.42	13.99	14.39	15.09	15.49	16.99
	12H	14.49	14.85	15.61	15.96	17.46	14.04	14.40	15.16	15.52	17.02
8H	4H	13.98	14.38	15.08	15.48	16.97	13.60	14.00	14.70	15.10	16.59
	6H	14.58	14.91	15.70	16.05	17.55	14.20	14.53	15.32	15.67	17.16
	8H	14.79	15.08	15.92	16.20	17.71	14.40	14.69	15.52	15.81	17.32
	12H	14.90	15.16	16.03	16.28	17.82	14.49	14.75	15.62	15.87	17.41
12H	4H	13.96	14.32	15.07	15.43	16.93	13.59	13.95	14.70	15.06	16.56
	6H	14.61	14.90	15.73	16.02	17.53	14.23	14.52	15.36	15.64	17.16
	8H	14.83	15.08	15.96	16.20	17.75	14.45	14.70	15.58	15.82	17.37