

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903538

Luminaire Tested: DFN2DIP-SQ2F0-050D080US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903538
REPORT IS A COMBINATION OF REPORTS P899836 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D080US830-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10679.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 109.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4283	4283	4283
5°	4282	4206	4236
10°	4233	4114	4092
15°	4167	3969	3874
20°	4082	3773	3607
25°	3996	3555	3350
30°	3882	3332	3027
35°	3770	3094	2743
40°	3656	2847	2418
45°	3524	2576	2124
50°	3388	2303	1837
55°	3244	2012	1562
60°	3077	1710	1280
65°	2884	1403	1145
70°	2651	1118	1028
75°	2358	967	923
80°	1936	785	782
85°	1261	488	557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3524 cd/sqm

TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	1.7
10°-20°	501.1	4.7
20°-30°	703.6	6.6
30°-40°	766.9	7.2
40°-50°	704.9	6.6
50°-60°	553.6	5.2
60°-70°	360.3	3.4
70°-80°	185.5	1.7
80°-90°	54.1	0.5
90°-100°	147.6	1.4
100°-110°	468.9	4.4
110°-120°	802.4	7.5
120°-130°	1055.3	9.9
130°-140°	1184.5	11.1
140°-150°	1161.5	10.9
150°-160°	974.4	9.1
160°-170°	646.2	6.1
170°-180°	225.9	2.1
0°-30°	1387.2	13.0
0°-40°	2154.2	20.2
0°-60°	3412.7	32.0
0°-90°	4012.6	37.6
90°-120°	1418.8	13.3
90°-150°	4820.1	45.1
90°-180°	6666.0	62.4
0°-180°	10679.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	26	70	66	68	11
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7

TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7

TEST NUMBER: P903538

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.80	11.54	11.86	12.60	14.04	6.76	7.50	7.82	8.56	10.00
	3H	12.45	13.11	13.52	14.18	15.64	7.92	8.58	9.00	9.66	11.11
	4H	13.04	13.67	14.13	14.74	16.21	8.36	8.98	9.44	10.06	11.52
	6H	13.44	14.02	14.54	15.09	16.57	8.66	9.23	9.75	10.31	11.79
	8H	13.56	14.11	14.66	15.20	16.67	8.74	9.28	9.83	10.38	11.85
	12H	13.61	14.13	14.71	15.21	16.71	8.77	9.29	9.87	10.37	11.87
4H	2H	10.80	11.43	11.89	12.50	13.97	7.33	7.96	8.43	9.03	10.50
	3H	12.60	13.12	13.70	14.22	15.70	8.66	9.18	9.75	10.27	11.75
	4H	13.27	13.75	14.38	14.84	16.34	9.18	9.66	10.29	10.75	12.25
	6H	13.77	14.17	14.87	15.29	16.78	9.58	9.99	10.69	11.10	12.59
	8H	13.93	14.31	15.04	15.41	16.92	9.70	10.08	10.80	11.18	12.69
	12H	14.01	14.35	15.13	15.47	16.98	9.75	10.09	10.87	11.21	12.72
8H	4H	13.23	13.61	14.34	14.72	16.22	9.45	9.83	10.55	10.93	12.44
	6H	13.77	14.09	14.90	15.23	16.74	9.94	10.25	11.07	11.40	12.90
	8H	13.97	14.25	15.11	15.38	16.90	10.11	10.39	11.25	11.52	13.04
	12H	14.10	14.34	15.24	15.46	17.02	10.21	10.46	11.35	11.58	13.14
12H	4H	13.18	13.52	14.30	14.64	16.15	9.44	9.79	10.57	10.91	12.42
	6H	13.74	14.02	14.88	15.15	16.67	9.98	10.26	11.12	11.38	12.91
	8H	13.95	14.19	15.09	15.31	16.87	10.17	10.41	11.31	11.54	13.10