

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917230

Luminaire Tested: DFN2DIP-SQ2F0-080D030US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917230
REPORT IS A COMBINATION OF REPORTS P899782 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D030US930-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7708.6 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 101.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5928	5928	5928
5°	5927	5821	5862
10°	5858	5694	5663
15°	5767	5493	5361
20°	5650	5222	4993
25°	5530	4920	4637
30°	5373	4612	4189
35°	5218	4281	3796
40°	5060	3941	3346
45°	4878	3565	2940
50°	4688	3187	2542
55°	4489	2785	2161
60°	4258	2366	1771
65°	3992	1942	1585
70°	3669	1547	1422
75°	3263	1339	1278
80°	2679	1087	1083
85°	1743	675	770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4878 cd/sqm

TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	3.3
10°-20°	693.6	9.0
20°-30°	973.7	12.6
30°-40°	1061.4	13.8
40°-50°	975.6	12.7
50°-60°	766.2	9.9
60°-70°	498.7	6.5
70°-80°	256.7	3.3
80°-90°	67.7	0.9
90°-100°	47.9	0.6
100°-110°	152.1	2.0
110°-120°	260.3	3.4
120°-130°	342.3	4.4
130°-140°	384.2	5.0
140°-150°	376.8	4.9
150°-160°	316.1	4.1
160°-170°	209.6	2.7
170°-180°	73.3	1.0
0°-30°	1919.9	24.9
0°-40°	2981.4	38.7
0°-60°	4723.1	61.3
0°-90°	5546.2	71.9
90°-120°	460.2	6.0
90°-150°	1563.5	20.3
90°-180°	2162.0	28.0
0°-180°	7708.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	1	8	23	21	22	8
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P917230

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.06	16.11	15.81	16.87	17.79	11.02	12.07	11.77	12.83	13.76
	3H	16.73	17.67	17.50	18.45	19.40	12.21	13.14	12.97	13.92	14.87
	4H	17.34	18.22	18.12	19.01	19.97	12.65	13.54	13.43	14.32	15.29
	6H	17.75	18.57	18.55	19.36	20.34	12.97	13.78	13.76	14.58	15.56
	8H	17.88	18.65	18.68	19.47	20.45	13.06	13.83	13.86	14.64	15.62
	12H	17.94	18.68	18.75	19.48	20.49	13.10	13.84	13.91	14.64	15.65
4H	2H	15.10	15.98	15.88	16.77	17.73	11.63	12.51	12.42	13.30	14.26
	3H	16.92	17.66	17.72	18.48	19.46	12.98	13.71	13.78	14.53	15.51
	4H	17.61	18.28	18.42	19.09	20.10	13.52	14.19	14.33	15.00	16.01
	6H	18.12	18.69	18.95	19.54	20.55	13.93	14.51	14.76	15.35	16.37
	8H	18.29	18.82	19.12	19.66	20.69	14.05	14.59	14.89	15.43	16.46
	12H	18.38	18.86	19.23	19.72	20.75	14.12	14.60	14.97	15.46	16.49
8H	4H	17.59	18.13	18.42	18.96	19.99	13.80	14.34	14.64	15.18	16.21
	6H	18.14	18.58	19.00	19.47	20.49	14.31	14.75	15.17	15.63	16.66
	8H	18.34	18.74	19.22	19.62	20.66	14.48	14.88	15.35	15.75	16.80
	12H	18.48	18.83	19.35	19.69	20.79	14.60	14.94	15.47	15.81	16.91
12H	4H	17.55	18.03	18.40	18.89	19.92	13.82	14.30	14.67	15.16	16.19
	6H	18.11	18.51	18.99	19.39	20.43	14.35	14.74	15.22	15.62	16.67
	8H	18.33	18.68	19.20	19.55	20.65	14.55	14.90	15.43	15.77	16.87