

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903592

Luminaire Tested: DFN2DIP-SQ2F0-080D040US830-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903592  
REPORT IS A COMBINATION OF REPORTS P899793 AND P896659  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-080D040US830-FLLFLL  
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10801.5 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 108.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903592  
CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P903592

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58			
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49			
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41			
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35			
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31			
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27			
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26	24			
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22			
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19			
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6451	6451	6451
5°	6450	6348	6395
10°	6387	6248	6300
15°	6282	6131	6156
20°	6144	5974	6008
25°	6006	5790	5839
30°	5837	5617	5627
35°	5675	5415	5403
40°	5478	5211	5188
45°	5280	5005	4970
50°	5064	4789	4716
55°	4836	4539	4481
60°	4579	4245	4211
65°	4296	3937	3894
70°	3937	3564	3550
75°	3444	3115	3220
80°	2845	2543	2616
85°	1923	1607	1644

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5280 cd/sqm



TEST NUMBER: P903592

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.1	2.6
10°-20°	777.0	7.2
20°-30°	1141.8	10.6
30°-40°	1326.2	12.3
40°-50°	1324.5	12.3
50°-60°	1155.0	10.7
60°-70°	853.8	7.9
70°-80°	483.0	4.5
80°-90°	130.9	1.2
90°-100°	73.8	0.7
100°-110°	234.4	2.2
110°-120°	401.2	3.7
120°-130°	527.6	4.9
130°-140°	592.2	5.5
140°-150°	580.8	5.4
150°-160°	487.2	4.5
160°-170°	323.1	3.0
170°-180°	112.9	1.0
0°-30°	2195.0	20.3
0°-40°	3521.1	32.6
0°-60°	6000.6	55.6
0°-90°	7468.3	69.1
90°-120°	709.4	6.6
90°-150°	2410.0	22.3
90°-180°	3333.0	30.9
0°-180°	10801.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	1	13	35	33	34	10
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	



TEST NUMBER: P903592

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9



TEST NUMBER: P903592

CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3



TEST NUMBER: P903592  
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D040US830-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.24	16.30	16.01	17.10	18.07	14.79	15.86	15.57	16.65	17.62
	3H	16.89	17.85	17.68	18.65	19.65	16.40	17.36	17.19	18.16	19.16
	4H	17.48	18.38	18.28	19.19	20.20	16.98	17.89	17.79	18.70	19.71
	6H	17.87	18.71	18.69	19.53	20.55	17.37	18.21	18.19	19.03	20.05
	8H	17.97	18.77	18.80	19.61	20.63	17.47	18.27	18.30	19.11	20.13
	12H	18.02	18.78	18.86	19.61	20.67	17.51	18.27	18.35	19.11	20.16
4H	2H	15.71	16.61	16.52	17.43	18.44	15.36	16.26	16.16	17.07	18.08
	3H	17.57	18.33	18.39	19.17	20.20	17.16	17.92	17.98	18.77	19.79
	4H	18.28	18.97	19.11	19.81	20.87	17.86	18.54	18.69	19.39	20.44
	6H	18.79	19.38	19.64	20.25	21.31	18.36	18.95	19.21	19.82	20.88
	8H	18.93	19.49	19.79	20.35	21.42	18.50	19.05	19.35	19.92	20.99
	12H	19.01	19.51	19.88	20.39	21.47	18.56	19.06	19.43	19.94	21.02
8H	4H	18.48	19.04	19.33	19.90	20.97	18.10	18.66	18.96	19.52	20.59
	6H	19.10	19.56	19.98	20.46	21.53	18.71	19.17	19.59	20.08	21.15
	8H	19.31	19.71	20.20	20.62	21.70	18.91	19.32	19.80	20.22	21.31
	12H	19.43	19.79	20.33	20.69	21.83	19.02	19.38	19.92	20.28	21.42
12H	4H	18.47	18.97	19.35	19.86	20.94	18.10	18.60	18.98	19.49	20.57
	6H	19.12	19.53	20.01	20.43	21.52	18.75	19.16	19.64	20.06	21.15
	8H	19.36	19.72	20.25	20.61	21.75	18.98	19.34	19.87	20.23	21.37