

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917247

Luminaire Tested: DFN2DIP-SQ2F0-080D070US930-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P917247  
REPORT IS A COMBINATION OF REPORTS P901350 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-080D070US930-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11194.0 lumens  
Efficiency: N/A  
Efficacy: 83.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 133.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P917247  
CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P917247

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	50	49	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	40	38	36	32
4	75	65	57	52	69	60	54	48	52	47	42	44	40	37	36	33	31	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	21	23	20	18	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5928	5928	5928
5°	5927	5821	5862
10°	5858	5694	5663
15°	5767	5493	5361
20°	5650	5222	4993
25°	5530	4920	4637
30°	5373	4612	4189
35°	5218	4281	3796
40°	5060	3941	3346
45°	4878	3565	2940
50°	4688	3187	2542
55°	4489	2785	2161
60°	4258	2366	1771
65°	3992	1942	1585
70°	3669	1547	1422
75°	3263	1339	1278
80°	2679	1087	1083
85°	1743	675	770

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4878 cd/sqm



TEST NUMBER: P917247

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.6	2.3
10°-20°	693.6	6.2
20°-30°	973.7	8.7
30°-40°	1061.4	9.5
40°-50°	975.6	8.7
50°-60°	766.2	6.8
60°-70°	498.7	4.5
70°-80°	256.7	2.3
80°-90°	68.9	0.6
90°-100°	63.5	0.6
100°-110°	236.8	2.1
110°-120°	627.9	5.6
120°-130°	1041.5	9.3
130°-140°	1106.3	9.9
140°-150°	1028.1	9.2
150°-160°	826.6	7.4
160°-170°	532.6	4.8
170°-180°	183.3	1.6
0°-30°	1919.9	17.2
0°-40°	2981.4	26.6
0°-60°	4723.1	42.2
0°-90°	5547.4	49.6
90°-120°	928.2	8.3
90°-150°	4104.1	36.7
90°-180°	5647.0	50.4
0°-180°	11194.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	1	17	28	35	38	10
95°	90	44	54	61	60	107
105°	424	466	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1178	1188	1192	1010
135°	1402	1424	1437	1451	1448	1083
145°	1626	1625	1649	1658	1652	1017
155°	1791	1778	1795	1803	1792	825
165°	1887	1879	1883	1893	1883	533
175°	1930	1920	1923	1933	1919	184
180°	1926	1926	1926	1926	1926	



TEST NUMBER: P917247

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	163.0	48.8	71.0	75.3	76.6
100°	246.8	55.8	79.4	90.5	93.4
102.5°	338.6	336.0	82.3	97.5	101.7
105°	423.7	465.5	85.0	100.3	105.9
107.5°	522.6	557.4	87.9	103.1	108.8
110°	617.5	646.6	243.9	104.6	110.1



TEST NUMBER: P917247

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	706.7	731.6	708.0	107.2	111.5
115°	801.4	825.0	859.9	214.7	114.4
117.5°	883.6	911.4	935.2	735.8	370.7
120°	975.6	996.5	1021.7	1038.4	850.2
122.5°	1053.5	1075.9	1103.9	1112.1	1113.6
125°	1133.0	1151.2	1177.7	1187.5	1191.6
127.5°	1205.5	1225.0	1246.0	1260.0	1261.3
130°	1273.8	1296.2	1311.4	1326.8	1325.5
132.5°	1343.5	1361.7	1377.0	1389.5	1388.2
135°	1402.1	1424.4	1436.9	1450.9	1448.1
137.5°	1463.3	1480.1	1494.1	1508.1	1503.9
140°	1523.2	1534.5	1549.7	1562.3	1555.3
142.5°	1573.5	1583.3	1601.3	1612.4	1605.5
145°	1626.5	1625.1	1648.7	1658.5	1651.5
147.5°	1672.3	1668.3	1691.9	1698.8	1693.4
150°	1717.0	1707.3	1729.7	1737.9	1731.0
152.5°	1754.6	1743.5	1764.4	1772.8	1763.1
155°	1790.9	1778.4	1795.1	1803.4	1792.4
157.5°	1820.2	1809.1	1821.6	1831.4	1820.2
160°	1845.3	1836.9	1845.3	1853.6	1843.8
162.5°	1867.5	1859.2	1866.1	1875.9	1863.4
165°	1887.0	1878.8	1882.8	1892.6	1882.8
167.5°	1902.4	1893.9	1898.3	1908.0	1895.5
170°	1915.0	1906.6	1909.3	1919.1	1906.6
172.5°	1923.3	1915.0	1917.8	1927.5	1915.0
175°	1930.2	1920.4	1923.3	1933.0	1919.1
177.5°	1933.0	1923.3	1924.8	1934.5	1921.9
180°	1926.1	1926.1	1926.1	1926.1	1926.1



TEST NUMBER: P917247  
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US930-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.17	14.00	14.14	14.98	16.26	9.13	9.96	10.10	10.94	12.22
	3H	14.83	15.57	15.81	16.56	17.86	10.30	11.04	11.28	12.03	13.33
	4H	15.43	16.13	16.42	17.12	18.43	10.74	11.44	11.73	12.43	13.74
	6H	15.83	16.48	16.84	17.47	18.79	11.05	11.69	12.05	12.68	14.01
	8H	15.95	16.56	16.96	17.57	18.89	11.13	11.74	12.14	12.75	14.07
	12H	16.00	16.58	17.02	17.59	18.93	11.16	11.74	12.18	12.75	14.09
4H	2H	13.19	13.89	14.19	14.88	16.19	9.72	10.42	10.72	11.41	12.72
	3H	14.99	15.57	16.00	16.59	17.92	11.05	11.63	12.05	12.65	13.97
	4H	15.67	16.20	16.68	17.21	18.56	11.58	12.11	12.59	13.12	14.47
	6H	16.17	16.62	17.19	17.66	19.00	11.98	12.43	13.01	13.47	14.82
	8H	16.33	16.76	17.36	17.78	19.14	12.10	12.52	13.12	13.55	14.91
	12H	16.41	16.80	17.46	17.84	19.21	12.15	12.54	13.20	13.58	14.94
8H	4H	15.63	16.06	16.66	17.09	18.45	11.85	12.27	12.87	13.30	14.66
	6H	16.18	16.53	17.23	17.60	18.96	12.34	12.69	13.39	13.76	15.12
	8H	16.38	16.69	17.44	17.74	19.12	12.52	12.83	13.58	13.88	15.26
	12H	16.50	16.78	17.57	17.83	19.25	12.62	12.89	13.68	13.94	15.36
12H	4H	15.58	15.97	16.63	17.01	18.38	11.85	12.23	12.89	13.28	14.64
	6H	16.15	16.46	17.21	17.52	18.89	12.39	12.69	13.44	13.75	15.13
	8H	16.36	16.63	17.42	17.68	19.10	12.58	12.85	13.64	13.90	15.32