

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903604

Luminaire Tested: DFN2DIP-SQ2F0-080D070US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903604
REPORT IS A COMBINATION OF REPORTS P899829 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D070US830-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13304.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903604
CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P903604

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47	47	47	47
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40	40	40	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34	34	34	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29	29	29	29
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25	25	25	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22	22	22	22
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22	20	20	20	20
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20	17	17	17	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18	16	16	16	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6451	6451	6451
5°	6450	6348	6395
10°	6387	6248	6300
15°	6282	6131	6156
20°	6144	5974	6008
25°	6006	5790	5839
30°	5837	5617	5627
35°	5675	5415	5403
40°	5478	5211	5188
45°	5280	5005	4970
50°	5064	4789	4716
55°	4836	4539	4481
60°	4579	4245	4211
65°	4296	3937	3894
70°	3937	3564	3550
75°	3444	3115	3220
80°	2845	2543	2616
85°	1923	1607	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5280 cd/sqm



TEST NUMBER: P903604

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	2.1
10°-20°	777.0	5.8
20°-30°	1141.8	8.6
30°-40°	1326.2	10.0
40°-50°	1324.5	10.0
50°-60°	1155.0	8.7
60°-70°	853.8	6.4
70°-80°	483.0	3.6
80°-90°	133.4	1.0
90°-100°	129.1	1.0
100°-110°	410.3	3.1
110°-120°	702.1	5.3
120°-130°	923.3	6.9
130°-140°	1036.4	7.8
140°-150°	1016.3	7.6
150°-160°	852.6	6.4
160°-170°	565.4	4.2
170°-180°	197.6	1.5
0°-30°	2195.0	16.5
0°-40°	3521.1	26.5
0°-60°	6000.6	45.1
0°-90°	7470.9	56.2
90°-120°	1241.5	9.3
90°-150°	4217.6	31.7
90°-180°	5833.0	43.8
0°-180°	13304.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	2	23	62	58	60	13
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	



TEST NUMBER: P903604

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2



TEST NUMBER: P903604

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6



TEST NUMBER: P903604
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.18	15.10	15.09	16.02	17.21	13.74	14.66	14.64	15.58	16.76
	3H	15.83	16.65	16.74	17.58	18.79	15.34	16.16	16.25	17.09	18.30
	4H	16.41	17.19	17.33	18.12	19.34	15.91	16.69	16.84	17.63	18.84
	6H	16.79	17.51	17.73	18.46	19.68	16.29	17.01	17.23	17.96	19.18
	8H	16.89	17.58	17.84	18.54	19.76	16.39	17.08	17.34	18.04	19.26
	12H	16.94	17.59	17.89	18.54	19.79	16.43	17.08	17.38	18.03	19.28
4H	2H	14.64	15.42	15.58	16.36	17.57	14.28	15.06	15.22	16.00	17.22
	3H	16.49	17.14	17.43	18.11	19.34	16.08	16.73	17.03	17.70	18.93
	4H	17.19	17.78	18.14	18.75	20.00	16.77	17.36	17.72	18.32	19.58
	6H	17.69	18.20	18.66	19.19	20.44	17.26	17.77	18.23	18.76	20.01
	8H	17.83	18.31	18.80	19.29	20.56	17.39	17.87	18.36	18.85	20.12
	12H	17.90	18.33	18.89	19.33	20.60	17.45	17.88	18.44	18.88	20.15
8H	4H	17.38	17.86	18.35	18.84	20.10	17.00	17.48	17.97	18.46	19.73
	6H	17.99	18.39	18.98	19.41	20.67	17.60	18.00	18.60	19.02	20.29
	8H	18.20	18.55	19.20	19.56	20.84	17.80	18.15	18.81	19.16	20.45
	12H	18.32	18.63	19.33	19.63	20.96	17.91	18.22	18.92	19.22	20.55
12H	4H	17.36	17.80	18.35	18.79	20.07	17.00	17.43	17.98	18.42	19.70
	6H	18.01	18.37	19.02	19.37	20.66	17.64	17.99	18.64	19.00	20.28
	8H	18.24	18.55	19.25	19.55	20.88	17.86	18.17	18.87	19.17	20.50