

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919856

Luminaire Tested: DFN2DIP-SQ2F0-030D080US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919856
REPORT IS A COMBINATION OF REPORTS P899831 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D080US935-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8653.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27
3	77	68	61	56	69	61	55	51	49	44	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	38	35	33	30	27	23	21	19
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	26	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	18	16	16	13	12
9	47	35	28	23	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	32	25	21	40	29	23	19	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2210	2210	2210
5°	2210	2174	2191
10°	2188	2140	2158
15°	2152	2100	2109
20°	2105	2046	2058
25°	2057	1983	2000
30°	1999	1924	1927
35°	1944	1855	1851
40°	1876	1785	1777
45°	1809	1715	1702
50°	1735	1641	1616
55°	1657	1555	1535
60°	1569	1454	1443
65°	1472	1349	1334
70°	1349	1221	1216
75°	1180	1067	1104
80°	975	871	896
85°	659	550	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3036 cd/sqm

TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.1
10°-20°	266.2	3.1
20°-30°	391.1	4.5
30°-40°	454.3	5.3
40°-50°	453.7	5.2
50°-60°	395.6	4.6
60°-70°	292.5	3.4
70°-80°	165.5	1.9
80°-90°	49.9	0.6
90°-100°	134.8	1.6
100°-110°	428.3	4.9
110°-120°	733.0	8.5
120°-130°	964.0	11.1
130°-140°	1082.0	12.5
140°-150°	1061.0	12.3
150°-160°	890.1	10.3
160°-170°	590.3	6.8
170°-180°	206.3	2.4
0°-30°	751.9	8.7
0°-40°	1206.2	13.9
0°-60°	2055.6	23.8
0°-90°	2563.4	29.6
90°-120°	1296.1	15.0
90°-150°	4403.1	50.9
90°-180°	6090.0	70.4
0°-180°	8653.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1005	1001	991	998	996	95
15°	957	951	938	942	938	269
25°	866	858	842	844	842	398
35°	747	737	722	716	711	467
45°	608	601	587	576	572	469
55°	460	454	443	431	426	411
65°	310	304	295	286	281	307
75°	162	160	156	150	152	173
85°	40	39	38	35	34	44
90°	2	24	64	60	62	9
95°	96	114	118	118	114	107
105°	395	401	405	408	408	417
115°	736	746	743	741	736	728
125°	1070	1086	1081	1075	1073	956
135°	1384	1404	1408	1406	1401	1070
145°	1680	1693	1704	1706	1698	1050
155°	1921	1926	1932	1941	1935	884
165°	2090	2088	2088	2101	2092	590
175°	2174	2169	2165	2178	2167	207
180°	2178	2178	2178	2178	2178	

TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.0	1005.0	1005.0	1005.0	1005.0
2.5°	1010.9	1006.1	995.4	1005.0	1003.2
5°	1005.0	1001.3	990.6	998.3	996.4
7.5°	998.3	992.6	981.9	989.7	987.7
10°	987.7	980.9	969.4	977.1	974.2
12.5°	973.2	967.4	955.9	960.6	958.7
15°	956.7	951.1	938.4	942.3	937.5
17.5°	936.4	930.7	918.1	922.9	918.1
20°	914.2	908.4	894.9	897.8	894.0
22.5°	892.1	883.4	870.7	870.7	868.7
25°	865.9	858.2	841.8	843.7	841.8
27.5°	836.9	830.1	817.6	814.8	809.9
30°	808.0	800.2	785.7	782.8	778.9
32.5°	777.1	771.3	755.8	749.9	746.1
35°	747.1	737.4	721.9	716.1	711.3
37.5°	713.3	704.6	689.1	682.3	677.4
40°	678.5	670.7	655.2	646.6	642.7
42.5°	644.6	636.9	621.5	611.7	606.0
45°	608.0	601.1	586.6	576.0	572.1
47.5°	572.1	565.4	549.9	539.2	533.5
50°	534.4	529.6	516.1	502.6	497.7
52.5°	497.7	490.9	478.5	467.8	461.0
55°	460.1	454.3	442.6	431.1	426.3
57.5°	422.3	417.5	404.9	393.3	389.4
60°	384.6	380.8	367.3	356.6	353.8
62.5°	347.9	341.1	331.5	321.8	318.0
65°	310.3	304.4	294.8	286.1	281.3
67.5°	271.6	266.7	258.0	251.3	247.5
70°	235.8	232.0	223.3	216.5	212.7
72.5°	199.1	195.2	190.4	183.7	180.8
75°	162.3	160.5	155.6	149.8	151.8
77.5°	129.5	125.6	123.6	120.8	118.0
80°	96.7	95.7	93.7	90.8	88.9
82.5°	65.7	65.7	64.8	60.9	60.9
85°	39.6	38.7	37.7	34.8	33.8
87.5°	17.4	15.5	13.5	10.7	9.6
90°	2.0	23.7	64.4	60.4	62.4
92.5°	40.7	55.2	57.2	59.1	59.1
95°	95.9	114.3	117.5	117.5	114.3
97.5°	159.6	176.7	183.9	183.9	183.9
100°	233.2	248.2	253.5	253.5	251.5
102.5°	310.6	321.8	329.0	331.0	329.0
105°	395.4	400.6	404.6	407.9	407.9
107.5°	479.4	487.3	487.3	488.6	479.4
110°	560.9	571.4	571.4	571.4	566.1

TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	648.8	660.0	658.1	652.8	648.8
115°	735.6	746.1	742.8	740.8	735.6
117.5°	821.6	836.0	826.8	821.6	816.3
120°	908.3	922.7	908.3	908.3	902.3
122.5°	987.0	1005.5	996.3	991.0	987.0
125°	1069.8	1086.2	1081.0	1075.0	1073.1
127.5°	1150.6	1171.0	1163.7	1155.9	1150.6
130°	1226.1	1249.7	1246.5	1242.6	1235.4
132.5°	1310.9	1329.2	1330.6	1321.4	1316.1
135°	1383.7	1404.1	1408.1	1406.1	1400.8
137.5°	1465.2	1481.6	1484.9	1483.6	1475.7
140°	1536.8	1553.2	1562.4	1562.4	1555.1
142.5°	1610.3	1626.8	1632.0	1634.0	1626.8
145°	1680.0	1693.1	1703.6	1705.6	1698.3
147.5°	1742.3	1758.8	1766.6	1770.0	1762.7
150°	1806.7	1817.8	1825.1	1831.0	1825.1
152.5°	1863.8	1875.0	1884.2	1891.4	1884.2
155°	1921.0	1926.2	1932.2	1941.3	1935.4
157.5°	1970.2	1974.2	1977.5	1990.5	1981.4
160°	2014.2	2018.2	2020.2	2031.3	2023.4
162.5°	2054.9	2054.9	2056.9	2069.4	2060.2
165°	2089.7	2087.7	2087.7	2100.9	2091.7
167.5°	2121.2	2115.4	2115.4	2128.5	2119.3
170°	2144.9	2139.7	2137.7	2150.9	2139.7
172.5°	2161.4	2156.1	2154.1	2167.2	2156.1
175°	2174.5	2169.2	2165.2	2178.4	2167.2
177.5°	2181.7	2176.4	2172.5	2183.7	2172.5
180°	2178.4	2178.4	2178.4	2178.4	2178.4

TEST NUMBER: P919856

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.64	8.35	8.76	9.46	10.99	7.20	7.90	8.31	9.01	10.55
	3H	9.27	9.90	10.39	11.02	12.57	8.78	9.41	9.90	10.53	12.08
	4H	9.84	10.44	10.97	11.56	13.11	9.35	9.94	10.48	11.06	12.62
	6H	10.22	10.77	11.36	11.89	13.46	9.72	10.27	10.86	11.39	12.96
	8H	10.31	10.83	11.45	11.97	13.53	9.81	10.33	10.95	11.47	13.03
	12H	10.34	10.84	11.49	11.97	13.56	9.84	10.33	10.98	11.46	13.05
4H	2H	8.07	8.67	9.21	9.79	11.35	7.72	8.32	8.86	9.43	10.99
	3H	9.90	10.40	11.05	11.55	13.12	9.49	9.99	10.64	11.14	12.71
	4H	10.59	11.05	11.74	12.19	13.78	10.17	10.63	11.32	11.76	13.35
	6H	11.08	11.48	12.24	12.63	14.21	10.65	11.04	11.80	12.20	13.78
	8H	11.22	11.59	12.37	12.73	14.33	10.78	11.15	11.94	12.30	13.89
	12H	11.27	11.61	12.44	12.77	14.37	10.83	11.16	12.00	12.32	13.92
8H	4H	10.77	11.13	11.92	12.28	13.88	10.39	10.76	11.54	11.90	13.50
	6H	11.37	11.67	12.54	12.86	14.45	10.98	11.29	12.16	12.48	14.07
	8H	11.57	11.84	12.75	13.01	14.62	11.18	11.44	12.36	12.61	14.23
	12H	11.68	11.92	12.87	13.08	14.73	11.27	11.51	12.46	12.67	14.32
12H	4H	10.74	11.08	11.91	12.23	13.84	10.37	10.71	11.54	11.86	13.47
	6H	11.39	11.66	12.57	12.82	14.44	11.02	11.28	12.20	12.45	14.06
	8H	11.61	11.84	12.79	13.01	14.65	11.23	11.46	12.41	12.63	14.27