

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919934

Luminaire Tested: DFN2DIP-SQ2F0-070D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919934
REPORT IS A COMBINATION OF REPORTS P899780 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-070D030US935-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7408.8 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	66	65	64
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5477	5477	5477
5°	5477	5378	5417
10°	5413	5261	5233
15°	5329	5076	4954
20°	5221	4825	4613
25°	5110	4546	4285
30°	4965	4261	3871
35°	4822	3956	3507
40°	4676	3642	3092
45°	4507	3295	2716
50°	4332	2945	2349
55°	4148	2573	1998
60°	3935	2186	1637
65°	3689	1795	1465
70°	3391	1430	1314
75°	3015	1237	1181
80°	2475	1005	1001
85°	1612	624	712

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4507 cd/sqm

TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	3.2
10°-20°	640.9	8.7
20°-30°	899.8	12.1
30°-40°	980.8	13.2
40°-50°	901.5	12.2
50°-60°	708.0	9.6
60°-70°	460.8	6.2
70°-80°	237.2	3.2
80°-90°	62.9	0.8
90°-100°	50.6	0.7
100°-110°	160.6	2.2
110°-120°	274.9	3.7
120°-130°	361.5	4.9
130°-140°	405.7	5.5
140°-150°	397.9	5.4
150°-160°	333.8	4.5
160°-170°	221.3	3.0
170°-180°	77.4	1.0
0°-30°	1774.1	23.9
0°-40°	2754.9	37.2
0°-60°	4364.3	58.9
0°-90°	5125.2	69.2
90°-120°	486.0	6.6
90°-150°	1651.1	22.3
90°-180°	2284.0	30.8
0°-180°	7408.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	9	24	23	23	7
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3

TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P919934

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.57	15.58	15.35	16.38	17.35	10.53	11.54	11.31	12.34	13.31
	3H	16.24	17.15	17.03	17.96	18.96	11.71	12.62	12.51	13.43	14.43
	4H	16.84	17.70	17.66	18.52	19.53	12.16	13.02	12.97	13.83	14.84
	6H	17.26	18.05	18.08	18.87	19.90	12.47	13.26	13.30	14.09	15.11
	8H	17.38	18.13	18.22	18.97	20.00	12.56	13.31	13.39	14.15	15.18
	12H	17.44	18.16	18.28	18.99	20.04	12.60	13.32	13.44	14.15	15.20
4H	2H	14.60	15.46	15.42	16.28	17.29	11.14	11.99	11.95	12.81	13.82
	3H	16.43	17.14	17.25	17.99	19.02	12.48	13.19	13.31	14.04	15.07
	4H	17.11	17.76	17.95	18.61	19.66	13.02	13.67	13.86	14.52	15.57
	6H	17.62	18.17	18.47	19.05	20.11	13.43	13.99	14.29	14.86	15.92
	8H	17.79	18.31	18.65	19.17	20.25	13.55	14.07	14.41	14.94	16.01
	12H	17.88	18.35	18.76	19.23	20.31	13.62	14.08	14.49	14.97	16.05
8H	4H	17.09	17.61	17.95	18.48	19.55	13.30	13.82	14.16	14.69	15.76
	6H	17.64	18.07	18.53	18.98	20.05	13.80	14.23	14.69	15.14	16.22
	8H	17.84	18.22	18.74	19.13	20.22	13.98	14.36	14.88	15.27	16.36
	12H	17.98	18.31	18.88	19.21	20.35	14.09	14.43	14.99	15.32	16.47
12H	4H	17.05	17.52	17.93	18.40	19.48	13.31	13.78	14.19	14.67	15.75
	6H	17.61	18.00	18.51	18.90	19.99	13.85	14.23	14.75	15.13	16.22
	8H	17.83	18.16	18.73	19.06	20.20	14.05	14.39	14.95	15.28	16.43