

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919971

Luminaire Tested: DFN2DIP-SQ2F0-080D060US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919971
REPORT IS A COMBINATION OF REPORTS P901338 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D060US935-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10969.1 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6260	6260	6260
5°	6259	6147	6191
10°	6186	6013	5981
15°	6090	5801	5662
20°	5967	5514	5273
25°	5840	5196	4897
30°	5674	4870	4424
35°	5511	4521	4008
40°	5344	4162	3534
45°	5151	3765	3104
50°	4951	3366	2685
55°	4741	2941	2283
60°	4497	2499	1871
65°	4216	2051	1673
70°	3875	1634	1502
75°	3446	1414	1349
80°	2829	1149	1143
85°	1842	713	813

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5151 cd/sqm

TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	2.4
10°-20°	732.4	6.7
20°-30°	1028.3	9.4
30°-40°	1120.9	10.2
40°-50°	1030.3	9.4
50°-60°	809.1	7.4
60°-70°	526.6	4.8
70°-80°	271.1	2.5
80°-90°	72.3	0.7
90°-100°	57.5	0.5
100°-110°	214.3	2.0
110°-120°	568.4	5.2
120°-130°	942.7	8.6
130°-140°	1001.4	9.1
140°-150°	930.7	8.5
150°-160°	748.2	6.8
160°-170°	482.1	4.4
170°-180°	165.9	1.5
0°-30°	2027.6	18.5
0°-40°	3148.5	28.7
0°-60°	4987.8	45.5
0°-90°	5857.9	53.4
90°-120°	840.2	7.7
90°-150°	3714.9	33.9
90°-180°	5111.0	46.6
0°-180°	10969.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	1	15	25	32	34	10
95°	82	40	49	56	54	97
105°	384	421	77	91	96	410
115°	725	747	778	194	104	714
125°	1026	1042	1066	1075	1079	915
135°	1269	1289	1301	1313	1311	980
145°	1472	1471	1492	1501	1495	921
155°	1621	1610	1625	1632	1622	747
165°	1708	1701	1704	1713	1704	483
175°	1747	1738	1741	1750	1737	166
180°	1743	1743	1743	1743	1743	

TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	1.2	15.2	25.1	31.6	34.0
92.5°	31.6	26.5	30.2	32.8	34.0
95°	82.0	40.3	49.2	55.6	54.2
97.5°	147.6	44.2	64.2	68.2	69.4
100°	223.3	50.5	71.9	82.0	84.5
102.5°	306.5	304.1	74.5	88.3	92.1
105°	383.5	421.4	77.0	90.7	95.9
107.5°	473.1	504.5	79.6	93.3	98.4
110°	559.0	585.3	220.8	94.7	99.6

TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	639.6	662.3	640.8	97.0	101.0
115°	725.4	746.8	778.4	194.3	103.5
117.5°	799.8	825.0	846.5	666.1	335.5
120°	883.1	902.0	924.8	939.9	769.6
122.5°	953.6	973.9	999.2	1006.7	1008.1
125°	1025.6	1042.1	1066.0	1074.9	1078.6
127.5°	1091.2	1108.9	1127.9	1140.5	1141.7
130°	1153.0	1173.3	1187.1	1201.0	1199.8
132.5°	1216.2	1232.6	1246.4	1257.7	1256.5
135°	1269.2	1289.4	1300.6	1313.4	1310.8
137.5°	1324.6	1339.7	1352.5	1365.0	1361.3
140°	1378.8	1389.0	1402.8	1414.2	1407.9
142.5°	1424.3	1433.2	1449.6	1459.6	1453.3
145°	1472.3	1470.9	1492.4	1501.2	1495.0
147.5°	1513.8	1510.0	1531.5	1537.7	1532.8
150°	1554.3	1545.4	1565.6	1573.1	1566.8
152.5°	1588.3	1578.2	1597.1	1604.7	1595.9
155°	1621.1	1609.8	1625.0	1632.5	1622.4
157.5°	1647.6	1637.5	1648.9	1657.8	1647.6
160°	1670.3	1662.7	1670.3	1677.8	1669.0
162.5°	1690.4	1682.9	1689.2	1698.1	1686.7
165°	1708.1	1700.6	1704.3	1713.2	1704.3
167.5°	1722.0	1714.4	1718.3	1727.2	1715.7
170°	1733.4	1725.8	1728.4	1737.1	1725.8
172.5°	1740.9	1733.4	1735.9	1744.8	1733.4
175°	1747.2	1738.4	1740.9	1749.7	1737.1
177.5°	1749.7	1740.9	1742.2	1751.1	1739.7
180°	1743.4	1743.4	1743.4	1743.4	1743.4



TEST NUMBER: P919971

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.72	14.58	14.65	15.52	16.75	9.68	10.54	10.61	11.48	12.71
	3H	15.38	16.15	16.32	17.10	18.35	10.85	11.62	11.80	12.57	13.82
	4H	15.97	16.70	16.93	17.66	18.92	11.29	12.01	12.25	12.98	14.23
	6H	16.38	17.05	17.35	18.02	19.29	11.60	12.26	12.57	13.23	14.50
	8H	16.50	17.14	17.48	18.12	19.39	11.68	12.31	12.66	13.30	14.56
	12H	16.56	17.16	17.54	18.14	19.43	11.71	12.32	12.70	13.29	14.59
4H	2H	13.73	14.46	14.70	15.42	16.68	10.27	10.99	11.23	11.95	13.21
	3H	15.54	16.15	16.52	17.14	18.41	11.60	12.20	12.57	13.19	14.46
	4H	16.22	16.77	17.21	17.76	19.05	12.13	12.68	13.12	13.67	14.96
	6H	16.72	17.19	17.72	18.20	19.49	12.53	13.01	13.53	14.01	15.31
	8H	16.88	17.33	17.88	18.33	19.63	12.65	13.09	13.65	14.09	15.40
	12H	16.97	17.37	17.99	18.38	19.70	12.71	13.11	13.72	14.12	15.43
8H	4H	16.19	16.63	17.18	17.63	18.94	12.40	12.84	13.40	13.84	15.15
	6H	16.73	17.10	17.75	18.14	19.45	12.90	13.26	13.92	14.30	15.61
	8H	16.94	17.26	17.97	18.29	19.61	13.07	13.39	14.10	14.42	15.75
	12H	17.06	17.34	18.10	18.37	19.74	13.18	13.46	14.21	14.49	15.85
12H	4H	16.14	16.54	17.16	17.55	18.87	12.40	12.80	13.42	13.82	15.13
	6H	16.71	17.03	17.74	18.06	19.38	12.94	13.26	13.97	14.29	15.62
	8H	16.91	17.20	17.95	18.22	19.59	13.14	13.42	14.17	14.44	15.81