

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922568

Luminaire Tested: DFN2DIP-SQ2F0-030D040US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922568
REPORT IS A COMBINATION OF REPORTS P899783 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D040US940-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5805.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2289	2289	2289
5°	2289	2252	2269
10°	2266	2217	2235
15°	2229	2175	2184
20°	2180	2119	2132
25°	2131	2054	2072
30°	2071	1993	1996
35°	2013	1921	1917
40°	1943	1849	1841
45°	1873	1776	1763
50°	1797	1699	1673
55°	1716	1610	1590
60°	1624	1506	1494
65°	1524	1397	1382
70°	1397	1264	1260
75°	1222	1105	1143
80°	1009	902	928
85°	682	570	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1873 cd/sqm

TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	1.7
10°-20°	275.6	4.7
20°-30°	405.1	7.0
30°-40°	470.5	8.1
40°-50°	469.9	8.1
50°-60°	409.8	7.1
60°-70°	302.9	5.2
70°-80°	171.4	3.0
80°-90°	48.4	0.8
90°-100°	69.8	1.2
100°-110°	221.8	3.8
110°-120°	379.5	6.5
120°-130°	499.2	8.6
130°-140°	560.3	9.7
140°-150°	549.4	9.5
150°-160°	460.9	7.9
160°-170°	305.7	5.3
170°-180°	106.8	1.8
0°-30°	778.7	13.4
0°-40°	1249.2	21.5
0°-60°	2128.9	36.7
0°-90°	2651.6	45.7
90°-120°	671.2	11.6
90°-150°	2280.1	39.3
90°-180°	3153.0	54.3
0°-180°	5805.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	1	12	33	31	32	6
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	

TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2

TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0

TEST NUMBER: P922568

CATALOG NUMBER: DFN2DIP-SQ2F0-030D040US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.62	10.44	10.61	11.45	12.78	9.17	10.00	10.17	11.00	12.33
	3H	11.26	12.00	12.26	13.01	14.36	10.77	11.51	11.77	12.52	13.87
	4H	11.83	12.53	12.85	13.55	14.91	11.34	12.04	12.35	13.05	14.41
	6H	12.21	12.86	13.24	13.88	15.25	11.71	12.36	12.74	13.38	14.75
	8H	12.31	12.92	13.34	13.96	15.33	11.81	12.42	12.84	13.46	14.83
	12H	12.35	12.93	13.39	13.96	15.36	11.84	12.42	12.88	13.46	14.85
4H	2H	10.06	10.76	11.09	11.78	13.14	9.71	10.41	10.73	11.42	12.78
	3H	11.90	12.49	12.94	13.53	14.91	11.50	12.08	12.53	13.13	14.50
	4H	12.60	13.14	13.64	14.17	15.57	12.18	12.71	13.22	13.75	15.15
	6H	13.10	13.56	14.14	14.62	16.01	12.66	13.12	13.71	14.18	15.58
	8H	13.23	13.66	14.28	14.72	16.12	12.80	13.23	13.85	14.28	15.69
	12H	13.30	13.68	14.36	14.75	16.17	12.85	13.24	13.92	14.31	15.72
8H	4H	12.78	13.21	13.83	14.27	15.67	12.41	12.83	13.45	13.89	15.30
	6H	13.39	13.74	14.46	14.84	16.24	13.00	13.36	14.08	14.45	15.86
	8H	13.60	13.91	14.68	14.99	16.41	13.20	13.51	14.28	14.59	16.02
	12H	13.71	13.99	14.80	15.06	16.53	13.30	13.58	14.39	14.65	16.12
12H	4H	12.76	13.15	13.83	14.22	15.63	12.39	12.78	13.46	13.85	15.26
	6H	13.41	13.73	14.49	14.80	16.23	13.04	13.35	14.12	14.43	15.86
	8H	13.64	13.91	14.72	14.99	16.45	13.26	13.53	14.34	14.61	16.07