

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908970

Luminaire Tested: DFN2DIP-SQ2F0-040D080US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908970
REPORT IS A COMBINATION OF REPORTS P899834 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D080US840-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10583.4 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3671	3671	3671
5°	3671	3605	3631
10°	3628	3526	3508
15°	3572	3402	3320
20°	3499	3234	3092
25°	3425	3047	2872
30°	3327	2856	2595
35°	3232	2652	2351
40°	3134	2441	2073
45°	3021	2208	1821
50°	2903	1974	1574
55°	2780	1725	1339
60°	2637	1465	1097
65°	2473	1203	981
70°	2273	958	881
75°	2020	829	792
80°	1659	673	671
85°	1080	418	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3561 cd/sqm

TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	1.5
10°-20°	429.5	4.1
20°-30°	603.0	5.7
30°-40°	657.4	6.2
40°-50°	604.2	5.7
50°-60°	474.5	4.5
60°-70°	308.9	2.9
70°-80°	159.0	1.5
80°-90°	47.9	0.5
90°-100°	158.1	1.5
100°-110°	502.4	4.7
110°-120°	859.7	8.1
120°-130°	1130.6	10.7
130°-140°	1269.1	12.0
140°-150°	1244.5	11.8
150°-160°	1043.9	9.9
160°-170°	692.3	6.5
170°-180°	242.0	2.3
0°-30°	1189.0	11.2
0°-40°	1846.4	17.4
0°-60°	2925.1	27.6
0°-90°	3440.8	32.5
90°-120°	1520.1	14.4
90°-150°	5164.3	48.8
90°-180°	7143.0	67.5
0°-180°	10583.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	2	28	76	71	73	10
95°	112	134	138	138	134	125
105°	464	470	474	478	478	489
115°	863	875	871	869	863	853
125°	1255	1274	1268	1261	1259	1121
135°	1623	1647	1652	1649	1643	1254
145°	1970	1986	1998	2000	1992	1231
155°	2253	2259	2266	2277	2270	1037
165°	2451	2449	2449	2464	2453	691
175°	2550	2544	2540	2555	2542	242
180°	2555	2555	2555	2555	2555	

TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	2.3	27.8	75.5	70.9	73.2
92.5°	47.8	64.7	67.1	69.3	69.3
95°	112.5	134.0	137.8	137.8	134.0
97.5°	187.2	207.2	215.7	215.7	215.7
100°	273.5	291.1	297.3	297.3	295.0
102.5°	364.4	377.5	385.9	388.2	385.9
105°	463.7	469.9	474.5	478.4	478.4
107.5°	562.3	571.6	571.6	573.1	562.3
110°	657.8	670.1	670.1	670.1	664.0

TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	761.0	774.2	771.8	765.7	761.0
115°	862.7	875.0	871.2	868.9	862.7
117.5°	963.6	980.6	969.8	963.6	957.5
120°	1065.3	1082.3	1065.3	1065.3	1058.3
122.5°	1157.7	1179.3	1168.5	1162.4	1157.7
125°	1254.8	1274.0	1267.9	1260.9	1258.7
127.5°	1349.6	1373.4	1364.9	1355.7	1349.6
130°	1438.1	1465.8	1462.0	1457.4	1449.0
132.5°	1537.5	1559.0	1560.6	1549.8	1543.7
135°	1623.0	1646.9	1651.5	1649.2	1643.1
137.5°	1718.5	1737.8	1741.6	1740.1	1730.8
140°	1802.5	1821.7	1832.5	1832.5	1824.0
142.5°	1888.8	1908.0	1914.2	1916.5	1908.0
145°	1970.4	1985.8	1998.1	2000.4	1992.0
147.5°	2043.6	2062.9	2072.0	2076.0	2067.5
150°	2119.1	2132.1	2140.6	2147.6	2140.6
152.5°	2186.1	2199.2	2210.0	2218.5	2210.0
155°	2253.1	2259.3	2266.2	2276.9	2270.1
157.5°	2310.9	2315.5	2319.4	2334.7	2324.0
160°	2362.5	2367.1	2369.4	2382.5	2373.3
162.5°	2410.2	2410.2	2412.6	2427.2	2416.4
165°	2451.0	2448.7	2448.7	2464.2	2453.4
167.5°	2488.0	2481.1	2481.1	2496.5	2485.7
170°	2515.8	2509.6	2507.3	2522.7	2509.6
172.5°	2535.1	2528.9	2526.6	2541.9	2528.9
175°	2550.4	2544.3	2539.6	2555.1	2541.9
177.5°	2558.9	2552.7	2548.1	2561.2	2548.1
180°	2555.1	2555.1	2555.1	2555.1	2555.1

TEST NUMBER: P908970

CATALOG NUMBER: DFN2DIP-SQ2F0-040D080US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.65	10.35	10.75	11.45	12.95	5.61	6.32	6.71	7.41	8.91
	3H	11.30	11.93	12.41	13.03	14.55	6.77	7.40	7.88	8.50	10.02
	4H	11.89	12.49	13.01	13.59	15.11	7.20	7.80	8.32	8.90	10.43
	6H	12.29	12.84	13.41	13.94	15.48	7.50	8.05	8.63	9.16	10.69
	8H	12.40	12.92	13.53	14.04	15.58	7.58	8.10	8.71	9.22	10.75
	12H	12.45	12.95	13.58	14.06	15.61	7.61	8.11	8.74	9.22	10.77
4H	2H	9.65	10.25	10.77	11.35	12.87	6.18	6.78	7.30	7.88	9.41
	3H	11.44	11.94	12.57	13.07	14.61	7.50	7.99	8.63	9.12	10.66
	4H	12.11	12.57	13.25	13.69	15.25	8.02	8.48	9.16	9.60	11.16
	6H	12.60	13.00	13.74	14.14	15.69	8.42	8.81	9.56	9.95	11.50
	8H	12.77	13.13	13.91	14.26	15.83	8.53	8.90	9.67	10.03	11.60
	12H	12.84	13.17	14.00	14.32	15.89	8.58	8.91	9.74	10.06	11.63
8H	4H	12.07	12.43	13.21	13.57	15.13	8.28	8.65	9.42	9.78	11.35
	6H	12.61	12.91	13.77	14.08	15.65	8.77	9.07	9.93	10.25	11.81
	8H	12.81	13.07	13.98	14.23	15.81	8.95	9.21	10.12	10.37	11.95
	12H	12.93	13.16	14.10	14.31	15.93	9.05	9.28	10.22	10.43	12.05
12H	4H	12.01	12.34	13.17	13.49	15.06	8.28	8.61	9.44	9.76	11.33
	6H	12.58	12.84	13.75	14.00	15.58	8.82	9.08	9.98	10.23	11.82
	8H	12.78	13.01	13.95	14.16	15.78	9.01	9.24	10.18	10.39	12.01

END OF REPORT