

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922576

Luminaire Tested: DFN2DIP-SQ2F0-030D060US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922576
REPORT IS A COMBINATION OF REPORTS P899807 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D060US940-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7383.4 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 68.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2289	2289	2289
5°	2289	2252	2269
10°	2266	2217	2235
15°	2229	2175	2184
20°	2180	2119	2132
25°	2131	2054	2072
30°	2071	1993	1996
35°	2013	1921	1917
40°	1943	1849	1841
45°	1873	1776	1763
50°	1797	1699	1673
55°	1716	1610	1590
60°	1624	1506	1494
65°	1524	1397	1382
70°	1397	1264	1260
75°	1222	1105	1143
80°	1009	902	928
85°	682	570	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2355 cd/sqm

TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	1.3
10°-20°	275.6	3.7
20°-30°	405.1	5.5
30°-40°	470.5	6.4
40°-50°	469.9	6.4
50°-60°	409.8	5.5
60°-70°	302.9	4.1
70°-80°	171.4	2.3
80°-90°	50.0	0.7
90°-100°	104.7	1.4
100°-110°	332.7	4.5
110°-120°	569.3	7.7
120°-130°	748.8	10.1
130°-140°	840.5	11.4
140°-150°	824.2	11.2
150°-160°	691.4	9.4
160°-170°	458.5	6.2
170°-180°	160.3	2.2
0°-30°	778.7	10.5
0°-40°	1249.2	16.9
0°-60°	2128.9	28.8
0°-90°	2653.2	35.9
90°-120°	1006.7	13.6
90°-150°	3420.1	46.3
90°-180°	4730.0	64.1
0°-180°	7383.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	2	18	50	47	48	7
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P922576

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.57	9.32	9.64	10.39	11.85	8.12	8.87	9.19	9.94	11.40
	3H	10.20	10.87	11.28	11.95	13.43	9.71	10.38	10.79	11.46	12.94
	4H	10.77	11.41	11.86	12.49	13.97	10.28	10.91	11.37	11.99	13.48
	6H	11.15	11.74	12.25	12.82	14.31	10.65	11.24	11.75	12.32	13.82
	8H	11.24	11.80	12.35	12.90	14.39	10.74	11.30	11.85	12.40	13.89
	12H	11.28	11.81	12.39	12.90	14.42	10.77	11.30	11.88	12.40	13.91
4H	2H	9.01	9.64	10.10	10.72	12.21	8.65	9.29	9.75	10.37	11.85
	3H	10.84	11.37	11.94	12.48	13.97	10.43	10.96	11.53	12.07	13.56
	4H	11.53	12.02	12.64	13.12	14.63	11.11	11.60	12.22	12.69	14.21
	6H	12.02	12.44	13.14	13.56	15.07	11.59	12.01	12.71	13.13	14.64
	8H	12.16	12.55	13.27	13.66	15.19	11.72	12.11	12.84	13.23	14.75
	12H	12.22	12.57	13.35	13.70	15.23	11.77	12.12	12.90	13.25	14.78
8H	4H	11.71	12.10	12.82	13.21	14.74	11.33	11.72	12.45	12.83	14.36
	6H	12.31	12.63	13.45	13.79	15.31	11.93	12.25	13.06	13.40	14.93
	8H	12.52	12.80	13.66	13.93	15.48	12.12	12.41	13.27	13.54	15.08
	12H	12.63	12.88	13.78	14.01	15.59	12.22	12.47	13.37	13.60	15.18
12H	4H	11.69	12.04	12.82	13.16	14.70	11.32	11.67	12.45	12.80	14.33
	6H	12.33	12.62	13.48	13.75	15.29	11.96	12.24	13.10	13.38	14.92
	8H	12.56	12.80	13.70	13.94	15.51	12.17	12.42	13.32	13.55	15.13