

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922583

Luminaire Tested: DFN2DIP-SQ2F0-030D070US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922583
REPORT IS A COMBINATION OF REPORTS P901340 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D070US940-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8453.4 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		71	71	71		52	52	52		35	35	35
1	93	89	85	82		83	79	76	74		62	60	58		46	45	44		31	31	30
2	85	78	72	67		75	70	65	61		55	51	49		41	39	37		28	27	26
3	77	69	62	56		69	62	56	51		48	44	41		36	34	31		25	23	22
4	71	61	53	48		63	55	48	43		43	39	35		32	29	27		22	21	19
5	65	54	46	41		58	49	42	37		39	34	30		29	26	23		20	18	17
6	60	48	41	35		53	44	37	32		35	30	26		26	23	21		18	16	15
7	55	44	36	31		49	39	33	28		31	27	23		24	21	18		17	15	13
8	51	40	32	27		46	36	29	25		29	24	21		22	19	16		16	13	12
9	48	36	29	24		43	33	26	22		26	22	18		20	17	15		14	12	11
10	44	33	26	22		40	30	24	20		24	20	16		19	15	13		13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2431	2431	2431
5°	2431	2387	2404
10°	2403	2335	2323
15°	2365	2253	2199
20°	2317	2142	2048
25°	2268	2018	1902
30°	2204	1891	1718
35°	2140	1756	1557
40°	2076	1616	1373
45°	2001	1462	1206
50°	1923	1307	1043
55°	1841	1142	887
60°	1746	970	727
65°	1637	797	650
70°	1505	634	583
75°	1338	549	524
80°	1100	446	444
85°	715	277	316

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2001 cd/sqm

TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.2
10°-20°	284.5	3.4
20°-30°	399.4	4.7
30°-40°	435.3	5.1
40°-50°	400.1	4.7
50°-60°	314.2	3.7
60°-70°	204.5	2.4
70°-80°	105.3	1.2
80°-90°	30.6	0.4
90°-100°	69.5	0.8
100°-110°	259.0	3.1
110°-120°	686.8	8.1
120°-130°	1139.1	13.5
130°-140°	1209.9	14.3
140°-150°	1124.5	13.3
150°-160°	904.1	10.7
160°-170°	582.6	6.9
170°-180°	200.5	2.4
0°-30°	787.5	9.3
0°-40°	1222.8	14.5
0°-60°	1937.2	22.9
0°-90°	2277.6	26.9
90°-120°	1015.2	12.0
90°-150°	4488.7	53.1
90°-180°	6176.0	73.1
0°-180°	8453.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	1	18	30	38	41	8
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	

TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4

TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6

TEST NUMBER: P922583

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.45	8.12	8.59	9.24	10.81	3.41	4.08	4.55	5.21	6.77
	3H	9.09	9.69	10.24	10.83	12.41	4.57	5.17	5.71	6.30	7.88
	4H	9.68	10.25	10.83	11.38	12.97	5.00	5.57	6.15	6.70	8.29
	6H	10.08	10.60	11.24	11.74	13.34	5.29	5.82	6.46	6.95	8.55
	8H	10.19	10.69	11.36	11.84	13.43	5.37	5.87	6.54	7.02	8.61
	12H	10.24	10.71	11.41	11.86	13.47	5.40	5.87	6.57	7.02	8.63
4H	2H	7.44	8.01	8.60	9.14	10.73	3.97	4.54	5.14	5.68	7.27
	3H	9.23	9.71	10.40	10.87	12.47	5.29	5.76	6.45	6.92	8.52
	4H	9.90	10.34	11.07	11.49	13.11	5.81	6.25	6.98	7.40	9.02
	6H	10.39	10.76	11.57	11.94	13.55	6.21	6.58	7.38	7.75	9.36
	8H	10.55	10.90	11.73	12.06	13.69	6.32	6.67	7.49	7.83	9.46
	12H	10.63	10.95	11.82	12.12	13.75	6.37	6.68	7.56	7.86	9.49
8H	4H	9.86	10.20	11.03	11.37	12.99	6.07	6.42	7.24	7.58	9.21
	6H	10.39	10.68	11.59	11.89	13.51	6.56	6.85	7.75	8.05	9.67
	8H	10.60	10.85	11.79	12.03	13.67	6.74	6.99	7.93	8.17	9.81
	12H	10.71	10.93	11.92	12.11	13.79	6.83	7.05	8.03	8.23	9.91
12H	4H	9.80	10.11	10.99	11.29	12.92	6.07	6.38	7.25	7.55	9.19
	6H	10.37	10.62	11.56	11.80	13.44	6.60	6.85	7.80	8.03	9.68
	8H	10.57	10.79	11.77	11.97	13.64	6.79	7.01	7.99	8.19	9.87