

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908997

Luminaire Tested: DFN2DIP-SQ2F0-060D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908997
REPORT IS A COMBINATION OF REPORTS P901297 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-060D030US840-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8997.9 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5184	5184	5184
5°	5183	5101	5139
10°	5133	5021	5062
15°	5048	4927	4946
20°	4937	4801	4828
25°	4826	4652	4692
30°	4690	4513	4522
35°	4560	4351	4341
40°	4401	4187	4169
45°	4243	4022	3993
50°	4069	3848	3790
55°	3886	3648	3601
60°	3680	3411	3384
65°	3452	3165	3129
70°	3164	2863	2853
75°	2768	2503	2588
80°	2286	2043	2102
85°	1544	1290	1321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4243 cd/sqm

TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.9	2.5
10°-20°	624.4	6.9
20°-30°	917.5	10.2
30°-40°	1065.7	11.8
40°-50°	1064.4	11.8
50°-60°	928.1	10.3
60°-70°	686.1	7.6
70°-80°	388.2	4.3
80°-90°	104.2	1.2
90°-100°	33.7	0.4
100°-110°	125.7	1.4
110°-120°	333.3	3.7
120°-130°	552.9	6.1
130°-140°	587.3	6.5
140°-150°	545.8	6.1
150°-160°	438.8	4.9
160°-170°	282.8	3.1
170°-180°	97.3	1.1
0°-30°	1763.8	19.6
0°-40°	2829.5	31.4
0°-60°	4821.9	53.6
0°-90°	6000.4	66.7
90°-120°	492.7	5.5
90°-150°	2178.7	24.2
90°-180°	2998.0	33.3
0°-180°	8997.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2358	2358	2358	2358	2358	
5°	2358	2349	2324	2342	2337	224
15°	2244	2231	2201	2210	2199	632
25°	2031	2013	1975	1979	1975	935
35°	1752	1730	1694	1680	1668	1094
45°	1426	1410	1376	1351	1342	1101
55°	1079	1066	1038	1011	1000	965
65°	728	714	692	671	660	720
75°	381	376	365	351	356	406
85°	93	91	88	82	79	104
90°	1	9	15	19	20	8
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2357.6	2357.6	2357.6	2357.6	2357.6
2.5°	2371.4	2360.1	2335.0	2357.6	2353.3
5°	2357.6	2348.7	2323.7	2341.8	2337.4
7.5°	2341.8	2328.3	2303.3	2321.6	2317.0
10°	2317.0	2301.2	2273.9	2292.0	2285.2
12.5°	2282.9	2269.4	2242.2	2253.5	2249.0
15°	2244.3	2230.9	2201.3	2210.5	2199.2
17.5°	2196.8	2183.3	2153.7	2164.9	2153.7
20°	2144.6	2131.1	2099.3	2106.1	2097.2
22.5°	2092.6	2072.1	2042.6	2042.6	2038.0
25°	2031.2	2013.3	1974.7	1979.0	1974.7
27.5°	1963.2	1947.3	1917.9	1911.3	1900.0
30°	1895.4	1877.0	1843.2	1836.4	1827.3
32.5°	1822.7	1809.3	1772.9	1759.2	1750.1
35°	1752.5	1729.9	1693.5	1679.8	1668.5
37.5°	1673.1	1652.6	1616.4	1600.4	1589.1
40°	1591.5	1573.3	1537.0	1516.8	1507.6
42.5°	1512.2	1493.9	1457.8	1435.0	1421.5
45°	1426.1	1410.2	1376.0	1351.3	1342.1
47.5°	1342.1	1326.3	1290.0	1265.0	1251.4
50°	1253.6	1242.3	1210.6	1178.8	1167.5
52.5°	1167.5	1151.7	1122.3	1097.3	1081.5
55°	1079.2	1065.5	1038.3	1011.2	999.9
57.5°	990.8	979.5	949.9	922.7	913.5
60°	902.2	893.3	861.6	836.6	829.8
62.5°	816.1	800.2	777.6	755.0	745.9
65°	727.8	714.2	691.6	671.1	659.7
67.5°	637.1	625.6	605.4	589.6	580.4
70°	553.2	544.1	523.6	507.8	498.9
72.5°	467.1	458.0	446.7	430.8	424.0
75°	380.7	376.5	364.9	351.4	356.0
77.5°	303.8	294.7	290.0	283.4	276.6
80°	226.8	224.4	219.8	213.1	208.5
82.5°	154.2	154.2	152.0	142.9	142.9
85°	92.8	90.7	88.5	81.5	79.4
87.5°	40.9	36.4	31.7	25.0	22.6
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P908997

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.29	15.32	15.09	16.14	17.16	13.84	14.88	14.64	15.70	16.71
	3H	15.94	16.87	16.75	17.70	18.74	15.45	16.38	16.26	17.21	18.25
	4H	16.52	17.40	17.35	18.24	19.29	16.03	16.91	16.86	17.75	18.80
	6H	16.92	17.73	17.76	18.57	19.64	16.42	17.23	17.26	18.07	19.14
	8H	17.02	17.79	17.87	18.66	19.72	16.52	17.29	17.37	18.16	19.22
	12H	17.07	17.80	17.92	18.66	19.75	16.56	17.29	17.41	18.15	19.24
4H	2H	14.76	15.64	15.59	16.48	17.53	14.40	15.28	15.24	16.12	17.17
	3H	16.62	17.35	17.46	18.22	19.29	16.21	16.94	17.05	17.81	18.88
	4H	17.32	17.99	18.18	18.86	19.95	16.90	17.57	17.76	18.44	19.53
	6H	17.83	18.41	18.70	19.30	20.40	17.40	17.97	18.27	18.87	19.97
	8H	17.97	18.51	18.85	19.40	20.51	17.54	18.08	18.41	18.96	20.07
	12H	18.05	18.53	18.94	19.44	20.56	17.60	18.08	18.49	18.99	20.11
8H	4H	17.52	18.06	18.40	18.95	20.06	17.14	17.68	18.02	18.57	19.68
	6H	18.14	18.58	19.04	19.51	20.62	17.75	18.20	18.66	19.13	20.24
	8H	18.35	18.74	19.26	19.67	20.79	17.95	18.35	18.87	19.27	20.40
	12H	18.47	18.82	19.39	19.74	20.92	18.06	18.41	18.98	19.33	20.51
12H	4H	17.51	18.00	18.41	18.91	20.02	17.14	17.63	18.04	18.54	19.65
	6H	18.16	18.56	19.08	19.48	20.61	17.79	18.19	18.70	19.11	20.24
	8H	18.40	18.75	19.32	19.66	20.84	18.02	18.36	18.93	19.28	20.46