

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922613

Luminaire Tested: DFN2DIP-SQ2F0-050D030US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922613
REPORT IS A COMBINATION OF REPORTS P901295 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D030US940-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7062.4 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3814	3753	3782
10°	3777	3695	3725
15°	3714	3625	3640
20°	3633	3533	3553
25°	3552	3423	3453
30°	3451	3321	3327
35°	3355	3202	3195
40°	3239	3081	3068
45°	3122	2959	2938
50°	2994	2832	2789
55°	2860	2684	2650
60°	2708	2510	2490
65°	2540	2328	2302
70°	2328	2107	2099
75°	2037	1842	1905
80°	1682	1504	1547
85°	1136	949	972

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3122 cd/sqm

TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	2.3
10°-20°	459.4	6.5
20°-30°	675.2	9.6
30°-40°	784.2	11.1
40°-50°	783.2	11.1
50°-60°	682.9	9.7
60°-70°	504.8	7.1
70°-80°	285.6	4.0
80°-90°	77.0	1.1
90°-100°	29.8	0.4
100°-110°	111.0	1.6
110°-120°	294.3	4.2
120°-130°	488.2	6.9
130°-140°	518.5	7.3
140°-150°	481.9	6.8
150°-160°	387.5	5.5
160°-170°	249.7	3.5
170°-180°	85.9	1.2
0°-30°	1297.9	18.4
0°-40°	2082.0	29.5
0°-60°	3548.1	50.2
0°-90°	4415.6	62.5
90°-120°	435.1	6.2
90°-150°	1923.7	27.2
90°-180°	2647.0	37.5
0°-180°	7062.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	1	8	13	16	18	7
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6

TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P922613

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.89	13.88	13.73	14.74	15.82	12.45	13.43	13.29	14.30	15.38
	3H	14.54	15.43	15.39	16.30	17.41	14.05	14.94	14.90	15.81	16.92
	4H	15.12	15.96	15.99	16.84	17.96	14.63	15.46	15.50	16.34	17.46
	6H	15.51	16.28	16.40	17.17	18.30	15.01	15.78	15.89	16.67	17.80
	8H	15.61	16.35	16.50	17.25	18.38	15.11	15.85	16.00	16.75	17.88
	12H	15.66	16.36	16.56	17.26	18.41	15.15	15.85	16.05	16.75	17.91
4H	2H	13.36	14.19	14.23	15.07	16.19	13.00	13.84	13.87	14.72	15.83
	3H	15.21	15.91	16.10	16.82	17.95	14.80	15.50	15.69	16.41	17.54
	4H	15.91	16.55	16.81	17.46	18.62	15.49	16.13	16.39	17.03	18.19
	6H	16.42	16.97	17.33	17.90	19.06	15.99	16.54	16.90	17.47	18.63
	8H	16.56	17.07	17.48	18.00	19.18	16.12	16.64	17.04	17.56	18.74
	12H	16.63	17.09	17.57	18.04	19.22	16.18	16.65	17.12	17.59	18.77
8H	4H	16.11	16.62	17.02	17.55	18.72	15.73	16.24	16.65	17.17	18.35
	6H	16.72	17.15	17.66	18.12	19.29	16.34	16.76	17.28	17.73	18.90
	8H	16.93	17.31	17.88	18.27	19.46	16.54	16.91	17.49	17.87	19.06
	12H	17.05	17.39	18.01	18.34	19.58	16.64	16.98	17.60	17.93	19.17
12H	4H	16.10	16.56	17.03	17.51	18.69	15.73	16.19	16.66	17.14	18.32
	6H	16.75	17.12	17.70	18.08	19.27	16.37	16.75	17.33	17.71	18.90
	8H	16.98	17.31	17.93	18.26	19.50	16.60	16.93	17.55	17.88	19.12