

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925311

Luminaire Tested: DFN2DIP-SQ2F0-030D070US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925311
REPORT IS A COMBINATION OF REPORTS P901340 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D070US950-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9043.9 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30
2	85	78	72	67	75	70	65	61	55	51	49	41	39	37	28	27	26
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19
5	65	54	46	41	58	49	42	37	39	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	13	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11
10	44	33	26	22	40	30	24	20	24	20	16	19	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2601	2601	2601
5°	2601	2554	2572
10°	2570	2498	2485
15°	2531	2410	2352
20°	2479	2291	2191
25°	2427	2159	2035
30°	2358	2024	1838
35°	2290	1878	1666
40°	2220	1729	1469
45°	2140	1565	1290
50°	2057	1399	1115
55°	1969	1222	949
60°	1868	1039	777
65°	1752	852	695
70°	1610	679	624
75°	1431	588	560
80°	1176	477	475
85°	765	296	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2141 cd/sqm

TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	1.2
10°-20°	304.3	3.4
20°-30°	427.3	4.7
30°-40°	465.7	5.1
40°-50°	428.1	4.7
50°-60°	336.2	3.7
60°-70°	218.8	2.4
70°-80°	112.6	1.2
80°-90°	32.7	0.4
90°-100°	74.3	0.8
100°-110°	277.0	3.1
110°-120°	734.8	8.1
120°-130°	1218.6	13.5
130°-140°	1294.5	14.3
140°-150°	1203.1	13.3
150°-160°	967.2	10.7
160°-170°	623.3	6.9
170°-180°	214.5	2.4
0°-30°	842.5	9.3
0°-40°	1308.2	14.5
0°-60°	2072.5	22.9
0°-90°	2436.6	26.9
90°-120°	1086.1	12.0
90°-150°	4802.2	53.1
90°-180°	6607.0	73.1
0°-180°	9043.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	2	20	32	41	44	8
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8

TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P925311

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.68	8.35	8.82	9.48	11.05	3.64	4.31	4.78	5.44	7.01
	3H	9.33	9.93	10.47	11.06	12.65	4.80	5.40	5.95	6.53	8.12
	4H	9.92	10.49	11.07	11.62	13.21	5.23	5.80	6.38	6.93	8.52
	6H	10.31	10.84	11.48	11.97	13.57	5.53	6.05	6.69	7.19	8.79
	8H	10.43	10.93	11.59	12.08	13.67	5.60	6.10	6.77	7.25	8.85
	12H	10.48	10.95	11.64	12.09	13.71	5.63	6.11	6.80	7.25	8.87
4H	2H	7.68	8.25	8.84	9.38	10.97	4.21	4.78	5.37	5.91	7.50
	3H	9.47	9.94	10.63	11.10	12.70	5.52	6.00	6.69	7.16	8.76
	4H	10.14	10.58	11.31	11.72	13.34	6.05	6.48	7.22	7.63	9.25
	6H	10.63	11.00	11.80	12.17	13.78	6.44	6.81	7.61	7.98	9.59
	8H	10.79	11.14	11.96	12.30	13.92	6.55	6.90	7.73	8.06	9.69
	12H	10.86	11.18	12.05	12.35	13.98	6.60	6.92	7.79	8.09	9.72
8H	4H	10.09	10.44	11.26	11.60	13.23	6.30	6.65	7.48	7.81	9.44
	6H	10.63	10.92	11.82	12.12	13.74	6.79	7.08	7.98	8.28	9.91
	8H	10.83	11.08	12.03	12.26	13.91	6.97	7.22	8.17	8.40	10.05
	12H	10.95	11.17	12.15	12.35	14.02	7.07	7.29	8.27	8.47	10.14
12H	4H	10.03	10.35	11.22	11.52	13.15	6.30	6.61	7.49	7.79	9.42
	6H	10.60	10.85	11.80	12.03	13.68	6.84	7.09	8.03	8.27	9.91
	8H	10.80	11.02	12.00	12.20	13.88	7.02	7.24	8.22	8.42	10.10

END OF REPORT