

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925315

Luminaire Tested: DFN2DIP-SQ2F0-030D080US950-RLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P925315  
REPORT IS A COMBINATION OF REPORTS P901352 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-030D080US950-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9988.4 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 88  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925315  
CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P925315

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	21	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14				14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12				12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12	9				9
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	13	11	9				9
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	11	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2601	2601	2601
5°	2601	2554	2572
10°	2570	2498	2485
15°	2531	2410	2352
20°	2479	2291	2191
25°	2427	2159	2035
30°	2358	2024	1838
35°	2290	1878	1666
40°	2220	1729	1469
45°	2140	1565	1290
50°	2057	1399	1115
55°	1969	1222	949
60°	1868	1039	777
65°	1752	852	695
70°	1610	679	624
75°	1431	588	560
80°	1176	477	475
85°	765	296	338

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2447 cd/sqm



TEST NUMBER: P925315

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.9	1.1
10°-20°	304.3	3.0
20°-30°	427.3	4.3
30°-40°	465.7	4.7
40°-50°	428.1	4.3
50°-60°	336.2	3.4
60°-70°	218.8	2.2
70°-80°	112.6	1.1
80°-90°	33.3	0.3
90°-100°	84.9	0.9
100°-110°	316.6	3.2
110°-120°	839.7	8.4
120°-130°	1392.7	13.9
130°-140°	1479.4	14.8
140°-150°	1374.9	13.8
150°-160°	1105.4	11.1
160°-170°	712.3	7.1
170°-180°	245.2	2.5
0°-30°	842.5	8.4
0°-40°	1308.2	13.1
0°-60°	2072.5	20.7
0°-90°	2437.2	24.4
90°-120°	1241.3	12.4
90°-150°	5488.3	54.9
90°-180°	7551.0	75.6
0°-180°	9988.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	2	22	37	47	50	9
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P925315

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P925315

CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P925315  
 CATALOG NUMBER: DFN2DIP-SQ2F0-030D080US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.28	7.94	8.44	9.08	10.68	3.24	3.90	4.40	5.04	6.64
	3H	8.93	9.52	10.09	10.66	12.28	4.40	4.99	5.56	6.14	7.75
	4H	9.52	10.07	10.69	11.22	12.84	4.83	5.39	6.00	6.54	8.15
	6H	9.91	10.43	11.09	11.58	13.20	5.13	5.64	6.30	6.79	8.42
	8H	10.03	10.51	11.21	11.68	13.30	5.20	5.69	6.38	6.86	8.48
	12H	10.07	10.54	11.26	11.69	13.34	5.23	5.70	6.42	6.85	8.50
4H	2H	7.28	7.83	8.45	8.98	10.60	3.81	4.37	4.99	5.51	7.13
	3H	9.07	9.53	10.25	10.70	12.33	5.12	5.59	6.30	6.76	8.39
	4H	9.74	10.17	10.92	11.33	12.97	5.65	6.07	6.83	7.23	8.88
	6H	10.22	10.59	11.41	11.77	13.41	6.04	6.40	7.22	7.59	9.22
	8H	10.38	10.73	11.57	11.90	13.55	6.15	6.49	7.34	7.67	9.32
	12H	10.46	10.77	11.66	11.96	13.61	6.20	6.51	7.40	7.69	9.35
8H	4H	9.69	10.03	10.87	11.20	12.86	5.90	6.24	7.09	7.42	9.07
	6H	10.23	10.51	11.43	11.72	13.37	6.39	6.67	7.60	7.89	9.54
	8H	10.43	10.67	11.64	11.87	13.54	6.57	6.81	7.78	8.00	9.68
	12H	10.55	10.76	11.76	11.95	13.65	6.66	6.88	7.88	8.07	9.77
12H	4H	9.63	9.94	10.83	11.13	12.78	5.90	6.21	7.10	7.39	9.05
	6H	10.20	10.44	11.41	11.64	13.31	6.43	6.68	7.64	7.87	9.54
	8H	10.40	10.61	11.61	11.80	13.51	6.62	6.83	7.83	8.03	9.73