

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911710

Luminaire Tested: DFN2DIP-SQ2F0-050D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911710
REPORT IS A COMBINATION OF REPORTS P899800 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D050US850-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9620.6 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5039	5039	5039
5°	5039	4948	4984
10°	4980	4840	4815
15°	4903	4670	4558
20°	4803	4439	4244
25°	4701	4183	3942
30°	4568	3921	3562
35°	4436	3640	3227
40°	4302	3350	2845
45°	4147	3031	2499
50°	3986	2710	2161
55°	3817	2367	1838
60°	3620	2011	1506
65°	3394	1651	1348
70°	3120	1315	1210
75°	2774	1138	1086
80°	2278	925	920
85°	1484	574	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4147 cd/sqm

TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	2.2
10°-20°	589.6	6.1
20°-30°	827.8	8.6
30°-40°	902.4	9.4
40°-50°	829.4	8.6
50°-60°	651.3	6.8
60°-70°	424.0	4.4
70°-80°	218.2	2.3
80°-90°	60.7	0.6
90°-100°	108.5	1.1
100°-110°	344.8	3.6
110°-120°	590.1	6.1
120°-130°	776.0	8.1
130°-140°	871.0	9.1
140°-150°	854.2	8.9
150°-160°	716.5	7.4
160°-170°	475.2	4.9
170°-180°	166.1	1.7
0°-30°	1632.2	17.0
0°-40°	2534.6	26.3
0°-60°	4015.3	41.7
0°-90°	4718.3	49.0
90°-120°	1043.4	10.8
90°-150°	3544.6	36.8
90°-180°	4902.0	51.0
0°-180°	9620.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	2	19	52	49	50	9
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	

TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7

TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7

TEST NUMBER: P911710

CATALOG NUMBER: DFN2DIP-SQ2F0-050D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.56	13.38	13.53	14.36	15.65	8.52	9.34	9.49	10.32	11.61
	3H	14.22	14.95	15.20	15.94	17.25	9.69	10.43	10.67	11.42	12.73
	4H	14.81	15.51	15.81	16.50	17.82	10.13	10.82	11.12	11.82	13.13
	6H	15.22	15.86	16.22	16.86	18.19	10.43	11.07	11.44	12.07	13.40
	8H	15.33	15.94	16.35	16.96	18.29	10.51	11.12	11.53	12.14	13.46
	12H	15.39	15.97	16.41	16.98	18.33	10.55	11.13	11.57	12.14	13.49
4H	2H	12.57	13.27	13.57	14.26	15.58	9.10	9.80	10.11	10.79	12.11
	3H	14.38	14.96	15.39	15.98	17.31	10.43	11.01	11.44	12.03	13.36
	4H	15.05	15.58	16.07	16.60	17.95	10.96	11.49	11.98	12.51	13.86
	6H	15.55	16.00	16.58	17.04	18.39	11.36	11.82	12.39	12.86	14.21
	8H	15.71	16.14	16.74	17.17	18.54	11.48	11.90	12.51	12.94	14.30
	12H	15.80	16.18	16.85	17.23	18.60	11.54	11.92	12.58	12.96	14.34
8H	4H	15.02	15.44	16.05	16.47	17.84	11.23	11.66	12.26	12.69	14.05
	6H	15.56	15.91	16.62	16.98	18.35	11.73	12.08	12.78	13.15	14.51
	8H	15.76	16.07	16.83	17.13	18.51	11.90	12.21	12.96	13.27	14.65
	12H	15.89	16.16	16.95	17.21	18.64	12.01	12.28	13.07	13.33	14.76
12H	4H	14.97	15.35	16.02	16.40	17.77	11.23	11.62	12.28	12.66	14.03
	6H	15.53	15.84	16.60	16.90	18.28	11.77	12.08	12.83	13.14	14.52
	8H	15.74	16.01	16.81	17.06	18.49	11.96	12.23	13.03	13.29	14.71