

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925340

Luminaire Tested: DFN2DIP-SQ2F0-050D030US950-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P925340  
REPORT IS A COMBINATION OF REPORTS P899775 AND P896659  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-050D030US950-FLLFLL  
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7255.1 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 67  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925340  
CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P925340

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59	55				55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46				46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39				39
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37	33				33
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29				29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	26				26
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	23				23
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20				20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18				18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19	17				17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4081	4081	4081
5°	4081	4015	4046
10°	4040	3953	3985
15°	3974	3878	3894
20°	3887	3779	3801
25°	3800	3662	3694
30°	3692	3553	3560
35°	3590	3425	3418
40°	3465	3296	3282
45°	3340	3166	3144
50°	3203	3029	2983
55°	3060	2871	2835
60°	2897	2686	2664
65°	2718	2491	2464
70°	2491	2254	2246
75°	2179	1970	2038
80°	1800	1609	1655
85°	1216	1015	1040

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3340 cd/sqm



TEST NUMBER: P925340

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.4
10°-20°	491.5	6.8
20°-30°	722.3	10.0
30°-40°	838.9	11.6
40°-50°	837.9	11.5
50°-60°	730.6	10.1
60°-70°	540.1	7.4
70°-80°	305.6	4.2
80°-90°	83.2	1.1
90°-100°	56.0	0.8
100°-110°	178.0	2.5
110°-120°	304.6	4.2
120°-130°	400.5	5.5
130°-140°	449.6	6.2
140°-150°	440.9	6.1
150°-160°	369.8	5.1
160°-170°	245.3	3.4
170°-180°	85.7	1.2
0°-30°	1388.5	19.1
0°-40°	2227.5	30.7
0°-60°	3796.0	52.3
0°-90°	4724.9	65.1
90°-120°	538.5	7.4
90°-150°	1829.5	25.2
90°-180°	2530.0	34.9
0°-180°	7255.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	10	27	25	26	7
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P925340

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P925340

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P925340  
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US950-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.35	14.15	15.19	16.22	12.89	13.90	13.70	14.74	15.78
	3H	14.98	15.90	15.81	16.74	17.81	14.49	15.41	15.32	16.25	17.32
	4H	15.57	16.43	16.41	17.28	18.36	15.07	15.93	15.92	16.79	17.87
	6H	15.96	16.75	16.82	17.62	18.71	15.46	16.25	16.32	17.12	18.21
	8H	16.06	16.82	16.93	17.70	18.79	15.56	16.32	16.43	17.20	18.29
	12H	16.11	16.83	16.98	17.70	18.82	15.60	16.32	16.47	17.20	18.31
4H	2H	13.80	14.66	14.65	15.52	16.59	13.45	14.31	14.29	15.16	16.24
	3H	15.66	16.38	16.52	17.26	18.36	15.25	15.97	16.11	16.86	17.95
	4H	16.36	17.02	17.24	17.90	19.02	15.94	16.59	16.81	17.48	18.60
	6H	16.87	17.44	17.76	18.34	19.46	16.44	17.00	17.33	17.91	19.03
	8H	17.01	17.54	17.90	18.44	19.58	16.58	17.10	17.47	18.01	19.14
	12H	17.08	17.56	17.99	18.48	19.62	16.64	17.11	17.55	18.04	19.18
8H	4H	16.56	17.09	17.45	17.99	19.13	16.18	16.71	17.07	17.62	18.75
	6H	17.17	17.61	18.09	18.56	19.69	16.79	17.23	17.71	18.17	19.31
	8H	17.38	17.77	18.31	18.71	19.86	16.99	17.38	17.92	18.32	19.47
	12H	17.51	17.85	18.44	18.78	19.98	17.10	17.44	18.03	18.37	19.57
12H	4H	16.55	17.03	17.46	17.95	19.09	16.18	16.66	17.09	17.58	18.72
	6H	17.20	17.59	18.13	18.53	19.68	16.83	17.22	17.76	18.15	19.30
	8H	17.43	17.78	18.37	18.71	19.91	17.05	17.40	17.99	18.33	19.53