

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925391

Luminaire Tested: DFN2DIP-SQ2F0-070D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925391
REPORT IS A COMBINATION OF REPORTS P901300 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-070D030US950-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8509.6 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71
1	102	98	94	91	96	93	89	86	82	80	78		73	71	69		64
2	94	86	80	75	88	82	76	72	73	69	65		65	62	59		57
3	86	77	69	64	81	72	66	61	65	60	56		58	54	51		51
4	79	68	60	54	74	65	58	52	58	53	48		52	48	44		46
5	73	61	53	47	68	58	51	45	52	47	42		47	42	39		42
6	67	55	47	41	63	53	45	40	48	42	37		43	38	34		38
7	62	50	42	37	59	48	41	36	43	37	33		39	34	31		35
8	58	46	38	33	55	44	37	32	40	34	30		36	31	28		33
9	54	42	35	30	51	40	33	29	37	31	27		33	29	25		30
10	51	39	32	27	48	37	31	26	34	28	24		31	26	23		28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6069	6069	6069
5°	6068	5959	6002
10°	5998	5829	5799
15°	5904	5624	5489
20°	5785	5346	5112
25°	5662	5037	4748
30°	5501	4721	4289
35°	5342	4384	3886
40°	5181	4035	3426
45°	4994	3651	3009
50°	4800	3263	2603
55°	4596	2851	2213
60°	4360	2423	1814
65°	4087	1989	1623
70°	3757	1584	1456
75°	3340	1371	1308
80°	2744	1113	1109
85°	1785	691	789

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4994 cd/sqm

TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	3.0
10°-20°	710.1	8.3
20°-30°	997.0	11.7
30°-40°	1086.8	12.8
40°-50°	998.8	11.7
50°-60°	784.4	9.2
60°-70°	510.6	6.0
70°-80°	262.8	3.1
80°-90°	68.8	0.8
90°-100°	31.9	0.4
100°-110°	118.7	1.4
110°-120°	314.9	3.7
120°-130°	522.3	6.1
130°-140°	554.8	6.5
140°-150°	515.6	6.1
150°-160°	414.5	4.9
160°-170°	267.1	3.1
170°-180°	91.9	1.1
0°-30°	1965.7	23.1
0°-40°	3052.5	35.9
0°-60°	4835.8	56.8
0°-90°	5678.0	66.7
90°-120°	465.5	5.5
90°-150°	2058.1	24.2
90°-180°	2832.0	33.3
0°-180°	8509.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2760	2760	2760	2760	2760	
5°	2760	2748	2715	2738	2730	262
15°	2625	2598	2513	2465	2440	740
25°	2383	2303	2138	2036	1998	1096
35°	2053	1926	1706	1549	1494	1285
45°	1679	1511	1249	1071	1012	1296
55°	1276	1082	812	662	615	1140
65°	862	659	435	350	342	854
75°	460	285	200	182	180	486
85°	107	55	47	47	47	123
90°	1	8	14	18	19	8
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	

TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2760.0	2760.0	2760.0	2760.0	2760.0
2.5°	2772.4	2760.0	2732.4	2757.6	2752.6
5°	2760.0	2747.5	2715.0	2737.5	2730.1
7.5°	2737.5	2722.6	2687.7	2697.4	2685.0
10°	2707.5	2690.1	2640.2	2632.6	2617.7
12.5°	2670.2	2647.6	2580.1	2565.2	2537.6
15°	2625.1	2597.6	2512.7	2465.3	2440.4
17.5°	2572.7	2532.7	2427.7	2372.8	2332.8
20°	2512.7	2462.7	2337.9	2275.6	2220.4
22.5°	2447.9	2390.3	2245.3	2160.5	2123.2
25°	2382.9	2302.9	2138.0	2035.7	1998.2
27.5°	2305.5	2220.4	2038.1	1920.8	1863.3
30°	2223.1	2128.0	1928.1	1801.0	1733.4
32.5°	2143.1	2028.1	1823.5	1673.5	1610.9
35°	2053.2	1925.7	1706.1	1548.7	1493.6
37.5°	1965.8	1828.2	1596.1	1423.6	1361.4
40°	1873.3	1723.6	1481.1	1303.8	1238.9
42.5°	1778.4	1618.7	1366.3	1181.3	1119.1
45°	1678.6	1511.0	1249.0	1071.4	1011.5
47.5°	1583.6	1406.4	1136.6	959.1	904.2
50°	1478.7	1301.4	1026.6	854.1	801.9
52.5°	1376.1	1188.8	921.7	756.8	709.4
55°	1276.3	1081.5	811.7	662.0	614.6
57.5°	1174.0	974.1	714.5	574.5	534.5
60°	1069.1	869.2	611.9	484.7	444.7
62.5°	966.7	766.9	524.4	404.7	384.7
65°	861.7	659.3	434.6	349.8	342.1
67.5°	761.9	559.4	349.8	307.1	299.7
70°	656.9	462.1	289.6	264.7	254.6
72.5°	557.0	372.1	242.2	222.4	217.3
75°	459.5	284.6	199.8	182.3	179.9
77.5°	362.2	202.2	157.4	147.3	142.3
80°	272.2	144.9	119.8	110.0	110.0
82.5°	189.8	97.5	82.4	77.4	77.4
85°	107.3	54.9	47.4	47.4	47.4
87.5°	40.0	19.8	19.8	17.5	17.5
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2

TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P925391

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.73	15.72	15.54	16.54	17.56	10.69	11.68	11.50	12.50	13.52
	3H	16.40	17.29	17.22	18.12	19.16	11.87	12.76	12.69	13.59	14.63
	4H	17.00	17.84	17.84	18.68	19.73	12.32	13.15	13.16	13.99	15.05
	6H	17.42	18.19	18.27	19.03	20.10	12.63	13.40	13.48	14.25	15.31
	8H	17.54	18.27	18.40	19.14	20.20	12.72	13.45	13.58	14.32	15.38
	12H	17.60	18.29	18.46	19.15	20.25	12.76	13.45	13.62	14.31	15.41
4H	2H	14.76	15.60	15.61	16.44	17.49	11.30	12.13	12.14	12.97	14.02
	3H	16.59	17.28	17.44	18.15	19.22	12.64	13.33	13.49	14.21	15.27
	4H	17.27	17.90	18.13	18.77	19.87	13.18	13.81	14.04	14.68	15.77
	6H	17.77	18.32	18.65	19.21	20.31	13.59	14.13	14.47	15.02	16.12
	8H	17.94	18.45	18.82	19.34	20.45	13.71	14.21	14.59	15.10	16.22
	12H	18.03	18.49	18.93	19.40	20.51	13.77	14.22	14.67	15.13	16.25
8H	4H	17.24	17.75	18.13	18.64	19.75	13.46	13.96	14.34	14.85	15.97
	6H	17.79	18.21	18.70	19.14	20.26	13.96	14.38	14.87	15.31	16.42
	8H	18.00	18.37	18.92	19.29	20.42	14.14	14.51	15.06	15.43	16.56
	12H	18.13	18.46	19.05	19.37	20.55	14.25	14.57	15.17	15.49	16.67
12H	4H	17.20	17.66	18.10	18.57	19.68	13.47	13.92	14.37	14.83	15.95
	6H	17.77	18.14	18.69	19.06	20.19	14.00	14.37	14.92	15.30	16.43
	8H	17.98	18.31	18.90	19.22	20.41	14.20	14.53	15.13	15.45	16.63

END OF REPORT